


FEATURES

- Planar Die Construction
- Ultra-Small Surface Mount Package
- General purpose, Medium Current
- Ideally Suited for Automated Assembly Processes



Maximum Ratings(T_a=25°C unless otherwise specified)








| Characteristic | Symbol | Value | Unit |
|--|-----------------------------------|----------|------|
| Forward Voltage (Note 2) @ I _F = 10mA | V _F | 0.9 | V |
| Power Dissipation(Note 1) | P _d | 500 | mW |
| Thermal Resistance, Junction to Ambient Air | R _{θJA} | 250 | °C/W |
| Operation Junction and Storage Temperature Range | T _J , T _{stg} | -55~+150 | °C |

Notes:1. Mounted on 1 in² FR-4 board with 2oz. Copper, in a still air environment with T_a=25 °C.
2. Tested with pulses, T_p≤1.0ms.




ELECTRICAL CHARACTERISTICS $T_a=25^\circ\text{C}$ unless otherwise specified

| Type Number | Code | Zener Voltage Range (Note 2) | | | | Maximum Zener Impedance (Note 4) | | | Maximum Reverse Current | |
|-------------|------|------------------------------|--------|--------|----------|----------------------------------|-----------------|----------|-------------------------|-------|
| | | $V_Z@I_{ZT}$ | | | I_{ZT} | $Z_{ZT}@I_{ZT}$ | $Z_{ZK}@I_{ZK}$ | I_{ZK} | I_R | V_R |
| | | Nom(V) | Min(V) | Max(V) | mA | Ω | | mA | μA | V |
| MMSZ5221B | C1 | 2.4 | 2.28 | 2.52 | 20 | 30 | 1200 | 0.25 | 100 | 1.0 |
| MMSZ5223B | C3 | 2.7 | 2.57 | 2.84 | 20 | 30 | 1300 | 0.25 | 75 | 1.0 |
| MMSZ5225B | C5 | 3.0 | 2.85 | 3.15 | 20 | 30 | 1600 | 0.25 | 50 | 1.0 |
| MMSZ5226B | G1 | 3.3 | 3.14 | 3.47 | 20 | 28 | 1600 | 0.25 | 25 | 1.0 |
| MMSZ5227B | G2 | 3.6 | 3.42 | 3.78 | 20 | 24 | 1700 | 0.25 | 15 | 1.0 |
| MMSZ5228B | G3 | 3.9 | 3.71 | 4.10 | 20 | 23 | 1900 | 0.25 | 10 | 1.0 |
| MMSZ5229B | G4 | 4.3 | 4.09 | 4.52 | 20 | 22 | 2000 | 0.25 | 5 | 1.0 |
| MMSZ5230B | G5 | 4.7 | 4.47 | 4.94 | 20 | 19 | 1900 | 0.25 | 5 | 2.0 |
| MMSZ5231B | E1 | 5.1 | 4.85 | 5.36 | 20 | 17 | 1600 | 0.25 | 5 | 2.0 |
| MMSZ5232B | E2 | 5.6 | 5.32 | 5.88 | 20 | 11 | 1600 | 0.25 | 5 | 3.0 |
| MMSZ5233B | E3 | 6.0 | 5.70 | 6.30 | 20 | 7 | 1600 | 0.25 | 5 | 3.5 |
| MMSZ5234B | E4 | 6.2 | 5.89 | 6.51 | 20 | 7 | 1000 | 0.25 | 5 | 4.0 |
| MMSZ5235B | E5 | 6.8 | 6.46 | 7.14 | 20 | 5 | 750 | 0.25 | 3 | 5.0 |
| MMSZ5236B | F1 | 7.5 | 7.13 | 7.88 | 20 | 6 | 500 | 0.25 | 3 | 6.0 |
| MMSZ5237B | F2 | 8.2 | 7.79 | 8.61 | 20 | 8 | 500 | 0.25 | 3 | 6.5 |
| MMSZ5238B | F3 | 8.7 | 8.27 | 9.14 | 20 | 8 | 600 | 0.25 | 3 | 6.5 |
| MMSZ5239B | F4 | 9.1 | 8.65 | 9.56 | 20 | 10 | 600 | 0.25 | 3 | 7.0 |
| MMSZ5240B | F5 | 10 | 9.50 | 10.50 | 20 | 17 | 600 | 0.25 | 3 | 8.0 |
| MMSZ5241B | H1 | 11 | 10.45 | 11.55 | 20 | 22 | 600 | 0.25 | 2.0 | 8.4 |
| MMSZ5242B | H2 | 12 | 11.40 | 12.60 | 20 | 30 | 600 | 0.25 | 1.0 | 9.1 |
| MMSZ5243B | H3 | 13 | 12.35 | 13.65 | 9.5 | 13 | 600 | 0.25 | 0.5 | 9.9 |
| MMSZ5244B | H4 | 14 | 13.30 | 14.70 | 9.0 | 15 | 600 | 0.25 | 0.1 | 10 |
| MMSZ5245B | H5 | 15 | 14.25 | 15.75 | 8.5 | 16 | 600 | 0.25 | 0.1 | 11 |
| MMSZ5246B | J1 | 16 | 15.20 | 16.80 | 7.8 | 17 | 600 | 0.25 | 0.1 | 12 |
| MMSZ5247B | J2 | 17 | 16.15 | 17.85 | 7.4 | 19 | 600 | 0.25 | 0.1 | 13 |
| MMSZ5248B | J3 | 18 | 17.10 | 18.90 | 7.0 | 21 | 600 | 0.25 | 0.1 | 14 |
| MMSZ5250B | J5 | 20 | 19.00 | 21.00 | 6.2 | 25 | 600 | 0.25 | 0.1 | 15 |
| MMSZ5251B | K1 | 22 | 20.90 | 23.10 | 5.6 | 29 | 600 | 0.25 | 0.1 | 17 |
| MMSZ5252B | K2 | 24 | 22.80 | 25.20 | 5.2 | 33 | 600 | 0.25 | 0.1 | 18 |
| MMSZ5253B | K3 | 25 | 23.75 | 26.25 | 5.0 | 35 | 600 | 0.25 | 0.1 | 19 |
| MMSZ5254B | K4 | 27 | 25.65 | 28.35 | 5.0 | 41 | 600 | 0.25 | 0.1 | 21 |
| MMSZ5255B | K5 | 28 | 26.60 | 29.40 | 4.5 | 44 | 600 | 0.25 | 0.1 | 21 |
| MMSZ5256B | M1 | 30 | 28.50 | 31.50 | 4.2 | 49 | 600 | 0.25 | 0.1 | 23 |
| MMSZ5257B | M2 | 33 | 31.35 | 34.65 | 3.8 | 58 | 700 | 0.25 | 0.1 | 25 |
| MMSZ5258B | M3 | 36 | 34.20 | 37.80 | 3.4 | 70 | 700 | 0.25 | 0.1 | 27 |
| MMSZ5259B | M4 | 39 | 37.05 | 40.95 | 3.2 | 80 | 800 | 0.25 | 0.1 | 30 |

Typical Characteristics



SOD-123 Package Outline Dimensions



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|-------|
| | Min | Max | Min | Max |
| A | 1.050 | 1.250 | 0.041 | 0.049 |
| A1 | 0.000 | 0.100 | 0.000 | 0.004 |
| A2 | 1.050 | 1.150 | 0.041 | 0.045 |
| b | 0.450 | 0.650 | 0.018 | 0.026 |
| c | 0.080 | 0.150 | 0.003 | 0.006 |
| D | 1.500 | 1.700 | 0.059 | 0.067 |
| E | 2.600 | 2.800 | 0.102 | 0.110 |
| E1 | 3.550 | 3.850 | 0.140 | 0.152 |
| L | 0.500 REF | | 0.020 REF | |
| L1 | 0.250 | 0.450 | 0.010 | 0.018 |
| θ | 0° | 8° | 0° | 8° |