## MHz Range Crystal unit FA-128

### SEIKO EPSON CORPORATION


# Product nameFA-12848.000000 MHz 10.0 +10.0-10.0Product Number / Ordering codeQ22FA12800150xx


Please refer to the 5.Packing information about xx (last 2 digits)

 $\ensuremath{\mathsf{Pb}}\xspace$  free / Complies with EU RoHS directive

1.Absolute maximum ratings	;					
Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions / Remarks
Storage temperature	T_stg	-40	-	+125	°C	Storage as single product
Operating temperature	T_use	-40	-	+105	°C	


2.Specifications(characteris	stics)					
Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions / Remarks
Nominal frequency	f_nom	-	48.000000	-	MHz	Fundamental
Frequency tolerance	f_tol	-10	-	+10	x 10- <sup>6</sup>	@+25°C
Frequency Stability over temperature	f_tem	-20	-	+20	x 10⁻ <sup>6</sup>	-40ºC to +85ºC
Operating temperature	T_use	-40	-	+85	°C	
Level of drive	DL	10	-	100	μW	
Load capacitance	CL	-	10	-	pF	
Motional resistance (ESR)	R1	-	-	60	Ω	
Motional capacitance	C1	-	3.33	-	fF	
Motional inductance	L1	-	3.30	-	mH	
Shunt capacitance	C0	-	0.86	-	pF	
Frequency aging	f_age	-1	_	+1	x10 <sup>-6</sup> /yea	@+25°C, First year






5.Packing	informati	ion				
[1]Product	Product number last 2 digits code (xx) description			The recommended code is "18"		
	Q22FA12	800150xx				
	Code	Condition	Code	Condition		
	01	Any Q'ty vinyl bag(Tape cut)	00	3000pcs / Reel		
	11	Any Q'ty / Reel	18	5000pcs / Reel		
	12	250pcs / Reel				
	14	1000pcs / Reel				

### SEIKO EPSON CORPORATION



#### SEIKO EPSON CORPORATION



•	This material is subject to change without notice.
·	Any part of this material may not be reproduced or duplicated in any form or any means without the written permission of Seiko Epson.
•	The information about applied data, circuitry, software, usage, etc. written in this material is intended for reference only.
	Seiko Epson does not assume any liability for the occurrence of customer damage or infringing on any patent or copyright of a third party.
	This material does not authorize the licensing for any patent or intellectual copyrights.
	When exporting the products or technology described in this material, you should comply with the applicable
	export control laws and regulations and follow the procedures required by such laws and regulations.
•	You are requested not to use the products (and any technical information furnished, if any) for the development
	and/or manufacture of weapon of mass destruction or for other military purposes. You are also requested that
	you
	would not make the products available to any third party who may use the products for such prohibited purposes.
	These products are intended for general use in electronic equipment. When using them in specific applications that require
	extremely high reliability, such as the applications stated below, you must obtain permission from Seiko Epson in advance.
	/ Space equipment (artificial satellites, rockets, etc.)
	/ Transportation vehicles and related (automobiles, aircraft, trains, vessels, etc.)
	/ Medical instruments to sustain life
	/ Submarine transmitters
	/ Power stations and related
	/ Fire work equipment and security equipment
	/ Traffic control equipment
	/ And others requiring equivalent reliability.

Contact us