


Data sheet

Order No.: 1840599

Type: DFK-PC 4/ 6-GF-7,62

Plug component, Screw connection with tension sleeve



The figure shows a 5-pos. version of the product

1 Main features



• No. of pos.	6	• Nominal current	20 A
• Conductor cross section	4 mm ²	• Nominal voltage	630 V
• Color	green	• Connection direction	0 °
• Pitch	7.62 mm	• Type of packaging	packed in cardboard
• Connection method	Screw connection with tension sleeve		

2 Your advantages

- ✓ Well-known connection principle allows worldwide use
- ✓ Low temperature rise, thanks to maximum contact force
- ✓ Allows connection of two conductors
- ✓ Screwable flange for superior mechanical stability
- ✓ Flexible side panels enable convenient wall mounting prewired from the inside



Make sure you always use the latest documentation.


It can be downloaded at: phoenixcontact.net/product/1840599

3 Table of contents

1	Main features.....	1
2	Your advantages	1
3	Table of contents	2
4	3D model in PDF can be activated (Acrobat Reader only).....	3
5	item properties.....	4
	5.1 Connection capacity	4
	5.2 Material data	4
6	Dimensions.....	4
	6.1 Dimensions for the product	5
7	Series drawing.....	6
8	Packaging information	7
9	Application.....	7
	9.1 Temperature limit values	7
10	Mechanical tests.....	8
	10.1 Termination and connection method.....	8
	10.2 Pull-out test	8
11	Electrical tests	9
	11.1 Electrical data	9
	11.2 Air and creepage distances	9
12	Current carrying capacity/derating curves	10
13	Environmental and durability tests	11
	13.1 Vibration test	11
14	Classification for connectors.....	11
15	Approvals	11
16	Commercial Data.....	13
17	corresponding headers.....	13
18	Accessories.....	13
19	Combination tests.....	14

1840599 DFK-PC 4/ 6-GF-7,62

4 3D model in PDF can be activated (Acrobat Reader only)



1840599 DFK-PC 4/ 6-GF-7,62**5 item properties**

Order No.	1840599
Type	DFK-PC 4/ 6-GF-7,62
Type of contact	Male connector
Range of articles	DFK-PC 4/...GF
Pitch	7.62 mm
Number of positions	6
Connection method	Screw connection with tension sleeve
Screw thread	M3
Tightening torque	0.5 Nm ... 0.6 Nm
Locking	Threaded flange
Mounting type	Direct mounting

5.1 Connection capacity

Conductor cross section, solid	0.2 mm ² to 4 mm ²
Conductor cross section, flexible	0.2 mm ² to 4 mm ²
Conductor cross section AWG/kcmil	24 to 10
2 conductors with same cross section, solid	0.2 mm ² to 2.5 mm ²
2 conductors with same cross section, stranded	0.2 mm ² to 2.5 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve	0.25 mm ² to 4 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve	0.25 mm ² to 4 mm ²
2 conductors with same cross section, stranded, with ferrule without plastic sleeve	0.2 mm ² to 1.5 mm ²
2 conductors with same cross section, stranded, with TWIN ferrules with plastic sleeve	0.5 mm ² to 2.5 mm ²
Cylindrical gauge a x b / diameter	3.6 mm x 3.1 mm / 3.0 mm
Stripping length	7 mm

5.2 Material data

Material of metal parts	
Note	WEEE/RoHS-compliant, whisker-free acc. to IEC 60068-2-82/JEDEC JESD 201
Contact material	Cu alloy
Terminal point surface	Sn 5 µm ... 7 µm
Surface contact area	Sn 5 µm ... 7 µm
Surface characteristics	hot-dip tin-plated
Insulating material data	
Insulating material	PA
CTI according to IEC 60112	600
Flammability rating according to UL 94	V0
Color	green (6021)
Glow wire flammability index GWFI according to EN 60695-2-12	850
Glow wire ignition temperature GWIT according to EN 60695-2-13	775
Temperature for the ball pressure test according to EN 60695-10-2	125 °C

6 Dimensions


1840599 DFK-PC 4/ 6-GF-7,62

6.1 Dimensions for the product

Length	32 mm
Width	67.34 mm
Total height	30.5 mm
Dimension a	38.1 mm

1840599 DFK-PC 4/ 6-GF-7,62

7 Series drawing



1840599 DFK-PC 4/ 6-GF-7,62**8 Packaging information**

Type of packaging	packed in cardboard
Pieces per package	50

9 Application**9.1 Temperature limit values**

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C (dependent on the derating curve)

1840599 DFK-PC 4/ 6-GF-7,62**10 Mechanical tests**

Mechanical test group A	
Specification	IEC 61984:2001-06
Visual test	Test passed
Specification	IEC 60512-1-1:2002-02
Dimensional test	Test passed
Specification	IEC 60512-1-2:2002-02
Resistance of marking	Test passed
Specification	IEC 60068-2-70:1995-12
Insertion and withdrawal force	Test passed
Specification	IEC 60512-7:1993-08
No. of cycles	25
Insertion strength per pos. approx.	8 N
Withdraw strength per pos. approx.	6 N
Polarization and coding	Test passed
Specification	IEC 60512-7:1993-08 (Polarization)
Test force	96 N
Contact retention in insert	
Specification	
Test force per pos.	

10.1 Termination and connection method

Specification	IEC 60999-1:1999-11
Check for damage to conductor or loosening	Test passed

10.2 Pull-out test

Termination and connection method: pull-out test	
Specification	IEC 60999-1:1999-11
Result	Test passed
Conductor cross section/conductor type/tractive force actual value	0.2 mm ² / solid / > 10 N
Conductor cross section/conductor type/tractive force actual value	0.2 mm ² / stranded / > 10 N
Conductor cross section/conductor type/tractive force actual value	4 mm ² / solid / > 60 N
Conductor cross section/conductor type/tractive force actual value	4 mm ² / stranded / > 60 N

1840599 DFK-PC 4/ 6-GF-7,62**11 Electrical tests****11.1 Electrical data**


Rated current / conductor cross section	20 A / 4 mm ²
Rated insulation voltage (III/2)	630 V
Rated surge voltage (III/2)	6 kV
Contact resistance	0.4 mΩ
Degree of pollution	2

11.2 Air and creepage distances

Component	Plug component		
Specification	IEC 60664-1:2007-04		
Mains type	unearthed mains		
Insulating material group	I		
Comparative tracking index (IEC 60112:2003-01)	CTI 600		
Rated insulation voltage	400 V	630 V	1000 V
Rated surge voltage	6 kV	6 kV	6 kV
Degree of pollution	3	2	2
Overvoltage category	III	III	II
Minimum clearance case A (inhomogeneous field)	5.5 mm	5.5 mm	5.5 mm
Minimum value of the creepage path requirement in acc. with table	5.5 mm	5.5 mm	5.5 mm

1840599 DFK-PC 4/ 6-GF-7,62**12 Current carrying capacity/derating curves**

Specification	IEC 61984:2001-06
Note	Representation based on IEC 60512-5-2:2002-02
Reduction factor	0.8
Number of positions	See diagram
Conductor cross section	4 mm ²

Type: PC 4/...-STF-7,62 with DFK-PC 4/...-GF-7,62**Type: PC 5/...-ST...-7,62 with DFK-PC 4/...-GF-7,62**

1840599 DFK-PC 4/ 6-GF-7,62

13 Environmental and durability tests


13.1 Vibration test


Specification	IEC 60068-2-6:1995-03
Result	Test passed
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm (10 - 60.1 Hz)
Acceleration	5 g (60.1 - 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis


14 Classification for connectors

Specification	IEC 61984:2001-06
Main features	Connectors without switching capacity (COC)
Construction form	Fixed connectors
Strain relief elements	without strain relief
Connection method	Can be reconnected
Protection against electric shock	Not encapsulated - touch-proof when inserted
Protective conductor	without PE
Lock	no
Connection method	Screw terminal points

15 Approvals

CSA 				
Use group	B	C		
mm ² /AWG/kcmil	28-10	28-10		
Voltage	300 V	300 V		
Current	20 A	20 A		

UL Recognized 				
Use group	B	C	D	
mm ² /AWG/kcmil	30-10	30-10	30-10	
Voltage	300 V	300 V	600 V	
Current	35 A	35 A	5 A	


cUL Recognized 				
Use group	B	C	D	
mm ² /AWG/kcmil	30-10	30-10	30-10	
Voltage	300 V	300 V	600 V	
Current	35 A	35 A	5 A	

LR 				

EAC 				

1840599 DFK-PC 4/ 6-GF-7,62

DNV GL

cULus Recognized  us

1840599 DFK-PC 4/ 6-GF-7,62**16 Commercial Data**

Order No.	1840599
Type	DFK-PC 4/ 6-GF-7,62
Pieces per package	50
Net weight	24.802 g
GTIN	4017918111748
	Information that applies locally, see link on page 1
Country of origin	Information that applies locally, see link on page 1

17 corresponding headers



Order No.	Type
1828281	PC 4/ 6-STF-7,62
1777875	PC 5/ 6-STF1-7,62
1996168	SPC 5/ 6-STF-7,62
1728248	TSPC 5/ 6-STF-7,62

18 Accessories

Description	Order No.	Type
Screw set, for securing the header to the device wall, consists of an M3 x 10 screw, with a spring washer and a nut	0708263	DFK-MSTB-SS
Coding profile, for plugging into the coding ribs of the plug at a later date, insulating material, color: Red	1701967	CP-PC RD
	0804549	SK 7,62/3,8:FORTL.ZAHLEN
Actuation tool, for ST terminal blocks, insulated, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip	1205053	SZS 0,6X3,5

1840599 DFK-PC 4/ 6-GF-7,62

19 Combination tests

**DFK-PC 4/...-GF**

Specification

Mechanical tests (A)

Insertion/withdrawal force per position

Polarization when inserted
Requirement >20 N**Durability tests (B)**Contact resistance R_1

Insertion/withdrawal cycles

Contact resistance R_2 Rated impulse voltage at sea level
Voltage waveform $\geq (1.2/50 \mu s)$ Power-frequency withstand voltage
Voltage waveform $\geq (50/60 \text{ Hz})$ Insulation resistance
Requirements > 5 M Ω **Thermal tests (C)**

Tested number of positions

Tested conductor cross section

Test current

Upper limiting temperature
Requirements < 100°C**Climatic tests (D)**

Test sequence 1: low temperature storage

Test sequence 2: heat storage

Test sequence 3: noxious gas storage
(ISO 6988)Rated impulse voltage at sea level
Voltage waveform $\geq (1.2/50 \mu s)$ Power-frequency withstand voltage
Voltage waveform $\geq (50/60 \text{ Hz})$ **Environmental and endurance tests (E)**

Specification

Degree of protection

PC 4/...-STF

IEC 61984

approx. 8 N / 6 N

Test passed

0.4 m Ω

25

0.6 m Ω

7.3 kV

3.31 kV

10¹² Ω

12

4 mm²

20 A

Test passed

-40 °C/2 h

100 °C/168 h

KFW 0.2 S/1 cycle

7.3 kV

3.31 kV

IEC 61984:2001-06

Finger safety with IP20
test finger**PC 5/...-STF1**

IEC 61984

approx. 28 N / 11 N

Test passed

0.5 m Ω

25

0.5 m Ω

7.3 kV

3.31 kV

> 1 T Ω

12

6 mm²

20 A

Test passed

-40 °C/2 h

100 °C/168 h

0.2 dm³ SO₂ on 300 dm³/
40 °C/1 cycle

7.3 kV

3.31 kV

IEC 61984:2008-10

Finger safety with IP20
test finger