Clock OSC

SG-310SEF

Product name SG-310SEF 24.000000 MHz L Product Number / Ordering code Q33310F

Q33310FE00252xx

Please refer to the 8.Packing information about xx (last 2 digits)


Output waveform CMOS

Pb free / Complies with EU RoHS directive

Reference	weight	Тур.	26 mg	
-----------	--------	------	-------	--

1.Absolute maximum ratings						
Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions / Remarks
Maximum supply voltage	Vcc-GND	-0.3	-	4.2	V	-
Storage temperature	T_stg	-40	-	125	٥C	Storage as single product
Input voltage	Vin	-0.3	-	Vcc+0.3	V	ST terminal

2.Specifications(characteris	tics)					
Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions / Remarks
Output frequency	fO		24.0000		MHz	
Supply voltage	Vcc	1.6	1.8	2.2	V	-
Operating temperature	T_use	-40	-	85	°C	-
Frequency tolerance	f_tol	-50	-	50	x10 ⁻⁶	T_use
Current consumption	lcc	-	-	2	mA	No load condition
Stand-by current	I_std	-	-	0.7	μA	ST = GND
Symmetry	SYM	40	-	60	%	50% Vcc Level L_CMOS=<15pF
Output voltage	V _{OH}	0.9Vcc	-	-		IOH=-3mA
	V _{OL}	-	-	0.1Vcc		IOL=3mA
Output load condition	L_CMOS	-	-	15	pF	CMOS Load
Input voltage	V _{IH}	0.8Vcc	-	-		ST terminal
	V _{IL}	-	-	0.2Vcc		ST terminal
Rise time	t _r	-	-	4	ns	0.2Vcc to 0.8Vcc Level, L_CMOS=15pF
Fall time	tf	-	-	4	ns	0.2Vcc to 0.8Vcc Level, L_CMOS=15pF
Start-up time	t_str	-	-	10	ms	t = 0 at 0.9Vcc
Jitter	t _{DJ}	-	TBD	-	ps	Deterministic Jitter
	T _{RJ}	-	TBD	-	ps	Random Jitter
	t _{RMS}	-	TBD	-	ps	δ(RMS of total distribution)
	t _{p-p}	-	TBD	-	ps	Peak to Peak
	t _{acc}	-	TBD	-	ps	Accumulated Jitter(δ) n=2 to 50000 cycles
Phase jitter	t _{PJ}	-	TBD	-	ps	Off set Frequency: 12kHz to 20MHz
Phase noise	L(f)	-	TBD	-	dBc/Hz	Off set 1Hz
		-	TBD	-	dBc/Hz	Off set 10Hz
		-	TBD	-	dBc/Hz	Off set 100Hz
		-	TBD	-	dBc/Hz	Off set 1kHz
		-	TBD	-	dBc/Hz	Off set 10kHz
		-	TBD	-	dBc/Hz	Off set 100kHz
		-	TBD	-	dBc/Hz	Off set 1MHz
Frequency aging	f_age	-5	-	5	x10 ⁻⁶	@+25°C first year
		-	-	-		-




(1) Oscilloscope


• Band width should be minimum 5 times higher (wider) than measurement frequency.

· Probe earth should be placed closely from test point and lead length should be as short as possible

- * Recommendable to use miniature socket. (Don't use earth lead.)
- (2) L_CMOS also includes probe capacitance.
- (3) By-pass capacitor (0.01 mF to 0.1 mF) is placed closely between VCC and GND.
- (4) Use the current meter whose internal impedance value is small.
- (5) Power supply
- Start up time (0 %VCC ® 90 %VCC) of power source should be more than 150 ms.
- \cdot Impedance of power supply should be as lowest as possible.

SEIKO EPSON CORPORATION






8.Packing information

[1]Produc	Product number last 2 digits code(xx) description			The recommended code is "00"
	Q33310F	E00252xx		
	Code	Condition	Code	Condition
	01	Any Q'ty vinyl bag(Tape cut)	13	500pcs / Reel
	11	Any Q'ty / Reel	14	1000pcs / Reel
	12	250pcs / Reel	00	2000pcs / Reel

SEIKO EPSON CORPORATION



·	This material is subject to change without notice.
•	Any part of this material may not be reproduced or duplicated in any form or any means without the written permission of Seiko Epson.
•	The information about applied data, circuitry, software, usage, etc. written in this material is intended for reference only.
	Seiko Epson does not assume any liability for the occurrence of customer damage or infringing on any patent or copyright of a third party.
	This material does not authorize the licensing for any patent or intellectual copyrights.
	When exporting the products or technology described in this material, you should comply with the applicable
	export control laws and regulations and follow the procedures required by such laws and regulations.
·	You are requested not to use the products (and any technical information furnished, if any) for the development
	and/or manufacture of weapon of mass destruction or for other military purposes. You are also requested that
	you
	would not make the products available to any third party who may use the products for such prohibited
	purposes. These products are intended for general use in electronic equipment. When using them in specific applications
Ċ	that require
	extremely high reliability, such as the applications stated below, you must obtain permission from Seiko Epson in advance.
	/ Space equipment (artificial satellites, rockets, etc.)
	/ Transportation vehicles and related (automobiles, aircraft, trains, vessels, etc.)
	/ Medical instruments to sustain life
	/ Submarine transmitters
	/ Power stations and related
	/ Fire work equipment and security equipment
	/ Traffic control equipment
	/ And others requiring equivalent reliability.

10.Contact us

http://www5.epsondevice.com/en/contact/