AUTOMOTIVE GRADE

RoHS

COMPLIANT

HALOGEN FREE



Vishay General Semiconductor

High Current Density Surface-Mount Schottky Rectifier



SMB (DO-214AA)



LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS					
I _{F(AV)}	4.0 A				
V _{RRM}	30 V, 40 V				
I _{FSM}	100 A				
V _F	0.38 V, 0.42 V				
T _J max.	150 °C				
Package	SMB (DO-214AA)				
Circuit configuration	Single				

FEATURES

- Low profile package
- · Ideal for automated placement
- · Guardring for overvoltage protection
- Low power losses, high efficiency
- Very low forward voltage drop
- · High surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak 260 °C
- AEC-Q101 qualified available
 - Automotive ordering code: base P/NHE3 or P/NHM3
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

TYPICAL APPLICATIONS

For use in low voltage high frequency inverters, freewheeling, DC/DC converters, and polarity protection applications.

MECHANICAL DATA

Case: SMB (DO-214AA)

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade Base P/N-M3 - halogen-free, RoHS-compliant, commercial grade

Base P/NHE3_X - RoHS-compliant and AEC-Q101 qualified Base P/NHM3_X - halogen-free, RoHS-compliant, and AEC-Q101 qualified

("_X" denotes revision code e.g. A, B,)

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3, M3, HE3, and HM3 suffix meets JESD 201 class 2 whisker test

Polarity: color band denotes cathode end

PARAMETER	SYMBOL	SSB43L	SSB44	UNIT
Device marking code		43L	S44	
Maximum repetitive peak reverse voltage	V _{RRM}	30	40	V
Maximum RMS voltage	V _{RMS}	21	28	V
Maximum DC blocking voltage	V _{DC}	30	40	V
Max. average forward rectified current at T _L (fig. 1)	I _{F(AV)}	4.0		А
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	100		А
Voltage rate of change (rated V _R)	dV/dt	10 000		V/µs
Operating junction temperature range	TJ	-65 to +150		°C
Storage temperature range	T _{STG}	-65 to +150		



www.vishay.com

Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)								
PARAMETER	TEST CONDITIONS		SYMBOL	SSB43L		SSB44		UNIT
PARAMETER				TYP.	MAX.	TYP.	MAX.	UNII
Maximum instantaneous forward voltage (1)	4.0 A	T _J = 25 °C	· //-	0.43	0.45	0.45	0.49	V
	4.0 A	T _J = 125 °C		0.33	0.38	0.37	0.42	
Maximum reverse current at rated V _B (2)		T _J = 25 °C		-	0.6	-	0.4	А
waximum reverse current at rated $v_R \sim$	T,	T _J = 125 °C	I _R	35	45	25	40	mA

Notes

 $^{(1)}\,$ Pulse test: 300 μs pulse width, 1 $\,\%$ duty cycle

(2) Pulse test: Pulse width ≤ 40 ms

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)					
PARAMETER SYMBOL SSB			SSB44	UNIT	
Typical thermal resistance (1)	$R_{\theta JA}$	70		°C/W	
Typical thermal resistance (*)	$R_{\theta JL}$	2	3	C/VV	

Note

(1) Aluminum substrate mounted

ORDERING INFORMATION (Example)						
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE		
SSB43L-E3/52T	0.096	52T	750	7" diameter plastic tape and reel		
SSB43L-E3/5BT	0.096	5BT	3200	13" diameter plastic tape and reel		
SSB43LHE3_A/H (1)	0.096	Н	750	7" diameter plastic tape and reel		
SSB43LHE3_A/I (1)	0.096	I	3200	13" diameter plastic tape and reel		
SSB43L-M3/52T	0.096	52T	750	7" diameter plastic tape and reel		
SSB43L-M3/5BT	0.096	5BT	3200	13" diameter plastic tape and reel		
SSB43LHM3_A/H (1)	0.096	Н	750	7" diameter plastic tape and reel		
SSB43LHM3_A/I (1)	0.096	I	3200	13" diameter plastic tape and reel		

Note

(1) AEC-Q101 qualified



Vishay General Semiconductor

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)





Fig. 1 - Forward Current Derating Curve



SSB43

1000




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current




Fig. 5 - Typical Junction Capacitance




Fig. 3 - Typical Instantaneous Forward Characteristics




Vishay General Semiconductor

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

0.086 (2.20) 0.077 (1.95) 0.180 (4.57) 0.160 (4.06) 0.096 (2.44) 0.084 (2.13) 0.060 (1.52) 0.030 (0.76) 0.220 (5.59)

0.205 (5.21)





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay: