

### **Features**

• Single-Supply Operation from +2.1V ~ +5.5V

• Rail-to-Rail Input / Output

• Gain-Bandwidth Product: 11MHz (Typ)

Low Input Bias Current: 1pA (Typ)

• Low Offset Voltage: 3.5mV (Max)

• High Slew Rate: 9V/μs

• Settling Time to 0.1% with 2V Step: 0.3μs

Low Noise : 8nV/√Hz @10kHz

Quiescent Current: 1.1mA per Amplifier (Typ)

• Operating Temperature: -40°C ~ +125°C

• Small Package:

GS8600 Available in DFN2\*2-8 Package

## **General Description**

The GS8600 have a high gain-bandwidth product of 11MHz, a slew rate of  $9V/\mu s$ , and a quiescent current of 1.1mA per amplifier at 5V. The GS8600 is designed to provide optimal performance in low voltage and low noise systems. They provide rail-to-rail output swing into heavy loads. The input common mode voltage range includes ground, and the maximum input offset voltage is 3.5mV for GS8600. They are specified over the extended industrial temperature range (-40  $^{\circ}$ C to +125  $^{\circ}$ C). The operating range is from 2.1V to 5.5V. The GS8600 dual is available in Green DFN2\*2-8 package.

## **Applications**

- Sensors
- Active Filters
- Cellular and Cordless Phones
- Laptops and PDAs

- Audio
- Handheld Test Equipment
- Battery-Powered Instrumentation
- A/D Converters

## **Pin Configuration**




Figure 1. Pin Assignment Diagram





March 2020-REV\_V0 1/11



## **Absolute Maximum Ratings**

Condition	Min	Max			
Power Supply Voltage (V <sub>DD</sub> to Vss)	-0.5V	+7.5V			
Analog Input Voltage (IN+ or IN-)	Vss-0.5V	V <sub>DD</sub> +0.5V			
PDB Input Voltage	Vss-0.5V	+7V			
Operating Temperature Range	-40°C	+125°C			
Junction Temperature	+16	+160°C			
Storage Temperature Range	-55°C	+150°C			
Lead Temperature (soldering, 10sec)	+26	+260°C			
ESD Susceptibility					
НВМ	8	KV			
MM	40	00V			

**Note:** Stress greater than those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions outside those indicated in the operational sections of this specification are not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

# **Package/Ordering Information**

MODEL	CHANNEL	ORDER NUMBER	PACKAGE DESCRIPTION	PACKAGE OPTION	MARKING INFORMATION
GS8600	Dual	GS8600-FR	DFN2*2-8	Tape and Reel,3000	GS8600







## **Electrical Characteristics**

(At Vs=5V,  $T_A$  = +25  $^{\circ}\text{C}$  ,  $V_{\text{CM}}$  = V<sub>S</sub>/2,  $R_L$  = 600  $^{\Omega}$  , unless otherwise noted.)

		GS8600						
DADAMETED	CONDITIONS	TYP	MIN/MAX OVER TEMPERATURE					
PARAMETER	CONDITIONS	+25℃	+25℃	0℃ to 70℃	-40 ℃ to 85 ℃	-40 ℃ to	UNITS	MIN /
NPUT CHARACTERISTICS		•	•	•				
nput Offset Voltage (V <sub>OS</sub> )		0.8	3.5	3.9	4.3	4.6	mV	MAX
nput Bias Current (I <sub>B</sub> )		1					pA	TYP
nput Offset Current (I <sub>OS</sub> )		1					pA	TYP
nput Common Mode Voltage Range (V <sub>CM</sub> )	V <sub>S</sub> = 5.5V	-0.1 to					V	TYP
		+5.6						
Common Mode Rejection Ratio (CMRR)	$V_S = 5.5V$ , $V_{CM} = -0.1V$ to 4V	82	65	64	64	63	dB	MIN
	$V_S = 5.5V$ , $V_{CM} = -0.1V$ to 5.6V	75					dB	MIN
Open-Loop Voltage Gain (A <sub>OL</sub> )	$R_L = 600\Omega, V_O = 0.15V \text{ to } 4.85V$	90	80	76	75	68	dB	MIN
	$R_L = 10k\Omega, V_O = 0.05V \text{ to } 4.95V$	108					dB	MIN
nput Offset Voltage Drift ( $\Delta V_{OS}/\Delta_T$ )		2.4					μV/°C	TYP
OUTPUT CHARACTERISTICS						•		
Output Voltage Swing from Rail	R <sub>L</sub> = 600Ω	0.1					V	TYP
	$R_L = 10k\Omega$	0.015					V	TYP
Output Current (I <sub>OUT</sub> )		70	55	45	42	38	mA	MIN
Closed-Loop Output Impedance	f = 100kHz, G = 1	7.5					Ω	TYP
POWER SUPPLY								
Operating Voltage Range			2.1	2.1	2.1	2.1	V	MIN
			5.5	5.5	5.5	5.5	V	MAX
Power Supply Rejection Ratio (PSRR)	V <sub>S</sub> = +2.5V to +5.5V							
	$V_{CM} = (-V_S) + 0.5V$	91	74	72	72	68	dB	MIN
Quiescent Current/Amplifier (IQ)	I <sub>OUT</sub> = 0	1.1	1.5	1.65	1.7	1.85	mA	MAX







## **Electrical Characteristics**

(At Vs=5V, T<sub>A</sub> = +25  $^{\circ}\text{C}$  , V<sub>CM</sub> = V<sub>S</sub>/2, R<sub>L</sub> = 600  $^{\Omega}$  , unless otherwise noted.)

	CONDITIONS		GS8600							
PARAMETER		TYP	MIN/MAX OVER TEMPERATURE							
		+25℃	+25℃	0°C to	-40℃ to	-40℃to 125℃	UNITS	MIN /		
		725		<b>70</b> ℃	85℃			MAX		
DYNAMIC PERFORMANCE										
Gain-Bandwidth Product (GBP)	R <sub>L</sub> = 10kΩ, C <sub>L</sub> = 100pF	11					MHz	TYP		
Phase Margin $(\phi_O)$	$R_L = 10k\Omega, C_L = 100pF$	51					Degrees	TYP		
Full Power Bandwidth (BWP)	$<$ 1% distortion, R <sub>L</sub> = 600 $\Omega$	400					kHz	TYP		
Slew Rate (SR)	$G = +1$ , 2V Step, $R_L = 10$ kΩ	9					V/µs	TYP		
Settling Time to 0.1% (t <sub>S</sub> )	G = +1, 2V Step, $R_L$ = 600 $\Omega$	0.3					μs	TYP		
Overload Recovery Time	V <sub>IN</sub> ·Gain = VS, R <sub>L</sub> = 600Ω	1.5					μs	TYP		
NOISE PERFORMANCE	•									
Voltage Noise Density (e <sub>n</sub> )	f = 1kHz	11.5					$nV/\sqrt{Hz}$	TYP		
	f = 10kHz	8					$nV/\sqrt{Hz}$	TYP		








Voltage (1V/div)


## **Typical Performance characteristics**

(At Vs=5V, TA = +25  $^{\circ}$ C, V<sub>CM</sub> = Vs/2, R<sub>L</sub> = 600 $\Omega$ , unless otherwise noted.)

### Large-Signal Step Response




Large-Signal Step Response



Time (1µs/div)

Time (1µs/div)


### Small-Signal Step Response



Voltage (50mV/div)

0


Small-Signal Step Response



Time (1µs/div)


Time (1µs/div)

### Positive Overload Recovery



Time (2µs/div)

## Negative Overload Recovery



Time (2µs/div)




March 2020-REV VO




## **Typical Performance characteristics**


(At Vs=5V, TA = +25 $^{\circ}$ C, VcM = Vs/2, RL = 600 $\Omega$ , unless otherwise noted.)





Output Current(mA)




Temperature (°C)









Frequency (Hz)



## **Application Note**

#### Size

GS8600 opamp are unity-gain stable and suitable for a wide range of general-purpose applications. The small footprints of the GS8600 package save space on printed circuit boards and enable the design of smaller electronic products.

### **Power Supply Bypassing and Board Layout**

GS8600 operate from a single 2.1V to 5.5V supply or dual  $\pm 1.05$ V to  $\pm 2.75$ V supplies. For best performance, a  $0.1\mu$ F ceramic capacitor should be placed close to the  $V_{DD}$  pin in single supply operation. For dual supply operation, both  $V_{DD}$  and  $V_{SS}$  supplies should be bypassed to ground with separate  $0.1\mu$ F ceramic capacitors.

### **Low Supply Current**

The low supply current (typical 1.1mA per channel) of GS8600 will help to maximize battery life. They are ideal for battery powered systems.

### **Operating Voltage**

GS8600 operate under wide input supply voltage (2.1V to 5.5V). In addition, all temperature specifications apply from -40 °C to +125 °C. Most behavior remains unchanged throughout the full operating voltage range. These guarantees ensure operation throughout the single Li-Ion battery lifetime.

### Rail-to-Rail Input

The input common-mode range of GS8600 extends 100mV beyond the supply rails ( $V_{SS}$ -0.1V to  $V_{DD}$ +0.1V). This is achieved by using complementary input stage. For normal operation, inputs should be limited to this range.

### Rail-to-Rail Output

Rail-to-Rail output swing provides maximum possible dynamic range at the output. This is particularly important when operating in low supply voltages. The output voltage of GS8600 can typically swing to less than 2mV from supply rail in light resistive loads (> $100k\Omega$ ), and 15mV of supply rail in moderate resistive loads ( $10k\Omega$ ).

### **Capacitive Load Tolerance**

The GS8600 is optimized for bandwidth and speed, not for driving capacitive loads. Output capacitance will create apole in the amplifier's feedback path, leading to excessive peaking and potential oscillation. If dealing with load capacitance is a requirement of the application, the two strategies to consider are (1) using a small resistor in series with the amplifier's output and the load capacitance and (2) reducing the bandwidth of the amplifier's feedback loop by increasing the overall noise gain. Figure 2. shows a unity gain follower using the series resistor strategy. The resistor isolates the output from the capacitance and, more importantly, creates a zero in the feedback path that compensates for the pole created by the output capacitance.




Figure 2. Indirectly Driving a Capacitive Load Using Isolation Resistor







The bigger the  $R_{ISO}$  resistor value, the more stable  $V_{OUT}$  will be. However, if there is a resistive load  $R_L$  in parallel with the capacitive load, a voltage divider (proportional to  $R_{ISO}/R_L$ ) is formed, this will result in a gain error.

The circuit in Figure 3 is an improvement to the one in Figure 2.  $R_F$  provides the DC accuracy by feed-forward the  $V_{IN}$  to  $R_L$ .  $C_F$  and  $R_{ISO}$  serve to counteract the loss of phase margin by feeding the high frequency component of the output signal back to the amplifier's inverting input, thereby preserving the phase margin in the overall feedback loop. Capacitive drive can be increased by increasing the value of  $C_F$ . This in turn will slow down the pulse response.




Figure 3. Indirectly Driving a Capacitive Load with DC Accuracy





8/11



## **Typical Application Circuits**

### **Differential amplifier**

The differential amplifier allows the subtraction of two input voltages or cancellation of a signal common the two inputs. It is useful as a computational amplifier in making a differential to single-end conversion or in rejecting a common mode signal. Figure 4. shown the differential amplifier using GS8600.




Figure 4. Differential Amplifier

$$V_{\text{OUT}} = (\frac{R_1 + R_2}{R_3 + R_4}) \frac{R_4}{R_1} V_{\text{IN}} - \frac{R_2}{R_1} V_{\text{IP}} + (\frac{R_1 + R_2}{R_3 + R_4}) \frac{R_3}{R_1} V_{\text{REF}}$$

If the resistor ratios are equal (i.e. R<sub>1</sub>=R<sub>3</sub> and R<sub>2</sub>=R<sub>4</sub>), then

$$V_{\text{OUT}} = \frac{R_2}{R_1} (V_{\text{IP}} - V_{\text{IN}}) + V_{\text{REF}}$$

### **Low Pass Active Filter**

The low pass active filter is shown in Figure 5. The DC gain is defined by  $-R_2/R_1$ . The filter has a -20dB/decade roll-off after its corner frequency  $f_C=1/(2\pi R_3C_1)$ .




Figure 5. Low Pass Active Filter







## **Instrumentation Amplifier**

The triple GS8600 can be used to build a three-op-amp instrumentation amplifier as shown in Figure 6. The amplifier in Figure 6 is a high input impedance differential amplifier with gain of  $R_2/R_1$ . The two differential voltage followers assure the high input impedance of the amplifier.




Figure 6. Instrument Amplifier








# **Package Information**


## DFN-8



N5 N8 N8 F1 N1 N1

**Bottom View** 

Top View



Side View

Symbol	Dimensions In Millimeters			Dimensions In Inches			
	Min	Nom	Max	Min	Nom	Max	
Α	0.80	0.85	0.9	0.031	0.033	0.035	
A1	0.00	0.02	0.05	0.000	0.001	0.002	
A2	0.153	0.203	0.253	0.006	0.008	0.010	
b	0.18	0.24	0.30	0.007	0.009	0.012	
D	1.9	2.0	2.1	0.075	0.079	0.083	
Е	1.9	2.0	2.1	0.075	0.079	0.083	
D1	0.5	0.6	0.7	0.020	0.024	0.028	
E1	1.1	1.2	1.3	0.043	0.047	0.051	
е		0.50			0.20		
k	0.2			0.008			
L	0.25	0.35	0.45	0.010	0.014	0.018	