

## **SK78LXX** Three-terminal Positive Regulator


#### **General Description**

SK78LXX is three-terminal positive regulators. One of these regulators can deliver up to 150 mA of output current. The internal limiting and thermal -shutdown features of the regulator make them essentially immune to overload. When used as a replacement for a zener diode-resist or Combination, an effective improvement in output impedance can be obtained, together with lower quiescent current.

#### **Features**

- Output Current of 150mA
- Thermal Overload Protection
- **Short Circuit Protection**
- Output transistor safe area protection
- No external components
- Package: SOT89-3 and TO92
- Output voltage accuracy: tolerance ±5%

#### **Block Diagram**





#### **Ordering Information**

| Part No.  | Output Voltage      | Package | Tape/Reel |  |
|-----------|---------------------|---------|-----------|--|
| SK78LXX   | 5.0,6.0,8.0,9.0,12V | SOT89   | 1000/Reel |  |
| SK78LXXTR | 5.0,6.0,8.0,9.0,12V | TO92    | 1000/Reel |  |

#### **Pin Configuration**

SOT89 (Top View)




Table1: SK78LXX series (SOT89 PKG)

| PIN NO. | PIN NAME | FUNCTION           |
|---------|----------|--------------------|
| 1       | VOUT     | Output voltage pin |
| 2       | GND      | GND pin            |
| 3       | VIN      | Input voltage pin  |

#### TO92 (Top View)




Table3: SK78LXXTR series (TO92 PKG)

| PIN NO. | PIN NAME | FUNCTION           |
|---------|----------|--------------------|
| 1       | VOUT     | Output voltage pin |
| 2       | GND      | GND pin            |
| 3       | VIN      | Input voltage pin  |



#### Absolute Maximum Ratings (Ta=25℃)

| Parameter                       | Rating                | Unit       |
|---------------------------------|-----------------------|------------|
| Input supply voltage: VIN       | 30                    | V          |
| MAX. Output current:lout        | 100                   | mA         |
| MAX Power:Pmax                  | 0.5                   | W          |
| Maximum junction temperature:Tj | -40~125               | °C         |
| Storage temperature:Tstr        | -55~125               | $^{\circ}$ |
| Soldering temperature and time  | +260(Recommended 10S) | $^{\circ}$ |

Note: The absolute maximum ratings are rated values exceeding which the product could suffer physical damage. These values must therefore not be exceeded under any conditions.

#### **Electrical Characteristics**

(Cin=0.33uF, Co=0.1uF, 0≤Tj≤125°C, unless otherwise noted)


| Parameter               | Symbol         | Conditions                       | Min.      | Тур. | Max.      | Unit  |  |
|-------------------------|----------------|----------------------------------|-----------|------|-----------|-------|--|
|                         | Vout           | Io=40mA, VIN=10V                 | 0.964vout | vout | 1.036vout |       |  |
|                         |                | Io=1mA~40mA                      | 0.96vout  | vout | 1.04vout  | V     |  |
| Output Voltage          |                | VIN=7V~18V                       |           |      |           |       |  |
|                         |                | lo=1mA~10mA                      | 0.95vout  | vout | 1.05vout  |       |  |
|                         |                | VIN=10V                          | 0.930001  | vout |           |       |  |
| Line Regulation         | LNR            | VIN=7V~18V, Io=20mA              | -150      | -    | 150       | m\/   |  |
| Line Regulation         | LIVIN          | VIN=8V~18V, Io=20mA              | -100      | -    | 100       | mV    |  |
| Load Regulation         | LDR            | VIN=10V, Io=1mA~100mA            | -100      | -    | 100       | mV    |  |
| Load Regulation         |                | VIN=10V, Io=1mA~40mA             | -30       | -    | 30        |       |  |
| Dropout Voltage         | $V_{DIF}$      | Tj=25℃,lo=100mA                  | -         | 2    | -         | V     |  |
| Output noise<br>Voltage | V <sub>N</sub> | F=10Hz to 100KHz                 | -         | 40   | -         | uV/Vo |  |
| Binala Bainatina        | PSRR           | Tj=25℃,f=120Hz,                  |           | 80   | -         | dB    |  |
| Ripple Rejection        |                | Io=40mA, VIN=8V~20V              | -         |      |           |       |  |
| Quiescent Current       | lα             | VIN=10V, IOUT=40mA               | -         | -    | 5.5       | mA    |  |
| Quiescent Current       | ΔIQ            | VIN=8V~18V, I <sub>0</sub> =20mA | -1.5      | -    | 1.5       | mA    |  |
| Change                  |                | VIN=10V,                         | -0.1      | -    | 0.1       |       |  |
| -                       |                | IOUT=1mA~40mA,                   |           |      |           |       |  |


LNR: Line Regulation. The change in output voltage for a change in the input voltage. The measurement is made under conditions of low dissipation or by using pulse techniques such that the average chip temperature is not significantly affected.


LDR: Load Regulation. The change in output voltage for a change in load current at constant chip temperature.





#### **Typical Performance Characteristics**

















#### **Operation Description**


SK78LXX is designed with Thermal Overload Protection that shuts down the circuit when subjected to an excessive power overload condition, Internal Short Circuit Protection that limits the maximum current the circuit will pass, and Output Transistor Safe-Area Compensation that reduces the output short circuit current as the voltage across the pass transistor is increased. In many low current applications, compensation capacitors are not required. However, it is recommended that the regulator input be bypassed with a capacitor if the regulator is connected to the power supply filter with long wire lengths, or if the output load capacitance is large. An input bypass capacitor should be selected to provide good high frequency characteristics to insure stable operation under all load conditions. A 0.33µFor larger tantalum, mylar, or other capacitor having low internal impedance at high frequencies should be chosen. The bypass capacitor should be mounted with the shortest possible leads directly across the regulator's input terminals. Normally good construction techniques should be used to minimize ground loops and lead resistance drops since the regulator has no external sense lead.

#### **Typical Application**



A common ground is required between the input and the output voltages. The input voltage must remain typically 2.0 V above the output voltage even during the low point on the input ripple voltage.


- Cin is required if regulator is located an appreciable distance from power supply filter.
- Co is not needed for stability; however, it does improve transient response.



The SK78LXX regulator can also be used as a current source when connected as Fig.2. In order to minimize dissipation the SK78LXX is chosen in this application. Resistor R determines the current as


follows: 
$$I_0 = \frac{5V}{R} + I_Q$$








# Package Information 3-pin SOT89 Outline Dimensions




| Combal | Dimensions | In Millimeters | Dimension  | s In Inches |
|--------|------------|----------------|------------|-------------|
| Symbol | Min.       | Max.           | Min.       | Max.        |
| Α      | 1.400      | 1.600          | 0.055      | 0.063       |
| b      | 0.320      | 0.520          | 0.013      | 0.020       |
| b1     | 0.400      | 0.580          | 0.016      | 0.023       |
| С      | 0.350      | 0.440          | 0.014      | 0.017       |
| D      | 4.400      | 4.600          | 0.173      | 0.181       |
| D1     | 1.550      | REF.           | 0.061 REF. |             |
| E      | 2.300      | 2.600          | 0.091      | 0.102       |
| E1     | 3.940      | 4.250          | 0.155      | 0.167       |
| е      | 1.500 TYP. |                | 0.060 TYP. |             |
| e1     | 3.000 TYP. |                | 0.118      | TYP.        |
| L      | 0.900      | 1.200          | 0.035      | 0.047       |



### **3-pin TO92 Outline Dimensions**





| Symbol | Dimensions In Millimeters |        | Dimensions In Inches |       |  |
|--------|---------------------------|--------|----------------------|-------|--|
|        | Min.                      | Max.   | Min.                 | Max.  |  |
| Α      | 3.300                     | 3.700  | 0.130                | 0.146 |  |
| A1     | 1.100                     | 1.400  | 0.043                | 0.055 |  |
| b      | 0.380                     | 0.550  | 0.015                | 0.022 |  |
| С      | 0.360                     | 0.510  | 0.014                | 0.020 |  |
| D      | 4.300                     | 4.700  | 0.169                | 0.185 |  |
| D1     | 3.430                     |        | 0.135                |       |  |
| E      | 4.300                     | 4.700  | 0.169                | 0.185 |  |
| е      | 1.270 TYP.                |        | 0.050 TYP.           |       |  |
| e1     | 2.440                     | 2.640  | 0.096                | 0.104 |  |
| L      | 14.100                    | 14.500 | 0.555                | 0.571 |  |
| Φ      |                           | 1.600  |                      | 0.063 |  |
| h      | 0.000                     | 0.380  | 0.000                | 0.015 |  |