



| Part No            | Pin | A     | B     | C     |
|--------------------|-----|-------|-------|-------|
| WAFER-GH1.25-2PWB  | 2   | 1.25  | 5.75  | 3.75  |
| WAFER-GH1.25-3PWB  | 3   | 2.50  | 7.00  | 5.00  |
| WAFER-GH1.25-4PWB  | 4   | 3.75  | 8.25  | 6.25  |
| WAFER-GH1.25-5PWB  | 5   | 5.00  | 9.50  | 7.50  |
| WAFER-GH1.25-6PWB  | 6   | 6.25  | 10.75 | 8.75  |
| WAFER-GH1.25-7PWB  | 7   | 7.50  | 12.00 | 10.00 |
| WAFER-GH1.25-8PWB  | 8   | 8.75  | 13.25 | 11.25 |
| WAFER-GH1.25-9PWB  | 9   | 10.00 | 14.50 | 12.50 |
| WAFER-GH1.25-10PWB | 10  | 11.25 | 15.75 | 13.75 |
| WAFER-GH1.25-11PWB | 11  | 12.50 | 17.00 | 15.00 |
| WAFER-GH1.25-12PWB | 12  | 13.75 | 18.25 | 16.25 |
| WAFER-GH1.25-13PWB | 13  | 15.00 | 19.50 | 17.50 |
| WAFER-GH1.25-14PWB | 14  | 16.25 | 20.75 | 18.75 |
| WAFER-GH1.25-15PWB | 15  | 17.50 | 22.00 | 20.00 |
| WAFER-GH1.25-16PWB | 16  | 18.75 | 23.25 | 21.25 |

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.25
- 2.Voltage Rating: 125V AC DC
- 3.Current Rating: 1A AC,DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

|                                       |           |   |   |   |
|---------------------------------------|-----------|---|---|---|
| MANUFACTURE DWG                       |           |  |  东莞市讯普电子科技有限公司<br>DongGuan XunPu Electronics Co.,Ltd |   |
| UNLESS OTHERWISE SPECIFIED TOLERANCES |           |   | TITLE:<br>WAFER GH1.25 卧贴带扣   |   |
| DECIMALS:                             | ANGLES:   | PAR   | WAFER-GH1.25-NPWB   |   |
| X.:±0.2                               | X'.:±5°   | DWN   |   |   |
| .X:±0.1                               | X.X':±3°  | CHKD  |   |   |
| .XX:±0.05                             | X.XX':±1° | APVD  |   |   |
| CUSTOMER COPY                         |           | SCALE1:1  | UNIT:MM   |  |
|                                       |           | SIZE:A4   | SHEET:1F1   | REV:A   |