

TACT SWITCH

Operation: SMT/贴片立式 小型 轻触开关 [柄长/操作力可定制]



LTEM NO.: TS-1101E-R□□ (Series)

(L3.50mm×W6.00mm TACT-SWITCH)

表面贴装 SMT

正向操作

精密部品 NICETY

可靠 STABILIZE

適合環保 RoHS




Technical parameter

PROJECT	LEVEL	A[better product]		B[average product]	
Electrical	Contact Rating	0.25A, 24V DC			
	Initial Contact Resistance	50mΩ max.			
Properties	Insulation Resistance	100MΩ min.500V DC	Skey/PD: 100MΩ min.300V DC		
	Withstand Voltage	300V AC for 1 minute	250 V AC for 1 minut		
Durable Performance	There No Load	100,000 Cycles	75,000 Cycles		
	Rated Load	80,000 Cycles	50,000 Cycles		
	Storage temp.	-35℃~+75℃(Operating Temp:)			
	Operating Force	1.6 / 2.6N. (1N.=100gram-force)			
	Heat Rrsistance	IR Reflow:255℃, 5sec. Manual:350℃, 3sec.			

Material declaration		
No.	NAME	Description
① A	嵌件	镀银&H62 黄铜
② B	基座	PA6T (Black)热塑性
③ C	簧片	镀银&不锈钢/SUS304
④ D	盖板	不锈钢 Q235-A
⑤ E	拨柄	PA6T (Black)热塑性





CIRCUIT DIAGRAM



Unit:mm



P.C.B LAYOUT



H
4.3
5.0

