



N-Channel Super Junction Power MOSFET III

General Description

The series of devices use advanced trench gate super junction technology and design to provide excellent R_{DS(ON)} with low gate charge. This super junction MOSFET fits the industry's AC-DC SMPS requirements for PFC, AC/DC power conversion, and industrial power applications.


F	ea	ıtı	ır	20
	60	ILL		-5

- New technology for high voltage device
- ●Low on-resistance and low conduction losses
- Small package
- ●Ultra Low Gate Charge cause lower driving requirements
- ●100% Avalanche Tested
- ROHS compliant

Application

- Power factor correction (PFC)
- Switched mode power supplies(SMPS)
- Uninterruptible Power Supply (UPS)

V _{DS}	700	V
R _{DS(ON)TYP}	680	mΩ
I_D	7	A



Schematic diagram

Package Marking And Ordering Information

Device	Device Package	Marking	
NCE70T680I	TO-251	NCE70T680I	
NCE70T680K	TO-252	NCE70T680K	





TO-251

TO-252

v1.1

Table 1. Absolute Maximum Ratings ($T_c=25^{\circ}C$)

Parameter	Symbol	Value	Unit	
Drain-Source Voltage (VGS=0V)	V _{DS}	700	V	
Gate-Source Voltage (V _{DS} =0V) ,AC (f>1 Hz)	V _{GS}	±30	V	
Continuous Drain Current at Tc=25°C	I _{D (DC)}	7	А	
Continuous Drain Current at Tc=100°C	I _{D (DC)}	4.5	Α	
Pulsed drain current (Note 1)	I _{DM (pluse)}	28	Α	
Maximum Power Dissipation(Tc=25℃)	P _D	60	W	
Derate above 25°C		0.48	W/°C	
Single pulse avalanche energy (Note2)	Eas	101	mJ	
Avalanche current ^(Note 1)	I _{AR}	1.5	Α	
Repetitive Avalanche energy , t_{AR} limited by T_{jmax} (Note 1)	E _{AR}	0.28	mJ	



NCE70T680I, NCE70T680K

Parameter	Symbol	Value	Unit
Drain Source voltage slope, V _{DS} ≤480 V,	dv/dt	50	V/ns
Reverse diode dv/dt, $V_{DS} \leq 480 \text{ V,I}_{SD} < I_{D}$	dv/dt	15	V/ns
Operating Junction and Storage Temperature Range	T_{J}, T_{STG}	-55+150	°C

Table 2. Thermal Characteristic

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case (Maximum)	R_{thJC}	2.08	°C /W
Thermal Resistance, Junction-to-Ambient (Maximum)	R_{thJA}	62	°C /W

Table 3. Electrical Characteristics (TA=25 ℃ unless otherwise noted)

Parameter	Symbol	Condition	Min	Тур	Max	Unit
On/off states	1 -	1				
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V I _D =250μA	700			V
Zero Gate Voltage Drain Current(Tc=25℃)	I _{DSS}	V _{DS} =700V,V _{GS} =0V			1	μA
Zero Gate Voltage Drain Current(Tc=125℃)	I _{DSS}	V _{DS} =700V,V _{GS} =0V			100	μΑ
Gate-Body Leakage Current	I _{GSS}	V _{GS} =±20V,V _{DS} =0V			±100	nA
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} ,I _D =250μA	3		4	V
Drain-Source On-State Resistance	R _{DS(ON)}	V _{GS} =10V, I _D =3.5A		680	760	mΩ
Dynamic Characteristics						
Input Capacitance	C _{lss}	\/ -50\/\/ -0\/		435		pF
Output Capacitance	Coss	V _{DS} =50V,V _{GS} =0V,		28		pF
Reverse Transfer Capacitance	C _{rss}	F=1.0MHz		3.3		pF
Total Gate Charge	Q_g	\/ -400\/ -74		11		nC
Gate-Source Charge	Q_{gs}	V _{DS} =480V,I _D =7A,		3.5		nC
Gate-Drain Charge	Q_{gd}	- V _{GS} =10V		5		nC
Switching times						
Turn-on Delay Time	t _{d(on)}			8.5		nS
Turn-on Rise Time	t _r	V _{DD} =420V,I _D =3.5A,		7		nS
Turn-Off Delay Time	t _{d(off)}	R_G =4.7 Ω , V_{GS} =10 V		59	77	nS
Turn-Off Fall Time	t _f			9.5	16	nS
Source- Drain Diode Characteristics						
Source-drain current(Body Diode)	I _{SD}	T -25°C			7	Α
Pulsed Source-drain current(Body Diode)	I _{SDM}	- T _C =25°C			28	Α
Forward On Voltage	V_{SD}	Tj=25°C,I _{SD} =7A,V _{GS} =0V		0.9	1.2	V
Reverse Recovery Time	t _{rr}			210		nS
Reverse Recovery Charge	Qrr	Tj=25°C,I _F =3.5A,di/dt=100A/μs		0.85		uC
Peak Reverse Recovery Current	I _{rrm}			8		Α

Notes: 1.Repetitive Rating: Pulse width limited by maximum junction temperature

2. Tj=25°C,VDD=50V,VG=10V, R_G=25 Ω





TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS (curves)

Figure 1. Safe operating area




Figure 3. Source-Drain Diode Forward Voltage




Figure 5. Transfer characteristics




Figure 2. Transient Thermal Impedance




Figure 4. Output characteristics





Figure 6. Static drain-source on resistance



v1.1



NCE70T680I, NCE70T680K

Figure 7. R_{DS(ON)} vs Junction Temperature




Figure8. BV_{DSS} vs Junction Temperature




Figure 9. Maximum ID vs Junction Temperature




Figure 10. Capacitance






Figure 11. Gate charge waveforms







Test circuit


1) Gate charge test circuit & Waveform







2) Switch Time Test Circuit:





3) Unclamped Inductive Switching Test Circuit & Waveforms






v1.1



TO-252-2 Package Information




O	Dimensions	In Millimeters	Dimensions In Inches		
Symbol	Min.	Max.	Min.	Max.	
Α	2.20	2.38	0.087	0.094	
A1	0.00	0.10	0.000	0.004	
A2	0.90	1.10	0.035	0.043	
b	0.72	0.85	0.028	0.033	
b1	0.72	0.90	0.028	0.035	
b2	5.13	5.46	0.202	0.215	
С	0.47	0.60	0.019	0.024	
D	6.00	6.20	0.236	0.244	
D1	5.25		0.207		
E	6.50	6.70	0.256	0.264	
E1	4.70		0.185		
e	2.19	2.39	0.086	0.094	
Н	9.80	10.40	0.386	0.409	
L	1.40	1.70	0.055	0.067	
L1	2.9	0 REF	0.114	REF	
L2	0.50	8 BSC	0.020 BSC		
L3	0.90	1.25	0.035	0.049	
L4	0.60	1.00	0.024	0.039	
L5	0.15	0.75	0.006	0.030	
L6	1.8	0.071 REF		REF	
Ф	1.20	1.40	0.047	0.055	
θ	0°	8°	0°	8°	

v1.1



TO-251 Package Information



Symbol	Dimensions	In Millimeters	Dimensions In Inches		
Symbol	Min.	Max.	Min.	Max.	
Α	2.20	2.35	0.087	0.093	
A1	0.90	1.10	0.035	0.043	
b	0.56	0.69	0.022	0.027	
b1	0.77	0.90	0.030	0.035	
b2	5.23	5.43	0.206	0.214	
b3		1.05		0.041	
С	0.46	0.59	0.018	0.023	
c1	0.46	0.59	0.018	0.023	
D	6.00	6.20	0.236	0.244	
D1	5.20		0.205		
Е	6.50	6.70	0.256	0.264	
E1	4.60	5.00	0.181	0.197	
e	2.24	2.34	0.088	0.092	
e1	4.47	4.67	0.176	0.184	
Н	16.18	16.78	0.637	0.661	
L	9.00	9.60	0.354	0.378	
L1	0.95	1.35	0.037	0.053	
L2	0.90	1.25	0.035	0.049	



NCE70T680I, NCE70T680K

ATTENTION:

- Any and all NCE products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your NCE representative nearest you before using any NCE products described or contained herein in such applications.
- NCE assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all NCE products described or contained herein.
- Specifications of any and all NCE products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- NCE Power Semiconductor CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all NCE products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of NCE Power Semiconductor CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. NCE believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the NCE product that you intend to use.
- This catalog provides information as of Mar. 2010. Specifications and information herein are subject to change without notice.