



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
P6		REVISED PER ECO-11-011757	08JUN11	HMR	DR
P7		REVISED PER ECO-17-008806	14FEB2018	RS	DR



- 1 STAMP AMP 12-10* APPROX AS SHOWN
- 2 MAXIMUM LENGTH DOES NOT INCLUDE MANUFACTURING TABS
- 3 TIN PLATE .00254[.000100] MIN THK PER ASTM B545
- 4 BLACK OXIDE PER MIL-F-495
- 5 UL LISTED E13288, 12-10 AWG STRANDED.
- 6 MATERIAL; COPPER PER ASTM B-152 ANNEALED
- 7 FINISH: TIN/LEAD (60/40) PLATE, .000100 MIN THK PER SAE-AMS-P-81728
- 8 CSA CERTIFIED LR7189, 12-10 AWG SOLID OR STRANDED
- 9 NOTE DELETED
- 10 NOTE DELETED
- 11 UL 486 C

TEMP-RANGE	APPROVALS	FINISH	QTY	PACKAGE TYPE	PART NO
170°C[338°F]	5 8	3	50	LOOSE PIECE, BOX	8-34138-2
170°C[338°F]	---	7	500	LOOSE PIECE	34138-3
170°C[338°F]	---	4	500	LOOSE PIECE	34138-1
170°C[338°F]	5 8	3	500	LOOSE PIECE	34138

**AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS**

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: SEE TABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: N/A
FOR ORDER ENTRY	1-800-526-5142	CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: TA BRINKMAN 4-14-93	TE TE Connectivity Ltd.
CHK: DA PATTERSON 4-14-93	
APVD: DA PATTERSON 4-14-93	
NAME: SPLICE, PARALLEL, SOLISTRAND 12-10 AWG	
DIMENSIONS: mm [INCHES]	SIZE: A2
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± -	CAGE CODE: 00779
FINISH: SEE NOTES	DRAWING NO: 34138
MATERIAL: 6	RESTRICTED TO: -
	SCALE: 10:1
	SHEET: 1 of 1
	REV: P7