
KBU8A, KBU8B, KBU8D, KBU8G, KBU8J, KBU8K, KBU8M

Vishay General Semiconductor

Single-Phase Bridge Rectifier



www.vishay.com

| PRIMARY CHARACTERISTICS | | | | | | | |
|--|--|--|--|--|--|--|--|
| Package | KBU | | | | | | |
| I _{F(AV)} | 8 A | | | | | | |
| V _{RRM} | 50 V, 100 V, 200 V, 400 V, 600 V, 800 V, 1000 V | | | | | | |
| I _{FSM} | 300 A | | | | | | |
| I _R | 10 µA | | | | | | |
| V _F at I _F = 8 A | 1.0 V | | | | | | |
| T _J max. | 150 °C | | | | | | |
| Diode variations | In-Line | | | | | | |

FEATURES

- UL recognition, file number E54214
- · Ideal for printed circuit boards
- High surge current capability
- High case dielectric strength of 1500 V_{RMS}
- Solder dip 275 °C max. 10 s, per JESD 22-B106
 CompLiant
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

TYPICAL APPLICATIONS

General purpose use in AC/DC bridge full wave rectification for monitor, TV, printer, SMPS, adapter, audio equipment, and home appliances applications.

MECHANICAL DATA

Case: KBU

Molding compound meets UL 94 V-0 flammability rating Base P/N-E4 - RoHS-compliant, commercial grade

Terminals: Silver plated leads, solderable per J-STD-002 and JESD22-B102

Polarity: As marked on body

Mounting Torque: 10 cm-kg (8.8 inches-lbs) max.

Recommended Torque: 5.7 cm-kg (5 inches-lbs)

| MAXIMUM RATINGS ($T_A = 25 \text{ °C}$ unless otherwise noted) | | | | | | | | | | |
|--|--|-----------------------------------|---------------|-------|-------|-------|-------|-------|-------|------|
| PARAMETER | | SYMBOL | KBU8A | KBU8B | KBU8D | KBU8G | KBU8J | KBU8K | KBU8M | UNIT |
| Maximum repetitive peak reverse voltage | | V _{RRM} | 50 | 100 | 200 | 400 | 600 | 800 | 1000 | V |
| Maximum RMS voltage | | V _{RMS} | 35 | 70 | 140 | 280 | 420 | 560 | 700 | V |
| Maximum DC blocking voltage | | V _{DC} | 50 | 100 | 200 | 400 | 600 | 800 | 1000 | V |
| $\begin{array}{l} \mbox{Maximum average forward} \\ \mbox{rectified output current at} \end{array} & \begin{array}{c} T_{C} = 100 \ ^{\circ}C \ ^{(1)(3)} \\ \\ T_{A} = 40 \ ^{\circ}C \ ^{(2)} \end{array}$ | | I | 8.0 | | | | | | | A |
| | | IF(AV) | 6.0 | | | | | | | |
| Peak forward surge current single sine-wave superimposed on rated load | | I _{FSM} | 300 | | | | | | | А |
| Operating junction and storage temperature range | | T _J , T _{STG} | - 50 to + 150 | | | | | | | °C |

Notes

(1) Recommended mounting position is to bolt down on heatsink with silicone thermal compound for maximum heat transfer with #6 screw

⁽²⁾ Units mounted in free air, no heatsink, PCB at 0.375" (9.5 mm) lead length with 0.5" x 0.5" (12 mm x 12 mm) copper pads

(3) Units mounted on a 3.0" x 3.0" x 0.11" thick (7.5 cm x 7.5 cm x 0.3 cm) aluminum plate heatsink

| ELECTRICAL CHARACTERISTICS ($T_A = 25 \text{ °C}$ unless otherwise noted) | | | | | | | | | | |
|---|-------------------------|----------------|-------|-------|-------|-------|-------|-------|-------|------|
| PARAMETER | TEST CONDITIONS | SYMBOL | KBU8A | KBU8B | KBU8D | KBU8G | KBU8J | KBU8K | KBU8M | UNIT |
| Maximum instantaneous forward drop per diode | I _F = 8.0 A | V _F | 1.0 | | | | | | V | |
| Maximum DC reverse current at rated DC blocking | T _A = 25 °C | | 10 | | | | | | μA | |
| voltage per diode | T _A = 125 °C | I _R | 1.0 | | | | | | mA | |

Revision: 14-May-14 1 Document Number: 88658 For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>





HAY。 KBU8A, KBU8B, KBU8D, KBU8G, KBU8J, KBU8K, KBU8M

www.vishay.com

Vishay General Semiconductor

| THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted) | | | | | | | | | |
|---|---------------------------------|---|--|--|--|--|--|------|------|
| PARAMETER | SYMBOL | SYMBOL KBU8A KBU8B KBU8D KBU8G KBU8J KBU8K KBU8M UNIT | | | | | | | |
| Typical thermal resistance | R _{0JA} ⁽¹⁾ | 18 | | | | | | | °C/W |
| rypical mernal resistance | R _{0JC} ⁽²⁾ | 3.0 | | | | | | 0/10 | |

Notes

(1) Units mounted in free air, no heatsink, PCB at 0.375" (9.5 mm) lead length with 0.5" x 0.5" (12 mm x 12 mm) copper pads

⁽²⁾ Units mounted on a 3.0" x 3.0" x 0.11" thick (7.5 cm x 7.5 cm x 0.3 cm) aluminum plate heatsink

| ORDERING INFORMATION (Example) | | | | | | | | |
|--------------------------------|--|----|-----|----------------------|--|--|--|--|
| PREFERRED P/N | UNIT WEIGHT (g) PREFERRED PACKAGE CODE BASE QUANTITY DELIVERY MODE | | | | | | | |
| KBU8J-E4/51 | 8.0 | 51 | 250 | Anti-static PVC tray | | | | |

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)




Fig. 1 - Derating Curve Output Rectified Current




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current




Fig. 3 - Typical Instantaneous Forward Characteristics Per Diode





Fig. 4 - Typical Reverse Leakage Characteristics Per Diode

Revision: 14-May-14

2

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>







Fig. 5 - Typical Junction Capacitance Per Diode

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)



Case Style KBU



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.