

RS1A, RS1B, RS1D, RS1G, RS1J, RS1K

Vishay General Semiconductor

Surface-Mount Fast Switching Rectifier



Cathode O Anode

LINKS TO ADDITIONAL RESOURCES

3D Models

PRIMARY CHARACTERISTICS						
I _{F(AV)}	1.0 A					
V _{RRM}	50 V, 100 V, 200 V, 400 V, 600 V, 800 V					
I _{FSM}	30 A					
t _{rr}	150 ns, 250 ns, 500 ns					
V _F	1.3 V					
T _J max.	150 °C					
Package	SMA (DO-214AC)					
Circuit configuration	Single					

FEATURES

- Low profile package
- · Ideal for automated placement
- · Glass passivated pellet chip junction
- Fast switching for high efficiency
- High forward surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified available
 Automotive ordering code: base P/NHE3 or P/NHM3
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

TYPICAL APPLICATIONS

For use in fast switching rectification of power supply, inverters, converters, and freewheeling diodes for consumer, automotive and telecommunication.

MECHANICAL DATA

Case: SMA (DO-214AC)

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade

Base P/N-M3 - halogen-free, RoHS-compliant, commercial grade

Base P/NHE3_X - RoHS-compliant and AEC-Q101 qualified Base P/NHM3_X - halogen-free, RoHS-compliant and AEC-Q101 qualified

("_X" denotes revision code e.g. A, B,)

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3, M3, HE3 and HM3 suffix meets JESD 201 class 2 whisker test

Polarity: color band denotes cathode end

MAXIMUM RATINGS ($T_A = 25 \text{ °C}$ unless otherwise noted)								
PARAMETER	SYMBOL	RS1A	RS1B	RS1D	RS1G	RS1J	RS1K	UNIT
Device marking code		RA	RB	RD	RG	RJ	RK	
Maximum repetitive peak reverse voltage	V _{RRM}	50	100	200	400	600	800	V
Maximum RMS voltage	V _{RMS}	35	70	140	280	420	500	V
Maximum DC blocking voltage	V _{DC}	50	100	200	400	600	800	V
Maximum average forward rectified current at $T_L = 90$ °C	I _{F(AV)}	v) 1.0					А	
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	30					А	
Operating junction and storage temperature range	T _J , T _{STG}	-55 to +150					°C	

Revision: 15-Apr-2020

1

Document Number: 88707

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



RoHS COMPLIANT HALOGEN FREE



www.vishay.com

Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)									
PARAMETER	TEST CONDITIONS	SYMBOL	RS1A	RS1B	RS1D	RS1G	RS1J	RS1K	UNIT
Maximum instantaneous forward voltage	1.0 A	V _F	1.3					V	
Maximum DC reverse current at rated DC blocking voltage	T _A = 25 °C T _A = 125 °C	- I _R	5.0 50						μA
Maximum reverse recovery time	$I_F = 0.5 \text{ A}, I_R = 1.0 \text{ A}, I_{rr} = 0.25 \text{ A}$	t _{rr}	150 250 500				500	ns	
Typical junction capacitance	4.0 V, 1 MHz	CJ	10 7.0 pl				pF		

THERMAL CHARACTERISTICS ($T_A = 25 \text{ °C}$ unless otherwise noted)								
PARAMETER	SYMBOL	3OL RS1A RS1B RS1D RS1G RS1J RS1K UNIT						UNIT
Typical thermal resistance	$R_{\theta JA}$ ⁽¹⁾	105						°C/W
Typical mermai resistance	R _{θJL} ⁽¹⁾	32					0/10	

Note

(1) Thermal resistance from junction to ambient and from junction to lead mounted on PCB with 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pad areas

ORDERING INFORMATION (Example)									
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE					
RS1J-E3/61T	0.064	61T	1800	7" diameter plastic tape and reel					
RS1J-E3/5AT	0.064	5AT	7500	13" diameter plastic tape and reel					
RS1JHE3_A/H ⁽¹⁾	0.064	н	1800	7" diameter plastic tape and reel					
RS1JHE3_A/I ⁽¹⁾	0.064	I	7500	13" diameter plastic tape and reel					
RS1J-M3/61T	0.064	61T	1800	7" diameter plastic tape and reel					
RS1J-M3/5AT	0.064	5AT	7500	13" diameter plastic tape and reel					
RS1JHM3_A/H ⁽¹⁾	0.064	Н	1800	7" diameter plastic tape and reel					
RS1JHM3_A/I ⁽¹⁾	0.064	I	7500	13" diameter plastic tape and reel					

Note

(1) AEC-Q101 qualified



Vishay General Semiconductor

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)




Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current





Fig. 3 - Typical Instantaneous Forward Characteristics



Percent of Rated Peak Reverse Voltage (%) Fig. 4 - Typical Reverse Characteristics




Fig. 5 - Typical Junction Capacitance




Fig. 6 - Typical Transient Thermal Impedance

Revision: 15-Apr-2020

3

Document Number: 88707


For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>




RS1A, RS1B, RS1D, RS1G, RS1J, RS1K

Vishay General Semiconductor

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Mounting Pad Layout



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.