

60V, 30μA I_O, Low Dropout Voltage Linear Regulator

General Description

The RT9068 family are high voltage (60V operation), low quiescent current low dropout linear regulators capable of supplying 50mA of output current with a maximum dropout voltage of 300mV. The low quiescent and shutdown currents (30 μ A operating and 2 μ A shutdown) are ideal for use in battery-powered and/or high voltage systems. Ground current is well-controlled in all conditions, including dropout.

The RT9068 family operates with any reasonable output capacitors including $1\mu F$ low-ESR ceramic types and features excellent line and load transient responses. Internal protection circuitry includes reverse-battery protection, current limiting, thermal shutdown, and reverse current protection. Output voltage accuracy is $\pm 2\%$ over the entire line and load range.

These devices are available in 3 fixed-output versions (2.5V, 3.3V, 5V) as well as a version that supports an adjustable output voltage (1.25V to 60V). All versions come in SOP-8 and MSOP-8 packages with an exposed pad for high power dissipation.


Features


- Wide Input Voltage Range: 4.5V to 60V
- Low Quiescent Current : 30μA Operating and 2μA Shutdown
- Low Dropout Voltage: 300mV Maximum at 50mA
- Fixed (2.5V, 3.3V, 5V) and Adjustable (1.25V to 60V)
 Versions
- ±2% Output Tolerance
- Stable with 1μF Output Capacitor (Aluminum, Tantalum or Ceramic)
- Inherent Reverse-Current Protection (No diode needed)
- -60V Reverse-Battery Protection


Applications

- Low Current, High Voltage Regulators
- Battery Powered Applications
- Telecom and Datacom Applications
- Automotive Application


Typical Application Circuit







RT9068 (Adjustable Up to 25V Output)



RT9068 (Adjustable Up to 60V Output)

Copyright ©2017 Richtek Technology Corporation. All rights reserved. RICHTEK is a registered trademark of Richtek Technology Corporation.



Ordering and Marking Information

Part No.	Output Voltage	Package	Marking Information			
RT9068- 25GFP	2.5\/	MSOP-8	09=			
RT9068- 25GSP	2.5V	SOP-8 Exposed Pad-Option 1)	RT906825GSP			
RT9068- 33GFP	3.3V	MSOP-8	0A=			
RT9068- 33GSP	3.30	SOP-8 Exposed Pad-Option 1)	RT906833GSP			
RT9068- 50GFP	EV.	MSOP-8	0B=			
RT9068- 50GSP	5V	SOP-8 Exposed Pad-Option 1)	RT906850GSP			
RT9068 GFP	Adiustable	MSOP-8	08=			
RT9068 GSP	Adjustable	SOP-8 Exposed Pad-Option 1)	RT9068GSP			


Note:

Richtek products are:


- RoHS compliant and compatible with the current requirements of IPC/JEDEC J-STD-020.
- ▶ Suitable for use in SnPb or Pb-free soldering processes.

Pin Configuration


(TOP VIEW)




RT9068-25/33/50 MSOP-8



RT9068 MSOP-8



RT9068-25/33/50 SOP-8






Pin Description

Pin No.					
RT9068- 25/33/50GSP/GFP	RT9068GSP/GFP	Name	Function		
1	1	VOUT	VOUT supplies power to the load. A minimum output capacitor of $1\mu\text{F}$ is required for stable operation.		
2	2	SENSE	Output voltage sense. For applications with $V_{OUT} \leq 25V$, SENSE can be connected to the output voltage to optimize the control loop compensation. For applications with $V_{OUT} > 25V$ (adjustable versions only), SENSE must be left unconnected. Control loop compensation is optimized by adding a feed-forward capacitor in the feedback resistor divider connected to FB (see Adjustable Output Voltage and Compensation section).		
3		NC	No internal connection.		
	3	FB	Feedback input. Connect to the center tap of a resistor divider for setting the output voltage. (Adjustable versions only)		
4		NC	No internal connection.		
5	5	SHDN	Shutdown control input (Active High). Connect SHDN high to disable the output voltage and reduce the IC's quiescent current to $2\mu A$ (typical). Connect SHDN low to enable the output. SHDN is a high-voltage input (also able to withstand reverse voltage) and can be connected directly to a high-voltage input.		
6, 7, 9*	6, 7, 9*	GND	Ground. The exposed pad should be soldered to a large PCB and connected to GND for maximum thermal dissipation.		
8	8	VIN	Power input. Bypass VIN with a $0.18\mu F$ or larger capacitor with adequate voltage rating.		

^{*} exposed pad

Functional Block Diagram



Copyright ©2017 Richtek Technology Corporation. All rights reserved. **RICHTEK** is a registered trademark of Richtek Technology Corporation.



Operation

The RT9068 is a high input-voltage linear regulator specifically designed to minimize external components. The input voltage range is from 4.5V to 60V. The device supplies 50mA of output current with a maximum dropout voltage of 300mV. Its 30μA quiescent and 2μA shutdown currents make it ideal for use in battery-powered applications. Unlike many PNP LDO regulators, ground current does not increase much in dropout conditions.

Output Transistor

The RT9068 includes a built-in PNP output transistor configured for low dropout voltage. The output transistor blocks reverse current if the output voltage is held higher than the input voltage (such as in battery-backup applications) so no additional output blocking diode is needed.

Error Amplifier

The Error Amplifier compares the output feedback voltage from an internal feedback voltage divider (fixed output versions) or FB (adjustable output versions) to an internal reference voltage and controls the PNP output transistor's base current to maintain output voltage regulation. The RT9068's internal dividers are placed between SENSE and GND and have a divider resistance of about $1M\Omega$.

Current Limit Protection

The RT9068 provides a current limit function to prevent damage during output over-load or shorted-circuit conditions. The output current is detected by an internal current-sense transistor.

Over-Temperature Protection

The over temperature protection function will turn off the PNP output transistor when the internal junction temperature exceeds 155°C (typ.). Once the junction temperature cools down by approximately 5°C, the regulator will automatically resume operation.

Reverse-Battery Protection

The RT9068 inputs (VIN and SHDN) can withstand reverse voltages as high as -60V. Both the IC and the load are protected, as long as the load impedance is 500Ω or less. In these conditions, the output voltage is guaranteed to be no more negative than -1V with the maximum negative input voltage. In battery-powered applications, no additional protection against battery reversal is typically needed.

Reverse-Output Protection

The RT9068 protects against current flow to the input (VIN) when the output voltage exceeds VIN. This simplifies battery and capacitive "keep-alive" circuits since they need no additional output blocking diode.

Shutdown Input (8 Pin Versions)

The RT9068 SHDN input is an active-high input that turns off the output transistor and reduces the quiescent current to 2µA typical. Connect SHDN to a voltage below 0.6V for normal operation.



Absolute Maximum Ratings (Note 1)

• VIN to GND	60V to 80V
• SHDN to GND	60V to 80V
• VOUT to GND	40V to 80V
• SENSE to GND	30V to 35V
• VIN to VOUT/SENSE when VIN ≥ VOUT (Normal Operation or Reverse-Battery Condition)	60V to 80V
• VIN to VOUT/SENSE when VOUT ≥ VIN ≥ 0 (Reverse-VOUT Condition)	35V
• FB	0.3V to 10V
• FB Current	6mA to 6mA
 Power Dissipation, P_D @ T_A = 25°C 	
MSOP-8	2.1W
SOP-8	3.26W
Package Thermal Resistance (Note 2)	
MSOP-8, θ_{JA}	47.4°C/W
MSOP-8, θ_{JC}	11.9°C/W
SOP-8, θ_{JA}	30.6°C/W
SOP-8, θ _{JC}	3.4°C/W
• Junction Temperature	150°C
• Lead Temperature (Soldering, 10 sec.)	260°C
Storage Temperature Range	65°C to 150°C
ESD Susceptibility (Note 3)	
HBM (Human Body Model)	2kV

Recommended Operating Conditions (Note 4)

•	U	`	,		
Supply Input Voltage		 		 	- 4.5V to 60V
• Junction Temperature Range		 		 	- −40°C to 125°C
• Ambient Temperature Range		 		 	- −40°C to 85°C

Electrical Characteristics

(4.5V < V_{IN} < 60V, V_{SHDN} = 0V, T_A = 25°C, unless otherwise specified)

Parameter	Symbol Test Conditions		Min	Тур	Max	Unit		
Input Supply								
Operational V _{IN}	V _{IN}	0 < I _{OUT} < 50mA	4.5		60	V		
Quiescent Current	IQ	V _{IN} = 24V, V _{SHDN} = 0V		30	40	μΑ		
Shutdown Current	I _{SHDN}	V _{IN} = 24V, V _{SHDN} = 2.5V, V _{OUT} = 0		2	15	μΑ		
Input Reverse Leakage Current	IV _{INr}	V _{IN} = -60V, V _{OUT} = 0V			0.1	mA		
Output Voltage and Current	Output Voltage and Current							
Output Current Limit	I _{LIM}		120		300	mA		
Line Regulation	ΔV_{LINE}	5.5V < V _{IN} < 60V, I _{OUT} = 50mA		0.5		%		
Load Regulation	ΔV_{LOAD}	0.1mA < I _{OUT} < 50mA		0.7	-	%		

Copyright ©2017 Richtek Technology Corporation. All rights reserved. **RICHTEK** is a registered trademark of Richtek Technology Corporation.




Parameter		Symbol	Test Conditions	Min	Тур	Max	Unit	
FB Regulation Voltage	RT9068	V _{FB}	0 < I _{OUT} < 50mA	1.225	1.25	1.275	٧	
	RT9068-25		0 < I _{OUT} < 50mA	2.45	2.5	2.55		
Output Voltage	RT9068-33	Vout	0 < I _{OUT} < 50mA	3.24	3.3	3.36	V	
	RT9068-50		5.4V < V _{IN} < 60V, 0 < I _{OUT} < 50mA	4.9	5	5.1		
FB Input Bias Current	RT9068	I _{FB}			20	100	nA	
Output Voltage with Reverse Polarity V _{IN}		V _{ROUT}	$V_{IN} = -60V$, $R_L = 500\Omega$			-1	V	
			I _{OUT} = 1mA		15	80		
Dropout Voltage		V_{DROP}	I _{OUT} = 10mA		55	150	mV	
			I _{OUT} = 50mA		150	300		
Power Supply R	ejection Rate	PSRR	f = 1kHz, I _{OUT} = 50mA		60		dB	
Output Noise Vo	oltage	V _{ON}	I _{OUT} = 50mA, f = 10Hz to 100kHz		200		μV _{RMS}	
Shutdown								
Shutdown Outpu	ut Voltage	Voutsd	SHDN = V _{IN}	-	1	100	mV	
SHDN High Threshold		VIH			1.6	2.2	V	
SHDN Low Threshold		V _{IL}		0.6	1.2		V	
SHDN Input Bias Current		la	SHDN = V _{IN}		0.6	1.2	^	
		I _{SHDN}	V _{SHDN} = 0V			0.1	μΑ	
Thermal Protection								
Thermal Shutdown		T _{SD}		145	155	165	°C	


- **Note 1.** Stresses beyond those listed "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions may affect device reliability.
- Note 2. θ_{JA} is measured at T_A = 25°C on a high effective thermal conductivity four-layer test board per JEDEC 51-7. θ_{JC} is measured at the exposed pad of the package.
- Note 3. Devices are ESD sensitive. Handling precaution is recommended.
- Note 4. The device is not guaranteed to function outside its operating conditions.





Typical Operating Characteristics


 $(T_A = 25^{\circ}C, C_{IN} = 0.18\mu F, C_{OUT} = 1\mu F, unless otherwise specified)$


















Copyright ©2017 Richtek Technology Corporation. All rights reserved. RICHTEK is a registered trademark of Richtek Technology Corporation.



















Copyright ©2017 Richtek Technology Corporation. All rights reserved. RICHTEK is a registered trademark of Richtek Technology Corporation.








Copyright ©2017 Richtek Technology Corporation. All rights reserved. RICHTEK is a registered trademark of Richtek Technology Corporation.













Applications Information

The RT9068 is a high input-voltage linear regulator specifically designed to minimize external components. The input voltage range is from 4.5V to 60V. The device supplies 50mA of output current with a maximum dropout voltage of 300mV.

Fixed V_{OUT} Applications

The fixed output versions are equipped with internal resistive dividers to set the output voltage to 2.5V, 3.3V, or 5V, respectively. The total resistance of the each internal feedback divider is about $1M\Omega$ The internal dividers connect between SENSE and GND, with the midpoint connecting to the input of the error amplifier. These versions are all internally compensated.

Adjustable Output Voltage and Compensation RT9068

The adjustable output versions may be set to provide from 1.25V to 60V, using external feedback voltage divider resistors (Figure 1). These included an internal feedforward compensation capacitor, connected between SENSE and FB, which may be used when regulating at output voltages up to 25V. To achieve the correct compensation (together with your external FB divider, use an upper divider resistor (R1) value between $500k\Omega$ and $1M\Omega$. Calculate R2 according to the following formula : R2 = R1 / (V_{OUT} / 1.25V – 1).

For output voltages greater than 25V an external feed-forward capacitor (Figure 2) should be used and SENSE should be left unconnected. Choose a lower divider resistor (R2) at least $10k\Omega$ and calculate R1 according to the following formula : R1 = R2 x (V_{OUT} / 1.25V - 1), Then, calculate the compensation capacitor (C_{COMP}) value according to the following formula : $C_{COMP} = 25\mu s$ / R1.




Figure 1. RT9068 Adjustable Output Up to 25V




Figure 2. RT9068 Adjustable Output Above 25V

Remote-Sense Applications

Since VOUT and SENSE (and FB) are separate pins, it is possible to connect SENSE to the output voltage remotely at the load (as long as the output voltage is 25V or less). FB can also be connected remotely, with SENSE unconnected if the output exceeds 25V. Remote sensing eliminates output voltage errors due to any resistive voltage drop between VOUT and the load. (Voltage drops in the ground connection cannot be compensated.)

Added External NPN for High-Current Applications

Higher output currents and/or increased power dissipation are possible using an external NPN output transistor. VOUT drives the base of the transistor and SENSE and/or FB monitors the actual output voltage, as in normal applications. The fixed-output versions (Figure 3) or adjustable-output version (Figure 4) can be used.

Figure 3 and Figure 4 have no current limit and should be used with care. If a crude current limit is desired, add the two diodes and resistor shown in Figure 5. The approximate current limit is 0.7V/R3. Any small switching diodes can be used and size R3 for the power dissipated in R3, which is typically $0.7V \times 0.7V / R3$.




Figure 3. RT9068-25/33/50 External Transistor Application

ed. RICHTEK is a registered trademark of Richtek Technology Corporation.






Figure 4. RT9068 External Transistor Application




Figure 5. RT9068 External Transistor Application with Current Limit

Component Selection

A low-ESR capacitor such as ceramic type must be connected between VIN and GND with short, wide traces to bypass input noise. RT9068 is designed to work with small input capacitor to reduce the cost from high-voltage low-ESR requirement. To guarantee a minimum $0.1\mu F$ input capacitance, a ceramic $0.18\mu F$ input capacitor with an appropriate voltage rating is recommended.

The RT9068 operates with any reasonable output capacitor including low-ESR ceramic types. Low-ESR aluminum and tantalum capacitor may also be used. A minimum of $1\mu F$ is recommended and much higher values are also acceptable. Connect the output capacitor between VOUT and GND with short, wide traces to keep the circuit stable.

Thermal Considerations

For continuous operation, do not exceed absolute maximum junction temperature. The maximum power dissipation depends on the thermal resistance of the IC package, PCB layout, rate of surrounding airflow, and difference between junction and ambient temperature. The maximum power dissipation can be calculated by the following formula:

$$P_{D(MAX)} = (T_{J(MAX)} - T_A) / \theta_{JA}$$

where $T_{J(MAX)}$ is the maximum junction temperature, T_A is the ambient temperature, and θ_{JA} is the junction to ambient thermal resistance.

For recommended operating condition specifications, the maximum junction temperature is 125°C. The junction to ambient thermal resistance, θ_{JA} , is layout dependent. For MSOP-8 (Exposed Pad) package, the thermal resistance, θ_{JA} , is 47.4°C/W on a standard JEDEC 51-7 four-layer thermal test board. For SOP-8 (Exposed Pad) package, the thermal resistance, θ_{JA} , is 30.6°C/W on a standard JEDEC 51-7 four-layer thermal test board. The maximum power dissipation at T_A = 25°C can be calculated by the following formulas :

 $P_{D(MAX)}$ = (125°C - 25°C) / (47.4°C/W) = 2.1W for MSOP-8 (Exposed Pad) package

$$P_{D(MAX)}$$
 = (125°C - 25°C) / (30.6°C/W) = 3.26W for SOP-8 (Exposed Pad) package

The maximum power dissipation depends on operating ambient temperature for fixed $T_{J(MAX)}$ and thermal resistance, θ_{JA} . The derating curves in Figure 6 allow the designer to see the effect of rising ambient temperature on the maximum power dissipation.




Figure 6. Derating Curve of Maximum Power Dissipation

Layout Consideration





Figure 7. PCB Layout Guide




Outline Dimension



Oh al	Dimensions	n Millimeters	Dimensions In Inches		
Symbol	Min	Max	Min	Max	
Α	0.810	1.100	0.032	0.043	
A1	0.000	0.150	0.000	0.006	
A2	0.750	0.950	0.030	0.037	
b	0.220	0.380	0.009	0.015	
D	2.900	3.100	0.114	0.122	
е	0.6	550	0.0	26	
Е	4.800	5.000	0.189	0.197	
E1	2.900	3.100	0.114	0.122	
L	0.400	0.800	0.016	0.031	
U	1.300	1.700	0.051	0.067	
V	1.500	1.900	0.059	0.075	

8-Lead MSOP (Exposed Pad) Plastic Package





Symbol		Dimensions I	n Millimeters	Dimension	s In Inches
		Min	Max	Min	Max
Α		4.801	5.004	0.189	0.197
В		3.810	4.000	0.150	0.157
С		1.346	1.753	0.053	0.069
D		0.330	0.510	0.013	0.020
F		1.194	1.346	0.047	0.053
Н		0.170	0.254	0.007	0.010
I		0.000	0.152	0.000	0.006
J		5.791	6.200	0.228	0.244
М		0.406	1.270	0.016	0.050
Ontion 1	Χ	2.000	2.300	0.079	0.091
Option 1	Y	2.000	2.300	0.079	0.091
Option 2	Х	2.100	2.500	0.083	0.098
Option 2	Υ	3.000	3.500	0.118	0.138

8-Lead SOP (Exposed Pad) Plastic Package

Richtek Technology Corporation

14F, No. 8, Tai Yuen 1st Street, Chupei City Hsinchu, Taiwan, R.O.C.

Tel: (8863)5526789

Richtek products are sold by description only. Customers should obtain the latest relevant information and data sheets before placing orders and should verify that such information is current and complete. Richtek cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Richtek product. Information furnished by Richtek is believed to be accurate and reliable. However, no responsibility is assumed by Richtek or its subsidiaries for its use; nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Richtek or its subsidiaries.