






N-Channel Enhancement Mode Field Effect Transistor



TO-252



Product Summary

- V_{DS} 60 V
- I_D 50 A
- $R_{DS(ON)}$ (at $V_{GS}=10V$) <15 mohm
- $R_{DS(ON)}$ (at $V_{GS}=4.5V$) <17 mohm
- 100% UIS Tested
- 100% ∇V_{DS} Tested

General Description

- Trench Power MV MOSFET technology
- Excellent package for heat dissipation
- High density cell design for low $R_{DS(ON)}$

Applications

- DC-DC Converters
- Power management functions
- Motor Drive applications

■ Absolute Maximum Ratings ($T_A=25^\circ C$ unless otherwise noted)

Parameter		Symbol	Limit	Unit
Drain-source Voltage		V_{DS}	60	V
Gate-source Voltage		V_{GS}	± 20	V
Drain Current	$T_c=25^\circ C$	I_D	50	A
	$T_c=100^\circ C$		42	
Pulsed Drain Current ^A		I_{DM}	200	A
Total Power Dissipation @ $T_c=25^\circ C$ ^B		P_D	54	W
Total Power Dissipation @ $T_c=100^\circ C$ ^B		P_D	21.6	W
Total Power Dissipation @ $T_A=25^\circ C$ ^C		P_D	6.2	W
Single Pulse Avalanche Energy ^D		E_{AS}	49	mJ
Thermal Resistance Junction-to-Case		$R_{\theta JC}$	2.3	$^\circ C/W$
Thermal Resistance Junction-to-Ambient		$R_{\theta JA}$	20	$^\circ C/W$
Junction and Storage Temperature Range		T_J, T_{STG}	-55~+150	$^\circ C$

■ Ordering Information (Example)

PREFERRED P/N	PACKING CODE	Marking	MINIMUM PACKAGE(pcs)	INNER BOX QUANTITY(pcs)	OUTER CARTON QUANTITY(pcs)	DELIVERY MODE
YJD50N06A	F2	YJD50N06A	2500	/	25000	13" reel



YJD50N06A

■ Electrical Characteristics ($T_J=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Static Parameter						
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{\text{GS}}=0\text{V}, I_{\text{D}}=250\mu\text{A}$	60			V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{\text{DS}}=60\text{V}, V_{\text{GS}}=0\text{V}$			1	μA
Gate-Body Leakage Current	I_{GSS}	$V_{\text{GS}}= \pm 20\text{V}, V_{\text{DS}}=0\text{V}$			± 100	nA
Gate Threshold Voltage	$V_{\text{GS}(\text{th})}$	$V_{\text{DS}}=V_{\text{GS}}, I_{\text{D}}=250\mu\text{A}$	1.0	1.5	2.5	V
Static Drain-Source On-Resistance	$R_{\text{DS}(\text{ON})}$	$V_{\text{GS}}= 10\text{V}, I_{\text{D}}=15\text{A}$		11	15	$\text{m}\Omega$
		$V_{\text{GS}}= 4.5\text{V}, I_{\text{D}}=10\text{A}$		13.5	17	
Diode Forward Voltage	V_{SD}	$I_{\text{S}}=15\text{A}, V_{\text{GS}}=0\text{V}$		0.80	1.2	V
Maximum Body-Diode Continuous Current	I_{S}				50	A
Gate resistance	R_g	$f=1\text{ MHz}, \text{Open drain}$		2.1		Ω
Dynamic Parameters						
Input Capacitance	C_{iss}	$V_{\text{DS}}=30\text{V}, V_{\text{GS}}=0\text{V}, f=1\text{MHz}$		2585		pF
Output Capacitance	C_{oss}			150		
Reverse Transfer Capacitance	C_{rss}			77.5		
Switching Parameters						
Total Gate Charge	$Q_g(10\text{V})$	$V_{\text{GS}}=10\text{V}, V_{\text{DS}}=30\text{V}, I_{\text{D}}=20\text{A}$		51		nC
Total Gate Charge	$Q_g(4.5\text{V})$			24		
Gate-Source Charge	Q_{gs}			9.5		
Gate-Drain Charge	Q_{gd}			10		
Reverse Recovery Charge	Q_{rr}	$I_{\text{F}}=20\text{A}, \text{di/dt}=100\text{A/us}$		17		ns
Reverse Recovery Time	t_{rr}			14		
Turn-on Delay Time	$t_{\text{D(on)}}$			11		
Turn-on Rise Time	t_r	$V_{\text{GS}}=10\text{V}, V_{\text{DD}}=30\text{V}, I_{\text{D}}=20\text{A}$ $R_{\text{GEN}}=3\Omega$		25		ns
Turn-off Delay Time	$t_{\text{D(off)}}$			89		
Turn-off fall Time	t_f			79		

- A. Pulse Test: Pulse Width $\leqslant 300\text{us}$, Duty cycle $\leqslant 2\%$.
- B. The power dissipation P_D is based on $T_{J(\text{MAX})}=150^\circ\text{C}$, using junction-to-case thermal resistance, and is more useful in setting the upper dissipation limit for cases where additional heatsinking is used.
- C. The value of R_{QJA} is measured with the device mounted on 1in2 FR-4 board with 2oz. Copper, in a still air environment with $T_A=25^\circ\text{C}$.
- D. $T_J=25^\circ\text{C}$, $V_{\text{DD}}=55\text{V}$, $V_G=10\text{V}$, $L=0.5\text{mH}$.



■ Typical Performance Characteristics




Figure1. Output Characteristics




Figure2. Transfer Characteristics




Figure3. Capacitance Characteristics




Figure4. Gate Charge




Figure5. Drain-Source on Resistance




Figure6. Drain-Source on Resistance




Figure 7. Safe Operation Area




Figure 8. Drain current vs. Case Temperature





Figure 9. Normalized Maximum Transient Thermal Impedance



■TO-252 Package information



SYMBOL	DIMENSIONS					
	INCHES			Millimeter		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A1	0.000	---	0.008	0.000	---	0.200
A2	0.087	0.091	0.094	2.200	2.300	2.400
A3	0.035	0.039	0.043	0.900	1.000	1.100
b	0.026	0.030	0.034	0.660	0.760	0.860
c	0.018	0.020	0.023	0.460	0.520	0.580
D	0.256	0.260	0.264	6.500	6.600	6.700
D1	0.203	0.209	0.215	5.150	5.300	5.450
D2	0.181	0.189	0.195	4.600	4.800	4.950
E	0.390	0.398	0.406	9.900	10.100	10.300
E1	0.236	0.240	0.244	6.000	6.100	6.200
E2	0.203	0.209	0.215	5.150	5.300	5.450
e	0.0908SC			2.2868SC		
L	0.049	0.059	0.069	1.250	1.500	1.750
L1	0.035	---	0.050	0.900	---	1.270
L2	0.055	----	0.075	1.400	----	1.900
L3	0.240	0.310	0.039	6.000	0.800	1.000
L4	0.114REF			2.900REF		
θ	0*	---	10*	0*	---	10*

NOTE:

- 1.PACKAGE BODY SIZES EXCLUDE MOLD FLASH AND GATE BURRS.
- 2.TOLERANCE 0.1mm UNLESS OTHERWISE SPECIFIED.
- 3.THE PAD LAYOUT IS FOR REFERENCE PURPOSES ONLY.



Disclaimer

The information presented in this document is for reference only. Yangzhou Yangjie Electronic Technology Co., Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), Yangjie or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.

This publication supersedes & replaces all information previously supplied. For additional information, please visit our website <http://www.21yangjie.com>, or consult your nearest Yangjie's sales office for further assistance.