




NOTES: UNLESS OTHERWISE SPECIFIED

1 SEE SHEET 2 FOR KEY ARRANGEMENTS AND COLORS.

2. MATERIAL:

HOUSING: THERMOPLASTIC SEAL: SILICONE RUBBER


- 3. MODIFICATIONS: N/A
- 4. SPECIFICATIONS:
  - 4.1 CURRENT RATING: 7.5 AMPS
  - 4.2 OPERATING TEMPERATURE: -55°C TO +125°C.
  - 4.3 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
  - 4.4 INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 25°C.
  - 4.5 MOISTURE RESISTANCE: IP67 ( MATED CONDITION )
  - 4.6 MATING CYCLE DURABILITY: 100 CYCLES
  - 4.7 RoHS COMPLIANT
- 5. MATING PART: ATM06-12SX\* PLUG. (X = A,B,C,D KEYS; \* = MODIFICATIONS AND COLORS)
- 6. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.




## 7 CONTACT SIZE AND REAR SEAL WIRE RANGE:

| CONTACT | MIN. INSUL           | MAX. INSUL           | TYPICAL     |
|---------|----------------------|----------------------|-------------|
| SIZE    | O.D.                 | O.D.                 | WIRE RANGE  |
| 20      | 1.35 mm<br>(.053 in) | 3.05 mm<br>(.120 in) | 16 - 22 AWG |


|     |     | REVISIONS                            |  |  |  |  |
|-----|-----|--------------------------------------|--|--|--|--|
| REV | ECO | O DESCRIPTION DATE BY APPR           |  |  |  |  |
| А3  |     | RELEASE NEW DWG FORMAT 18/JUN/13 DRP |  |  |  |  |



|                                                        | PART NUMBER |                                           |                                                                                                                                           |          |                                               | ITEM  |                       |                 |       |
|--------------------------------------------------------|-------------|-------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------|----------|-----------------------------------------------|-------|-----------------------|-----------------|-------|
| QUANTITY                                               |             | MATERI                                    |                                                                                                                                           |          |                                               | S LI  | ST                    |                 |       |
| UNLESS OTHERWISE SPECIFIED                             |             | SIGNATURES                                |                                                                                                                                           | DATE     | HAMPHOL                                       |       |                       | I               |       |
| 1) All dimensions a 2) Tolerances are a 1 PL DEC ±0.30 |             | D.PARKS 18/JUN/13                         |                                                                                                                                           |          |                                               |       |                       |                 |       |
| 2 PL DEC ±0.15<br>3 PL DEC ±0.08                       | Angles ±1°  | CHECKED:                                  |                                                                                                                                           |          |                                               | Sin   | e Systems - www.am    | ohenol-sine.com |       |
| 3) Note reference                                      | = X         | ENGINEER:                                 |                                                                                                                                           |          | 44724 Morley Drive Clinton Township, MI 48036 |       |                       |                 |       |
| MATERIAL SPECIFICA                                     | TIONS:      | APPROVAL:                                 |                                                                                                                                           |          |                                               |       | Clinton Township, Ivi | 40030           |       |
|                                                        |             | CUSTOMER:                                 | ,                                                                                                                                         |          | REC                                           | CEPTA | CLE, KEYED, 12        | 2 PIN, ATM S    | ERIES |
| DDOCESS SDECIEICA                                      | TIONS       | THIS DRAWING IS SUPPLINFORMATION ONLY. DE | SIGN FEA                                                                                                                                  | TURES,   |                                               |       |                       | ·               |       |
|                                                        |             | SHOWN HEREON ARE THE THE AMPHENOL CORPOR  | SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL |          | B                                             | C-    | ATM04-1               | 2PX-XXX         | A3    |
|                                                        |             | MANUFACTURING VARIATIONS.                 |                                                                                                                                           | SCALE: N | ONE                                           |       | SHEET 1               | OF 2            |       |








| KEY-A CONFIGURATION |                |  |  |  |
|---------------------|----------------|--|--|--|
| COLOR PART NUMBER   |                |  |  |  |
| * GREY              | ATM04-12PA     |  |  |  |
| BLACK               | ATM04-12PA-BLK |  |  |  |
| GREEN               | ATM04-12PA-GRN |  |  |  |
| BROWN               | ATM04-12PA-BRN |  |  |  |

P/N ATM04-12PB KEY-B CONFIGURATION STANDARD COLOR: BLACK




### NOTE:

AN ASTERISKS (\*) PLACED BEFORE THE COLOR DENOTES THE STANDARD MOLDED COLOR OF THE CONNECTORS SHOWN ABOVE.


OTHER COLORS SHOWN ARE AVAILABLE VIA SPECIAL ORDER.

#### P/N ATM04-12PC KEY-C CONFIGURATION STANDARD COLOR: GREEN



| KEY-C C           | KEY-C CONFIGURATION |  |  |  |  |
|-------------------|---------------------|--|--|--|--|
| COLOR PART NUMBER |                     |  |  |  |  |
| GREY              | ATM04-12PC-GRY      |  |  |  |  |
| BLACK             | ATM04-12PC-BLK      |  |  |  |  |
| * GREEN           | ATM04-12PC          |  |  |  |  |
| BROWN             | ATM04-12PC-BRN      |  |  |  |  |

#### P/N ATM04-12PD KEY-D CONFIGURATION STANDARD COLOR: BROWN



RECEPTACLE, KEYED, 12 PIN, ATM SERIES

ATM04-12PX-XXX

REV: A3 SH:

| *BROWN ATM04-12PD   |                |  |  |  |
|---------------------|----------------|--|--|--|
| GREEN               | ATM04-12PD-GRN |  |  |  |
| BLACK               | ATM04-12PD-BLK |  |  |  |
| GREY                | ATM04-12PD-GRY |  |  |  |
| COLOR               | PART NUMBER    |  |  |  |
| KEY-D CONFIGURATION |                |  |  |  |

|                                                                                                                                 | PART NUMBER |                                                                                                  |                                                | DESCRIPTION                                          |                                                  |       |          |          |             | ITEM     |       |    |     |
|---------------------------------------------------------------------------------------------------------------------------------|-------------|--------------------------------------------------------------------------------------------------|------------------------------------------------|------------------------------------------------------|--------------------------------------------------|-------|----------|----------|-------------|----------|-------|----|-----|
| QUANTITY                                                                                                                        |             | M                                                                                                | ALS LIST                                       |                                                      |                                                  |       |          |          |             |          |       |    |     |
| UNLESS OTHERWISE SPECIFIED  1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30   Fractions ±1/64 |             | SIGNATU                                                                                          |                                                |                                                      |                                                  | · •   | h _      |          |             |          |       |    |     |
|                                                                                                                                 |             |                                                                                                  | SIGNATURES DATE Ampher  N: D.PARKS 18/JUN/13   |                                                      |                                                  |       |          |          | <b>311</b>  | 101      |       |    |     |
| 2 PL DEC ±0.15<br>3 PL DEC ±0.08                                                                                                | Angles ±1°  | CHECKED:                                                                                         |                                                |                                                      |                                                  | Sin   | e Syste  | ms - www | v.amphe     | nol-sine | .com  |    |     |
| 3) Note reference                                                                                                               | = X         | ENGINEER:                                                                                        |                                                |                                                      | 44724 Morley Drive<br>Clinton Township, MI 48036 |       |          |          |             |          |       |    |     |
| **************************************                                                                                          | 710110      | APPROVAL:                                                                                        |                                                |                                                      |                                                  |       | Cilition | i rownsn | ip, ivii 4c | 036      |       |    |     |
| MATERIAL SPECIFICA                                                                                                              | HONS:       | CUSTOMER:                                                                                        |                                                |                                                      | REC                                              | CEPTA | CLE.     | KEYE     | D, 12 F     | PIN, AT  | ΓM S' | ER | IES |
|                                                                                                                                 |             | THIS DRAWING IS SU                                                                               |                                                |                                                      |                                                  |       | ,        |          | ,           | ,        |       |    |     |
| PROCESS SPECIFICA                                                                                                               | TIONS:      | SPECIFICATIONS AN<br>SHOWN HEREON AR<br>THE AMPHENOL COF<br>OF REPRODUCTION<br>DIMENSIONS ARE SU | D PERFOR<br>E THE PRO<br>RPORATIO<br>ARE IMPLI | RMANCE DATA<br>OPERTY OF<br>N. NO RIGHTS<br>IED. ALL | B                                                | C-    | DWG NO:  | ATM0     | 4-12F       | γχ-χγ    | ίX    | F  | A3  |
| NEXT ASS'Y:                                                                                                                     |             | MANUFACTURING VA                                                                                 |                                                | 3.                                                   | SCALE: N                                         | ONE   |          |          |             | SHEET    | 2     | OF | 2   |

# **ATM Series™** - Contact Size 20 Options

| Machined Contacts, Sockets & Pins                         |                                                    |      |       |          |  |  |
|-----------------------------------------------------------|----------------------------------------------------|------|-------|----------|--|--|
| Part Number                                               | Description                                        | Size | AWG   | Туре     |  |  |
| AT60-010-2031                                             | Male Contact - Pin, Gold-plated                    | 20   | 16-18 | Machined |  |  |
| AT62-005-20141                                            | T62-005-20141 Female Contact - Socket, Gold-plated |      |       | Machined |  |  |
| AT60-010-20141                                            | 0-010-20141 Male Contact - Pin, Nickel-plated      |      |       | Machined |  |  |
| AT62-005-2031                                             | Female Contact - Socket, Nickel-plated             | 20   | 16-18 | Machined |  |  |
| AT60-202-2031                                             | Male Contact - Pin, Gold-plated                    | 20   | 20-22 | Machined |  |  |
| AT62-201-2031                                             | Female Contact - Socket, Gold-plated               | 20   | 20-22 | Machined |  |  |
| AT60-202-20141 Male Contact - Pin, Nickel-plated 20 20-22 |                                                    |      |       | Machined |  |  |
| AT62-201-20141                                            | Female Contact - Socket, Nickel-plated             | 20   | 20-22 | Machined |  |  |

|      | Tooling - Machined Contacts |                                                                      |  |  |  |  |
|------|-----------------------------|----------------------------------------------------------------------|--|--|--|--|
| Part | Part Number                 | Description                                                          |  |  |  |  |
|      | CA-5D12                     | Universal Hand Crimp Tool, Size 12/16/20<br>(Machined contacts only) |  |  |  |  |
| 33   | CA-5E12                     | Pneumatic Crimp Tool, Size 12/16/20<br>(Machined contacts only)      |  |  |  |  |

|      | Contact Removal Tools |                                                     |  |  |  |  |
|------|-----------------------|-----------------------------------------------------|--|--|--|--|
| Part | Part Number           | Description                                         |  |  |  |  |
|      | ATRT-100              | Used for removal of contacts for A Series™ products |  |  |  |  |
|      | AT11-240-2005         | Contact Removal Tool, Plastic, Size 20              |  |  |  |  |

|         | Sealing Plugs     |                                                  |  |  |  |  |
|---------|-------------------|--------------------------------------------------|--|--|--|--|
| Part    | Part Number       | Description                                      |  |  |  |  |
|         | AT13-204-2005     | Sealing Plug, Size 20, White                     |  |  |  |  |
|         | AT13-204-2005-SR  | Sealing Plug, Size 20, SR01 Series, Black        |  |  |  |  |
| <u></u> | ATM13-217-2005    | Locking Sealing Plug, Size 20, Grey              |  |  |  |  |
| _       | ATM13-217-2005-SR | Locking Sealing Plug, Size 20, SR01 Series, Blue |  |  |  |  |

| Stamped & Formed Contacts, Sockets & Pins |                                        |    |       |                  |  |  |
|-------------------------------------------|----------------------------------------|----|-------|------------------|--|--|
| Part Number                               | Description                            |    | AWG   | Туре             |  |  |
| AT60-20-0144                              | Male Contact - Pin, Gold-plated        | 20 | 16-22 | Stamped & Formed |  |  |
| AT62-20-0144                              | Female Contact - Socket, Gold-plated   | 20 | 16-22 | Stamped & Formed |  |  |
| AT60-20-0244                              | Male Contact - Socket, Gold-plated     | 20 | 16-22 | Stamped & Formed |  |  |
| AT62-20-0244                              | Female Contact - Socket, Gold-plated   | 20 | 16-22 | Stamped & Formed |  |  |
| AT60-20-0122                              | Male Contact - Pin, Nickel-plated      | 20 | 16-22 | Stamped & Formed |  |  |
| AT62-20-0122                              | Female Contact - Socket, Nickel-plated | 20 | 16-22 | Stamped & Formed |  |  |
| AT60-20-0222                              | Male Contact - Socket, Nickel-plated   | 20 | 16-22 | Stamped & Formed |  |  |
| AT62-20-0222                              | Female Contact - Socket, Nickel-plated | 20 | 16-22 | Stamped & Formed |  |  |
| AT60-20-0277                              | Male Contact - Socket, Tin-plated      | 20 | 16-22 | Stamped & Formed |  |  |
| AT62-20-0277                              | Female Contact - Socket, Tin-plated    | 20 | 16-22 | Stamped & Formed |  |  |
| AT60-20-0422                              | Male Contact - Socket, Nickel-plated   | 20 | 20-22 | Stamped & Formed |  |  |
| AT62-20-0444                              | Female Contact - Socket, Gold-plated   | 20 | 20-22 | Stamped & Formed |  |  |

| Tooling - Stamped & Formed Contacts |             |                                                                |  |  |
|-------------------------------------|-------------|----------------------------------------------------------------|--|--|
| Part                                | Part Number | Description                                                    |  |  |
|                                     | MFX-3974    | Crimp Die - Size 20 (S&F contacts only)                        |  |  |
|                                     | MFX-3976    | Crimp Die - Size 20 (S&F contacts only) 20-22AWG -04XX Series  |  |  |
|                                     | MFX-3978    | Crimp Die - Size 20 (\$&F contacts only) 20-22AWG -02XX Series |  |  |
|                                     | АП-20-00    | Hand Crimp Tool - Size 20, 20AWG (\$&F contacts only)          |  |  |

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 03/2022