



RECOMMENDED FCC/FPC DIM.

**Electrical Characteristics:**  
 Current rating: 0.4A AC/DC  
 Voltage rating: 50V AC/DC  
 Temperature range: -25°C~+85°C  
 Withstand Voltage: 200V AC/Minute  
 Contact Resistance: ≤ 20mΩ  
 Insulation resistance: ≥ 500MΩ  
 Relative Humidity: 93%~40°C

**Material Description:**  
 Terminal: Phosphor Bronze Tin-Leadplated  
 Fitting Nail: Brass Tin-plated  
 Housing: Thermoplastic(U194V-0)  
 Slider: Thermoplastic(U194V-0)  
 Poles: 4~60P

**注**  
 尺寸  
 4PIn~29PIn: 4.70mm  
 30PIn~39PIn: 4.80mm  
 40PIn~60PIn: 4.90mm

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

<b>APPROVED:</b>	<b>DATE:</b>
<b>CHECKED:</b>	<b>DATE:</b>
<b>DRAWN:</b>	<b>DATE:</b>
LYP	2011-01-13

**深圳市灿科盟实业有限公司**  
**SHENZHEN CHANKEMING INDUSTRY CO., LTD**

**标题:**  
 FCC0.5-16P 立贴 带锁 正牌位

<b>PART. NO.</b>	C3025534
<b>UNIT</b>	mm
<b>SCALE</b>	free
<b>FILE NO.</b>	F-FPC0N16P-D310
<b>REV.</b>	B JMK0