



Detail A Scale 5 : 1



PCB PATTERN LAYOUT (GENERAL TOLERANCE:±0.05)

▨ PAD AREA  
 ▩ No trace, no test point, no via hole, no ground area

Pin	Define
P1	DATA2
P2	CD/DATA3
P3	CMD
P4	YHD
P5	CLK
P6	VSS
P7	DATO
P8	DATA1
P9	CD



Specification  
 \*Electrical Characteristics:  
 Contact Current Rating:0.5Amperes.  
 Dielectric Withstanding Voltage:AC500V r.m.s.  
 Insulation Resistance:1000 Megohms  
 Minimum At DC 500V.  
 Contact Resistance:100 mΩ Maximum.  
 \*Mechanical Characteristics:  
 Mating Cycles:10,000 Cycles.  
 \*Environmental:  
 Operating Temperature:-25°C~+85°C.  
 \*Materials:  
 Insulator:HI-Temp plastic (LCP,S475),UL Black 94V-0.  
 Contact:Phosphor Bronze(C5210-EH,T=0.10±0.03mm)  
 Shell:SUS304-1/2H T=0.15±0.03mm  
 \*Plating:  
 Contact: Plated 50u"min Ni Overall  
 Plated 1u"min Au Selective Contact Area  
 Plated 80u"min Sn over Ni on solder area  
 Shell: Plated 50u"min Ni Overall



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: TF PUSH 板上1.5H
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HWCW141-TF09-150B MOLD NO.
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HVC-2206011430 SHEET NO. 1 OF 1