


www.vishay.com

WSL

Vishay Dale

Power Metal Strip[®] Resistors, Low Value (Down to 0.0005 Ω), Surface-Mount



LINKS TO ADDITIONAL RESOURCES







FEATURES

- All welded construction of the Power Metal Strip[®] resistors are ideal for all types of current sensing, voltage division and pulse applications
- Proprietary processing technique produces extremely low resistance values (down to $0.0005~\Omega$)
- Sulfur resistance by construction that is unaffected by high sulfur environments
- Very low inductance 0.5 nH to 5 nH
- Low thermal EMF (< 3 μV/°C)
- AEC-Q200 qualified (1)
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912











Notes

- * This datasheet provides information about parts that are RoHS-compliant and / or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details
- Follow link to Overview of Automotive Grade Products for more details: www.vishay.com/doc?49924
- "SMD Current Sense: AEC-Q200 vs. Vishay Qualification" technical note: www.vishay.com/doc?30416
- (1) Flame retardance test may not be applicable to some resistor technologies

STANDARD ELECTRICAL SPECIFICATIONS							
GLOBAL	SIZE	POWER RATING P _{70 °C}	RESISTANCE VA	WEIGHT (typical)			
MODEL	SIZE	w	TOL. ± 0.5 %	TOL. ± 1.0 %	g/1000 pieces		
WSL0603	0603	0.1	0.01 to 0.1	0.01 to 0.1	1.9		
WSL0805	0805	0.125	0.005 to 0.2	0.005 to 0.2	4.8		
WSL1206	1206	0.25	0.005 to 0.2	0.0005 to 0.2	16.2		
WSL2010	2010	0.5	0.004 to 0.5	0.001 to 0.5	38.9		
WSL2512	2512	1.0 ⁽¹⁾	0.003 to 0.5	0.0005 to 0.5	63.6		
WSL2816	2816	2.0	0.003 to 0.1	0.002 to 0.1	118		

Notes

- · Part marking: value; tolerance: due to resistor size limitations some resistors will be marked with only the resistance value
- "Thermal Management for Surface-Mount Devices" white paper: www.vishay.com/doc?30380
- ⁽¹⁾ For values above 0.1 Ω derate linearly to 80 % rated power at 0.5 Ω
- WSL1206 0.0005 Ω to 0.00099 Ω is only available with 2 % tolerance (G tolerance code)

GLOBAL PART NUMBER INFORMATION Global Part Numbering Example: WSL25124L000FEA (visit www.vishay.net Vishay Dale parts numbering manual for all options) W S 2 O 0 RESISTANCE VALUE (1) **GLOBAL TOLERANCE** PACKAGING CODE (2) SPECIAL (3) MODEL CODE (up to 2 digits) (2 digits) (7 digits) (5 digits) (1 digit) WSL0603 $\mathbf{L} = \mathbf{m}\Omega^*$ $D = \pm 0.5 \%$ EA = lead (Pb)-free, tape / reel (dash number) WSL0805 $F = \pm 1.0 \%$ $J = \pm 5.0 \%$ EH = lead (Pb)-free, tape / reel (WSL2816) from **1 to 99** as R = decimal WSL1206 **5L000** = 0.005 Ω applicable TA = tin / lead, tape / reel (R86) WSL2010 $R0100 = 0.01 \Omega$ TG = tin / lead, tape / reel (RT1, for WSL0603 and WSL0805) TH = tin / lead, tape / reel (RJ9, WSL2816) WSL2512 WSL2816 Use "L" for resistance SB = tin / lead, tape / reel for DLA drawings values < 0.01 Ω

Notes

Revision: 24-Mar-2022

- Per PCN-DR-00009-2022-REV-0, WSL marking will be removed effective March 1st, 2023
- (1) WSL marking (<u>www.vishay.com/doc?30327</u>); WSL decade values (<u>www.vishay.com/doc?30117</u>)
- Packaging code: EB (lead (Pb)-free) and TB (tin / lead) are non-standard packaging codes designating 1000 piece reels. These non-standard packaging codes are identical to our standard EA (lead (Pb)-free) and TA (tin / lead), except that they have a package quantity of 1000 pieces

Follow link for customization capabilities: www.vishay.com/doc?48163



www.vishay.com

WSL


Vishay Dale


TECHNICAL SPECIFICATIONS							
PARAMETER	UNIT	WSL RESISTOR CHARACTERISTICS					
PANAMETER	ONIT	WSL0603 (1)	WSL0805	WSL1206	WSL2010	WSL2512	WSL2816
	ppm/°C	\pm 75 for 50 m Ω to 100 m Ω	\pm 75 for 7 m Ω to 500 m Ω				
Component temperature coefficient (including terminal) (2)		\pm 110 for 10 m Ω to 49 m Ω	\pm 110 for 5 m Ω to 6.9 m Ω				
TCR measured from		-	\pm 150 for 3 m Ω to 4.9 m Ω				
-55 °C to +155 °C		-	\pm 275 for 1 m Ω to 2.9 m Ω				
		-	\pm 400 for 0.5 m Ω to 0.99 m Ω				
Element TCR (3)	ppm/°C	< 20					
Operating temperature range °C -65 to +170		-65 to +170					
Maximum working voltage $^{(4)}$ V $(P \times R)^{1/4}$		^o x <i>R</i>) ^{1/2}					

Notes

- "Temperature Coefficient of Resistance for Current Sensing" white paper: www.vishay.com/doc?30405
- (1) Consult factory for detailed TCR performance across temperature range associated with PCN-DR-00003-2020 for WSL0603. TCR performance is improved for +25 °C to +155 °C
- (2) Component TCR total TCR that includes the TCR effects of the resistor element and the copper terminal
- (3) Element TCR only applies to the alloy used for the resistor element; refer to item 1 in the construction illustration on the following page
- (4) Maximum working voltage the WSL is not voltage sensitive, but is limited by power / energy dissipation and is also not ESD sensitive

DIMENSIONS in inches (millimeters)





Notes

- 3D models available: www.vishav.com/doc?30306
- Surface mount solder profile recommendations: <u>www.vishay.com/doc?31052</u>

MODEL	RESISTANCE RANGE (Ω)	DIMENSIONS				SOLDER PAD DIMENSIONS		
MODEL		L	W	Н	Т	а	b	I
WSL0603 (1)	0.01 to 0.1	0.060 ± 0.010 (1.52 ± 0.254)	0.030 ± 0.010 (0.76 ± 0.254)	0.016 ± 0.005 (0.406 ± 0.127)	0.015 ± 0.010 (0.381 ± 0.254)	0.040 (1.01)	0.040 (1.01)	0.020 (0.50)
WSL0805 (2)	0.005 to 0.2	0.080 ± 0.010 (2.03 ± 0.254)	0.050 ± 0.010 (1.27 ± 0.254)	0.016 ± 0.005 (0.406 ± 0.127)	0.015 ± 0.010 (0.381 ± 0.254)	0.040 (1.02)	0.050 (1.27)	0.020 (0.50)
WSL1206	0.0005 to 0.00099		0.063 ± 0.010 (1.60 ± 0.254)	0.025 ± 0.010 (0.635 ± 0.254)	0.041 ± 0.010 (1.04 ± 0.254)	0.089 (2.26)	0.076 (1.93)	0.023 (0.58)
	0.001 to 0.0019	0.126 ± 0.010 (3.20 ± 0.254)				0.086 (2.18)	0.076 (1.93)	0.029 (0.74)
	0.002 to 0.0059				0.025 ± 0.010 (0.635 ± 0.254)	0.070 (1.78)	0.076 (1.93)	0.061 (1.55)
	0.006 to 0.20				0.020 ± 0.010 (0.508 ± 0.254)	0.065 (1.65)	0.076 (1.93)	0.071 (1.80)
WSL2010	0.001 to 0.0069	0.200 ± 0.010	0.100 ± 0.010 (2.54 ± 0.254)	0.025 ± 0.010 (0.635 ± 0.254)	0.058 ± 0.010 (1.47 ± 0.254)	0.093 (2.36)	0.120 (3.05)	0.055 (1.40)
	0.007 to 0.5	(5.08 ± 0.254)			0.020 ± 0.010 (0.508 ± 0.254)	0.055 (1.40)	0.120 (3.05)	0.130 (3.30)
WSL2512	0.0005 to 0.00099	0.250 ± 0.010 (6.35 ± 0.254)	0.125 ± 0.010 (3.18 ± 0.254)	0.025 ± 0.010 (0.635 ± 0.254)	0.107 ± 0.010 (2.72 ± 0.254)	0.120 (3.05)	0.145 0.083 0.11) 0.065	0.050 (1.27)
	0.001 to 0.0049				0.087 ± 0.010 (2.21 ± 0.254)			
	0.005 to 0.0069				0.047 ± 0.010 (1.19 ± 0.254)	0.083 (2.11)		0.125 (3.18)
	0.007 to 0.5				0.030 ± 0.010 (0.762 ± 0.254)	0.065 (1.65)		0.160 (4.06)
WSL2816	0.002 to 0.00399	0.280 ± 0.010 (7.1 ± 0.254)	0.165 ± 0.010 (4.2 ± 0.254)	0.025 ± 0.010 (0.635 ± 0.254)	0.098 ± 0.010 (2.49 ± 0.254)	0.135 (3.43)	0.185	0.060 (1.52)
	0.004 to 0.1				0.062 ± 0.010 (1.57 ± 0.254)	0.096 (2.45)	(4.7)	0.125 (3.20)

Notes

⁽¹⁾ PCN-DR-00003-2020 changed terminal height for WSL0603 from 0.013" ± 0.005" for clad construction to 0.016" ± 0.005" for welded construction

⁽²⁾ PCN-DR-00021-2021-REV-1 changed terminal height for WSLP0805 from 0.013" ± 0.005" for clad construction to 0.016" ± 0.005" for welded construction




www.vishay.com


WSL

Vishay Dale

DERATING




PULSE CAPABILITY



www.vishay.com/resistors/power-metal-strip-calculator

WELDED CONSTRUCTION



- (1) Resistive element: solid metal nickel-chrome or manganese-copper alloy resistive element with low TCR (< 20 ppm/°C)
- (2) Plated terminal: solid copper, 100 % Sn (100 μ" min.) with 100 % Ni (20 μ" min.) under layer finish
- (3) Terminal / element weld
- 4) Silicone coating with ink print

PERFORMANCE						
TEST	ST CONDITIONS OF TEST					
Thermal shock	-55 °C to +150 °C, 1000 cycles, 15 min at each extreme	± 0.5 % + 0.0005 Ω				
Short time overload	Refer to link for short time overload performance and pulse capability; www.vishay.com/resistors/power-metal-strip-calculator/	± 0.5 % + 0.0005 Ω				
Low temperature operation	-65 °C for 24 h	± 0.5 % + 0.0005 Ω				
High temperature exposure	1000 h at + 170 °C	± 1.0 % + 0.0005 Ω				
Bias humidity	+85 °C, 85 % RH, 10 % bias, 1000 h	± 0.5 % + 0.0005 Ω				
Mechanical shock	100 g's for 6 ms, 5 pulses	± 0.5 % + 0.0005 Ω				
Vibration	Frequency varied 10 Hz to 2000 Hz in 1 min, 3 directions, 12 h	± 0.5 % + 0.0005 Ω				
Load life	1000 h at rated power, + 70 °C, 1.5 h "ON", 0.5 h "OFF"	± 1.0 % + 0.0005 Ω				
Resistance to solder heat	+260 °C solder, 10 s to 12 s dwell, 25 mm/s emergence	± 0.5 % + 0.0005 Ω				
Moisture resistance	MIL-STD-202, method 106, 0 % power, 7a and 7b not required	± 0.5 % + 0.0005 Ω				

PACKAGING (1)							
MODEL	REEL						
	TAPE WIDTH	DIAMETER	PIECES/REEL	CODE			
WSL0603	8 mm / punched paper	178 mm / 7"	5000	EA			
WSL0805	8 mm / punched paper	178 mm / 7"	5000	EA			
WSL1206	8 mm / embossed plastic	178 mm / 7"	4000	EA			
WSL2010	12 mm / embossed plastic	178 mm / 7"	4000	EA			
WSL2512	12 mm / embossed plastic	178 mm / 7"	2000	EA			
WSL2816	12 mm / embossed plastic	178 mm / 7"	2000	EH			

Notes

- Embossed carrier tape per EIA-481
- (1) Additional packaging details at www.vishay.com/doc?20051



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.