
SB260-41 2.0AMPS. SCHOTTKY BARRIER RECTIFIERS

FEATURE

- . High current capability
- . Low forward voltage drop
- . Low power loss, high efficiency
- . High surge capability
- . High temperature soldering guaranteed $260^{\circ}\text{C}/10\text{sec}/0.375"$ lead length at 5 lbs tension

MECHANICAL DATA

- . Terminal: Plated axial leads solderable per MIL-STD 202E, method 208C
- . Case: Molded with UL-94 Class V-0 recognized Flame Retardant Epoxy (free halogen)
- . Polarity: color band denotes cathode
- . Mounting position: any



Dimensions in inches and (millimeters)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	SYM BOL	SB260-41	units
Maximum Recurrent Peak Reverse Voltage	$V_{ m RRM}$	60	V
Maximum RMS Voltage	$V_{ m RMS}$	42	V
Maximum DC blocking Voltage	$V_{ m DC}$	60	V
Maximum Average Forward Rectified Current .375"(9.5mm)lead length at T _L =90°C	I _{F(AV)}	2.0	A
Peak Forward Surge Current 8.3ms single half sine-wave superimposed on rated load (JEDEC method)	$I_{ m FSM}$	50.0	A
Maximum Forward Voltage at 2.0A DC	$V_{ m F}$	0.70	V
Maximum DC Reverse Current @T _A =25°C	7	0.1	
at rated DC blocking voltage @T _A =100°C	$I_{\rm R}$	10.0	mA
Typical Junction Capacitance (Note1)	$C_{ m J}$	90	pF
Typical Thermal Resistance (Note2)	R _(JA)	50	°C/W
Storage Temperature	T _{STG}	-55 to +150	°C
Operating Junction Temperature	$T_{ m J}$	-55 to +150	°C

Note:

- 1. Measured at 1.0 MHz and applied reverse voltage of 4.0Vdc
- 2. Thermal Resistance from Junction to Ambient at 0.375"(9.5mm)lead length, vertical P.C.Board Mounted

RATING AND CHARACTERISTIC CURVES (SB260-41)

