

N-Ch MOSFET

General Description

Features

Low RDS(on) & FOM

Extremely low switching loss

The WSD40120DN use advanced SGT MOSFET technology to provide low RDS(ON), low gate charge, fast switching and excellent avalanche characteristics.

This device is specially designed to get better ruggedness and suitable to use in

Excellent stability and uniformity or Invertors


Product Summery

BVDSS	RDSON	ID
40V	2.5mΩ	110A

Applications

- Consumer electronic power supply
- Synchronous-rectification
- Synchronous-rectification applications

DFN5X6-8 Pin Configuration



Absolute Maximum Ratings at Tj=25 °C unless otherwise noted

Symbol	Parameter	Rating	Units	
V _{DS}	Drain-Source Voltage	40	V	
V _{GS}	Gate-Source Voltage	±20	V	
I₀@T₀=25℃	Continuous Drain Current, V _{GS} @ 10V ¹	110	A	
I _D @T _C =100℃	Continuous Drain Current, V _{GS} @ 10V ¹	71	A	
I _{DM}	Pulsed Drain Current ²	240	A	
EAS	Single Pulse Avalanche Energy ³	145	mJ	
I _{AS}	Avalanche Current	54	A	
P₀@T₀=25℃	Total Power Dissipation ⁴	36	W	
T _{STG}	Storage Temperature Range -55 to		°C	
TJ	Operating Junction Temperature Range	-55 to 150	°C	

Thermal Data

Symbol	Parameter	Тур.	Max.	Unit
R _{θJA}	Thermal Resistance Junction-Ambient ¹		55	°C/W
R _{θJC}	Thermal Resistance Junction-Case ¹		3.4	°C/W



N-Ch MOSFET

Electrical Characteristics (T_J=25⁻¹C, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V , I _D =250uA	40			V
$\triangle BV_{DSS} / \triangle T_J$	BV _{DSS} Temperature Coefficient	Reference to 25 $^\circ\!\mathrm{C}$, I_D=1mA		0.043		V/℃
R _{DS(ON)}	Static Drain-Source On-Resistance ²	V _{GS} =10V , I _D =20A		2.5	3.5	mΩ
R _{DS(ON)}	Static Drain-Source On-Resistance ²	V _{GS} =4.5V , I _D =15A		3.5	4.5	mΩ
V _{GS(th)}	Gate Threshold Voltage		1.1	1.5	2.3	V
$ riangle V_{GS(th)}$	V _{GS(th)} Temperature Coefficient	V _{GS} -V _{DS} , I _D -2500A		-6.94		mV/℃
la se	I _{DSS} Drain-Source Leakage Current	$V_{\text{DS}}\text{=}32\text{V}$, $V_{\text{GS}}\text{=}0\text{V}$, $T_{\text{J}}\text{=}25^\circ\!\mathrm{C}$			1	
DSS		$V_{\text{DS}}\text{=}32\text{V}$, $V_{\text{GS}}\text{=}0\text{V}$, $T_{\text{J}}\text{=}55^\circ\!\text{C}$			5	uA
I _{GSS}	Gate-Source Leakage Current	V_{GS} = $\pm20V$, V_{DS} = $0V$			±100	nA
gfs	Forward Transconductance	V _{DS} =5V , I _D =20A		75		S
R _g	Gate Resistance	V_{DS} =0V , V_{GS} =0V , f=1MHz		1.5		Ω
Qg	Total Gate Charge (10V)	V _{DS} =20V , V _{GS} =4.5V , I _D =20A		23		
Q _{gs}	Gate-Source Charge			7.5		nC
Q _{gd}	Gate-Drain Charge			5.5		
T _{d(on)}	Turn-On Delay Time			10		
Tr	Rise Time	V _{DD} =20V , V _{GEN} =10V , R _G =3.0		5		
T _{d(off)}	Turn-Off Delay Time	Ω, I _D =20A .		33		- ns -
T _f	Fall Time			6.5		
C _{iss}	Input Capacitance	V _{DS} =20V , V _{GS} =0V , f=1MHz		2810		
C _{oss}	Output Capacitance			850		pF
C _{rss}	Reverse Transfer Capacitance			85		

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
I _S	Continuous Source Current	$V_G = V_D = 0V$, Force Current			30	А
V _{SD}	Diode Forward Voltage ²	V _{GS} =0V , I _S =1A , T _J =25℃			1.2	V

Note :

1. The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.

2 .The data tested by pulsed , pulse width \leq 300us , duty cycle \leq 2%

3. The EAS data shows Max. rating . The test condition is VDD=20V,VGS=10V,L=0.5mH,IAS=54A 4. The power dissipation is limited by 150°C junction temperature

5 .The data is theoretically the same as ID and IDM , in real applications , should be limited by total power dissipation.



WSD40110DN56G

N-Ch MOSFET

Typical Characteristics




Fig.1 Typical Output Characteristics




Fig.3 Source Drain Forward Characteristics




Fig.5 Normalized V_{GS(th)} vs T_J




Fig.2 On-Resistance vs G-S Voltage




Fig.4 Gate-Charge Characteristics




Fig.6 Normalized RDSON vs TJ

WSD40110DN56G



N-Ch MOSFET




Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform




Fig.11 Unclamped Inductive Switching Wave



Attention

1, Any and all Winsok power products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your Winsok power representative nearest you before using any Winsok power products described or contained herein in such applications.

2, Winsok power assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all Winsok power products described or contained herein.

3, Specifications of any and all Winsok power products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

4, Winsok power Semiconductor CO., LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

5, In the event that any or all Winsok power products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

6, No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of Winsok power Semiconductor CO., LTD.

7, Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. Winsok power believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

8, Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the Winsok power product that you Intend to use.

9, this catalog provides information as of Sep.2014. Specifications and information herein are subject to change without notice.