

承 认 书 DATA SHEET

Customer name:	深圳市金鹏辉科技有限公司				
BERYL SERIES:	BC	TYPE:	RADIAL		
DESCRIPTION:	220 μ F/25V Φ 6.3*8	L			
Apply date :	2019-10-9				

	BERYL		CUSTOMER			
P/N:	- 17		P/N:			
PREPARED	CHECKED	APPROVAL	PREPARED	CHECKED	APPROVAL	
王丽	工程就建明	伍小军				

Zhao Qing Beryl Electronic Technology Co., Ltd.

TEL: (0758) 2862871 FAX: (0758) 2862870

E-mail: master@zq-beryl.com http://www.zq-beryl.com

NO.8 DUANZHOU ROAD, ZHAOQING CITY. GUANGDONG. CHINA

After the product certification, please sign a copy, if you do not sign the acknowledgment before the formal order, it is considered that the user has defaulted our relevant standards and technical indicators.

Sheet NO.: 20191009A Page : 1 / 13



Revise record

NO.	Date	Revise reason	Revise content	Issue
01	2019.10.9			First issue

Sheet NO.: 20191009A Page : 2 / 13



1, Application

This specification applies to Aluminum electrolytic capacitor (foil type) used in electronic equipment. Designed capacitor's quality meets IEC 60384.

2. Table of specification and characteristics

Series Cap(uF) 120Hz/20℃		WV(V) Size		Temper		Life(hours)		
ВС	BC 220		25	6.3*8		6.3*8 -55-105℃		2000
DF (%)(MAX) 120Hz/20℃		LC(µA)(2min/			R(mΩ)(MAX) 00KHz/20℃	RC (mAr (MAX)100		Surge voltage(V)
12		11	00		30	1490		28.8


Other:

Frequency Multipliers:

- requestion rive	respires se				
频率 Frequency(Hz)	60Hz	120HZ≪f < 1KHZ	1KHZ≤f < 10KHZ	10KHZ≤f < 100KHZ	100KHZ≪f < 500KHZ
系数Coefficient	0.04	0.05	0.30	0.70	1.00

3. Product Dimensions

Standard Type




ΦD	L	Фф	Р	
6.3±0.5	8±1.0	0.5±0.05	2.5±0.5	


Sheet NO.: 20191009A Page : 3 / 13



4. Part Number



5. Construction




Material name	Composition	Supplier name
Lead	Al and (Fe+Cu+Sn)	Nan Ming(Quan Yong)、Jin Lian fu
Rubber	EPT / IIR	Lian An 、Lian Hua Xin
Case	Aluminum+Coating	Yi Peng、Ao Xing
Paper	Wood / Fibrous plant materials	KAN. NKK
Anode foil	$Al + Al_2O_3$	KDK、Heng Yang、JCC
Cathode foil	Aluminum	JCC、TOYO、Na Nuo
Dielectrics	Poly3,4-Ethylene Dioxy Thiophene	BERYL

Sheet NO.: 20191009A Page : 4 / 13



6. Product Marking



Marking Details:

Capacitor shall be marked the following items:

- 1) Trademark (BERYL)
- 2) working voltage
- 3) Nominal capacitance
- 4) Cathode marked
- 5) Series
- 6) Date code

19: Manufactured year 2019

Code	9	0	1	2	3	4	5	6	
Year	2019	2020	2021	2022	2023	2024	2025	2026	

16: Manufactured week (01, 02, 03, 04......51, 52)

Sheet NO.: 20191009A

Page : 5 / 13



7. Characteristics

Standard atmospheric conditions

Unless other specified, the standard range of atmospheric conditions for making measurements and tests is as follows:

Ambient temperature: 15°C to 35°C
Relative humidity: 45% to 85%
Air pressure: 86kPa to 106kPa

If there is any doubt about the results, measurement shall be made within the following conditions:

Ambient temperature : $20^{\circ}\text{C} \pm 2^{\circ}\text{C}$ Relative humidity : 60% to 70%Air pressure : 86kPa to 106kPa

Operating temperature range

The ambient temperature range at which the capacitor can be operated continuously at rated voltage is -55°C to +105°C.

Table

ITEM		PERFORMANCE				
1	Nominal capacitance (Tolerance)	Condition> Measuring Frequency: 120Hz±12Hz Measuring Voltage: Not more than 0.5Vrms +1.5~2.0V.DC Measuring Temperature: 20±2°C Criteria> Shall be within the specified capacitance tolerance.				
2	Leakage current	Condition> Connecting the capacitor with a protective resistor $(1kΩ±10Ω)$ in series for 2 minutes, and then, measure leakage current. Criteria> I: Leakage current (μA) I (μA) ≤ 0.2CVor280 (μA) whichever is greater, measurement circuit refer to right drawing. C: Capacitance (μF) V: Rated DC working voltage (V)				
3	Dissipation factor	<condition> Nominal capacitance, for measuring frequency, voltage and temperature. <criteria> Must be within the parameters (See page 3)</criteria></condition>				

Sheet NO.: 20191009A Page : 6 / 13



	ITEM	PERFORMANCE						
4	Equivalent Series Resistance	Condition> Measuring frequency:100kHz; Measuring temperature:20±2°C Measuring point: 2mm max. from the surface of a sealing rubber on the lead wire. Criteria> (20°C) Must be within the parameters (See page 3)						
5	Load life test	According to IEC60384-4No. 4.13 methods, the capacitor is stored at a temperature of Maximum operating temperature ±2°C with DC bias voltage for Rated life +48/0hour Then the product should be tested after 16 hours recovering time at atmospheric conditions. The result should meet the following table <criteria> The characteristic shall meet the following requirements. Leakage current Not more than the specified value. Capacitance Change Within ±20% of initial value. Dissipation Factor Not more than 150% of the specified value. Equivalent Series Resistance Not more than 150% of the specified value. Appearance There shall be no leakage of electrolyte.</criteria>						
6	Shelf life test	temperature±2°C for1000+48, from the test chamber and be leakage current <criteria></criteria>	Condition> The capacitors are then stored with no voltage applied at a temperature of Maximum operating temperature±2°C for1000+48/0 hours. Following this period, the capacitors shall be removed from the test chamber and be allowed to stabilized at room temperature for16 hours. measure leakage current Criteria> The characteristic shall meet the following requirements. Leakage current Not more than the specified value Capacitance Change Within ±20% of initial value. Dissipation Factor Not more than 150%of the specified value.					
7	Terminal strength	Condition> Tensile strength of terminals Fixed the capacitor, applied force to the terminal in lead out direction for30+5-0 seconds. Bending strength of terminals. Fixed the capacitor, applied force to bent the terminal (1~4 mm from the rubber) for 90° with 2~3 seconds, and then bent it for 90° to its original position within 2~3 seconds. Diameter of lead wire						

Sheet NO.: 20191009A Page : 7 / 13



	ITEM	PERFORMANCE							
		<condition></condition>				_			
		STEP	Testing temperature (°	C)	Time				
		1	20±2	Tin	ne to reach thermal equilibrium				
		2	(-55)-25±3	Tin	ne to reach thermal equilibrium				
		3	20±2	Tin	ne to reach thermal equilibrium				
		4	105±2	Tin	ne to reach thermal equilibrium				
		5	20±2	Tin	ne to reach thermal equilibrium				
8	Temperatur e characterist ics	a. At +105 Dissipa The lea b. In step Dissipa The lea c. At-55°C/Z	tion factor shall be within kage current measured shapes to capacitance measured at tion factor shall be within kage current measured shapes $\mathbb{C}/(20^{\circ}\mathbb{C})$, Impedance (Z) $\mathbb{Z}+20^{\circ}\mathbb{C}$ ≤ 1.26	the specifiall be with $t+20^{\circ}$ C so the specifiall be with the specifiall be with ratio shall	shall be within ±25% of its originated value in the specified value. nall be within ±10% of its originated value	l value.			
9	Surge test	Appli series for 30± 1000 times. The fore measure CR: Nomin Criteria Leakage control Capacitant Dissipation Appearant Attention: This test so	Leakage currentNot more than the specified value.Capacitance ChangeWithin ±15% of initial value.Dissipation FactorNot more than the specified value.AppearanceThere shall be no leakage of electrolyte.						

Sheet NO.: 20191009A Page : 8 / 13



	ITEM			PERFORMAN	NCE			
		<cond Tem Acc acco</cond 	, the condition					
			Ten	nperature	Time			
			(1) +20°C		3 Minutes			
10	Change of		(2) Rated low temperatu	ire (- 55°C) (-25°C)	30±2 Minutes			
10	temperature test		(3) Rated high temperat	ure (+105°C)	30±2 Minutes			
			(1) to (3) =1 cycle, total	5 cycle				
		<crite td="" the<=""><td>ria> characteristic shall meet t Leakage current</td><td>he following requirement Not more than the s</td><td></td><th></th></crite>	ria> characteristic shall meet t Leakage current	he following requirement Not more than the s				
			Dissipation Factor	Not more than the s	pecified value.			
			Appearance	There shall be no le	akage of electrolyte.			
11	Damp heat test	Humidity test: According to IEC60384-4 No.4.12 methods, capacitor shall be exposed for 500±8 hours in an atmosphere of 90~95%R H .at 40±2°C, the characteristic change shall meet the following requirement. Criteria> Leakage current Not more than the specified value. Capacitance Change Within ±10% of initial value. Dissipation Factor Not more than 150% of the specified value. Appearance There shall be no leakage of electrolyte.						
12	Solderabilit y test	The Solo Dipp Dipp Dipp	Condition> The capacitor shall be tested under the following conditions: Soldering temperature : 245 ±5°C Dipping depth : 2mm Dipping speed : 25±2.5mm/s Dipping time : 3±0.5s Criteria> Soldering wetting time Less than 3s Coating quality A minimum of 95% of the surface being immersed					

Sheet NO.: 20191009A Page : 9 / 13



ITEM		PERFORMANCE				
13	Vibration test	Condition> The following conditions shall be applied for 2 hours in each 3 mutually perpendicular directions. Vibration frequency range: 10Hz ~ 55Hz each to peak amplitude: 1.5mm Sweep rate: 10Hz ~ 55Hz ~ 10Hz in about 1 minute Mounting method: The capacitor with diameter greater than 12.5mm or longer than 25mm must be fixed in place with a bracket. Within 30°				
		Appearance o	To be soldered tems shall be tested: To intermittent contacts, open or short circuiting. To damage of tab terminals or electrodes. To mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible.			
	Resistance to solder heat test	Condition> Terminals of the capacitor shall be immersed into solder bath at 260±5°C for10±1seconds or400±10°C for3 ⁻⁰ seconds to 1.5~2.0 mm from the body of capacitor. Then the capacitor shall be left under the normal temperature and normal humidity for 1~2 hours before measurement. Criteria>				
14		Leakage current	Not more than the specified value.			
		Capacitance Change	Within ±5% of initial value.			
		Dissipation Factor	Not more than the specified value.			
		Appearance	There shall be no leakage of electrolyte.			

Sheet NO.: 20191009A Page : 10 / 13




8. Packing Information


Packing Label Marked (the following items shall be marked on the label) (Inside box or bag)

(1)Clint order number (2)Client part number (3)Beryl part number (4)Capacitance (5)Voltage (6)Dimension (7)Packaging quantity (8)Capacitance tolerance (9) QC Marking (0) Lot number (1) Series

LOT Number:




1) Bulk Packing:



3) Outer box



2) Taped Packing:



4) Outer box label:

BERYL	Zhao Qin	g Beryl Ele Ltd.	ctronic	Technology Co.,
C.S.R:				- 110 115
C.S.R P/O:			ROHS HE	
C.S.R P/N	l:			
S.P.R P/N:				QC
SPEC:				
QTY:	PCS	TOL:	%	
L/N:		S.P.R:		8

Sheet NO.: 20191009A Page : 11 / 13



9. Prohibition to Use Environment- related Substances

We are hereby to certify the followings:

Our company hereby warrants and guarantees that all or part of products, including, but not limited to, the peripherals, accessories or package, delivered to your company (including your subsidiaries and affiliated companies) directly or indirectly by our company are free from any of the substances listed below.

The latest version of <Substances Prohibited as per ROHS or <Sony-SS-00259>

	Cadmium and cadmium compounds				
Accord with	Lead and lead compounds				
heavy metal	Mercury and mercury compounds				
	Hexavalent chromium compounds				
	Polychlorinated biphenyls (PCB)				
Organia ablaria	Polychlorinated naphthalenes (PCN)				
Organic chlorin	Polychlorinated terphenyls (PCT)				
compounds	Chlorinated paraffins (CP)				
	Other chlorinated organic compounds				
Organic Polybrominated biphenyls (PBB)					
bromine Polybrominated diphenylethers (PBDE)					
compounds	Other brominated organic compounds				
Tributyltin compo	Tributyltin compounds				
Triphenyltin compounds					
Asbestos					
Specific azo compounds					
Formaldehyde					
Polyvinyl chloride (PVC) and PVC blends					
F、Cl、Br、I					
REACH					

Sheet NO.: 20191009A Page : 12 / 13



Test Report

Series	ВС	_ Spec.	220uF/25V	Size(mm)	6.3*8
Cap tolerance	±20%	Work temperature	105℃	Color of Tube	Blue lettering
Test date	2019-10-8	_ Test humidity	54%	Test temperature	32.8 ℃

Items	Cap (µF)	D.F (%)	L.C (μA)	ESR (mΩ)	Appearance
NO.	176~264 (120Hz)	≤ 12 (120Hz)	≤ 1100 (2min)	≤30 (100KHz)	OK
1	228.3	3.86	13	11.24	ОК
2	233.4	3.03	7	10.56	ОК
3	234.3	3.61	18	11.20	ОК
4	228.6	3.89	11	10.91	ОК
5	231.4	3.91	8	11.85	OK
6	234.1	3.65	14	11.13	OK
7	228.0	3.77	6	11.40	OK
8	234.6	3.51	39	10.45	OK
9	233.1	3.60	10	11.12	OK
10	231.7	3.71	5	10.74	OK
Opinion					
Approve: 伍小军		Audit: 邹廷	建 明	Test: 唐积君	

Sheet NO.: 20191009A Page : 13 / 13