

# **Positive Thermal Coefficent Diodes**

#### Features:

♦ RoHS Compliant & Halogen Free

♦ faster tripping, 1812 Dimension, Surface mountable, Solid state

♦ Operation Current: 0.10A~3.50A


♦ Maximum Voltage: 6V~60Vdc

♦ Operating Temperature: -40°C TO 85°C





# **Product Dimensions**



Terminal pad materials :Tin-Plated Nickle-copper Terminal pad solderability : Meets EIA specification RS 186-9E and ANSI/J-STD-002 Category 3.

Pig.1

Unit: mm

Model No.	А		В		С		D	E
Model No.	Min	Max	Min	Max	Min	Max	Min	Min
LP-MSM110/33	4.37	4.73	3.07	3.41	0.70	1.70	0.30	0.15

# Thermal Derating Chart-IH (A)

Part number	Maximum ambient operating temperatures (°C)								
	-40	-20	0	25	40	50	60	70	85
LP-MSM110/33	1.60	1.45	1.28	1.10	0.92	0.83	0.71	0.66	0.52

#### **Electrical Characteristic**

Model No. Umax (Vdc)	Llmany		Ihold	Itrip	Time to trip		R25	
	Imax (A)	@25°C	@25°C	Current	Time	Ri <sub>min</sub>	$R1_{\text{max}}$	
	(vuc)	(A)	(A)	(A)	(A)	(Sec)	$(\Omega)$	(Ω)
LP-MSM110/33	33.0	100	1.10	2.20	8.0	0.30	0.050	0.250



#### Test Procedures And Requirements

Test	Test Conditions	Accept/Reject Criteria
Resistance	In still air @ 25℃	$R_{min} \leq R \leq R_{max}$
Time to Trip	Specified current, V <sub>max</sub> , 25°C	T≤maximum Time to Trip
Hold Current	30min, at I <sub>H</sub>	No trip
Trip Cycle Life	Vmax, Imax, 100cycles	No arcing or burning
Trip Endurance	Vmax, 1 hours	No arcing or burning

# Physical Characteristics and Environmental Specifications

#### Physical Characteristics

Terminal materials:	Tin-Plated Nickle-copper			
Soldering zone	Meets EIA specification RS 186-9E and ANSI/J-STD-002 Category 3.			
Environmental Specifications				
Test	Conditions	Resistance Change		
Passive aging	85°C,1000hours	±10%		
Humidity aging	85℃/85%RH.1000 hours	±5%		
Thermal shock	MIL-STD-202,Method 107G	-30% typical resistance change		
	+85°C/-40°C,20times			
Solvent Resistance	MIL-STD-202,Method 215	no change		
Vibration	ML-STD-883C,Test Condition A	No chage		

#### **Electrical Specifications:**

 $I_{hold}$  = Hold Current. Maximum current device will not trip in 25 °C still air.

 $V_{\text{max}} = Maximum$  operating voltage device can withstand without damage at rated current (Imax).

 $I_{max} = Maximum$  fault current device can withstand without damage at rated voltage (Vmax).

Pd=Maximum power dissipation when device is in the tripped state in 25 °C still air environment at rated voltage.

 $Ri_{min/max} = Minimum/Maximum$  device resistance prior to tripping at 25 °C.


 $R1_{max}$  = Maximum device resistance is measured one hour post reflow.


Rev: 01.06.2018 2/5 www.leiditech.com



# Recommended pad layout (mm)

# **Solder reflow conditions**





Profile Feature	Pb-Free Assembly
Average ramp up rate (Ts <sub>MAX</sub> to Tp)	3°C/second max.
Preheat	
<ul> <li>Temperature min. (Ts<sub>MIN</sub>)</li> </ul>	150°C
<ul> <li>Temperature max. (Ts<sub>MAX</sub>)</li> </ul>	200°C
<ul> <li>Time (ts<sub>MIN</sub> to ts<sub>MAX</sub>)</li> </ul>	60-120 seconds
Time maintained above:	
• Temperature (T <sub>L</sub> )	217°C
• Time (t <sub>L</sub> )	60-150 seconds
Peak/Classification temperature (Tp)	260°C
Time within 5°C of actual peak temperature	re
Time (tp)	30 seconds max.
Ramp down rate	3°C/second max.
Time 25°C to peak temperature	8 minutes max.

Note: All temperatures refer to topside of the package, measured on the package body surface.

- Recommended reflow methods: IR, vapor phase oven, hot air oven, N2 environment for lead-free.
- Devices are not designed to be wave soldered to the bottom side of the board.
- Recommended maximum paste thickness is 0.25mm (0.010inch).
- Devices can be cleaned using standard industry methods and solvents.
- Soldering temprature profile meets RoHs leadfree process.

Notes: If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements


Rev: 01.06.2018 3/5 www.leiditech.com




Tape Specification And Reel Dimensions

<b>Coverning Specifications</b>				
EIA 481-1(Unit:mm)				
W	12.00+0.30/-0			
P <sub>0</sub>	8.0 ± 0.10			
P <sub>1</sub>	4.0± 0.10			
P <sub>2</sub>	2.0 ± 0.10			
A <sub>0</sub>	3.50 ± 0.10			
B <sub>0</sub>	4.90 ± 0.10			
D <sub>0</sub>	1.50+0.10/-0			
F	5.50± 0.05			
E <sub>1</sub>	1.75 ± 0.10			
Т	0.30± 0.10			
Leader min.	390			
Trailer min.	160			
Reel Dimensions				
А	178±1.0			
N	59±1			
W <sub>1</sub>	8.5+1.0/-0.2			
W <sub>2</sub>	12.0±1			

# EIA Tape Component Dimentions



# **EIA Reel Dimentions**





#### **Storage**

The maximum ambient temperature shall not exceed 38°C. Storage temperatures higher than 38°C could result in the deformation of packaging materials. The maximum relative humidity recommended for storage is 60%. High humidity with high temperature can accelerate the oxidation of the solder plating on the termination and reduce the solderability of the components. Sealed plastic bags with desiccant shall be used to reduce the oxidation of the termination and shall only be opened prior to use. The products shall not be stored in areas where harmful gases containing sulfur or chlorine are present Warning

- Use PPTC beyond the maximum ratings or improper use may result in device damage and possible electrical arcing and flame.
- PPTC are intended for protection against occasional over current or over temperature fault conditions and should not be used when repeated fault conditions or prolonged trip events are anticipated.
- Device performance can be impacted negatively if devices are handled in a manner inconsistent with recommended electronic, thermal, and mechanical procedures for electronic components.
- Use PPTC with a large inductance in circuit will generate a circuit voltage (L di/dt) above the rated voltage of the PPTC.
- Avoid impact PPTC device its thermal expansion like placed under pressure or installed in limited space.
- Contamination of the PPTC material with certain silicon based oils or some aggressive solvents can adversely impact the performance of the devices.PPTC SMD can be cleaned by standard methods.
- Requests that customers comply with our recommended solder pad layouts and recommended reflow profile. Improper board layouts or reflow profilecould negatively impact solderability performance of our devices.

Shanghai Leiditech Electronic Co.,Ltd

Email: sale1@leiditech.com Tel: +86- 021 50828806 Fax: +86- 021 50477059