

## SMCG Plastic-Encapsulate Diodes

### SK102 THRU SK1020 Schottky Rectifier Diodes

#### Features


- $I_{F(AV)}$  10A
- $V_{RRM}$  20V-200V
- High surge current capability
- Polarity: Color band denotes cathode

#### Applications

- Rectifier

#### Marking

- SK10X  
X : From 2 To 20



#### Limiting Values(Absolute Maximum Rating)

Item	Symbol	Unit	Test Conditions	SK10																
				2	3	4	5	6	8	10	15	20								
Repetitive Peak Reverse Voltage	$V_{RRM}$	V		20	30	40	50	60	80	100	150	200								
Maximum RMS Voltage	$V_{RMS}$	V		14	21	28	35	42	56	70	105	140								
Average Forward Current	$I_{F(AV)}$	A	60HZ Half-sine wave, Resistance load, TL(FIG.1)	10.0																
Surge(Non-repetitive)Forward Current	$I_{FSM}$	A	60Hz Half-sine wave, 1 cycle, $T_a=25^{\circ}C$	250																
Junction Temperature	$T_J$	$^{\circ}C$		-55~+125					-55~+150											
Storage Temperature	$T_{STG}$	$^{\circ}C$		-55 ~ +150																

#### Electrical Characteristics ( $T = 25^{\circ}C$ Unless otherwise specified)


Item	Symbol	Unit	Test Condition	SK10											
				2	3	4	5	6	8	10	15	20			
Peak Forward Voltage	$V_{FM}$	V	$I_{FM}=10.0A$	0.65		0.75		0.85		0.95					
Peak Reverse Current	$I_{RRM1}$	mA	$V_{RM}=V_{RRM}$	$T_a=25^{\circ}C$		0.5		0.1							
	$I_{RRM2}$			$T_a=100^{\circ}C$		20		10							
Thermal Resistance(Typical)	$R_{\theta J-A}$	$^{\circ}C/W$	Between junction and ambient		50										
	$R_{\theta J-L}$		Between junction and lead		15										
Typical junction capacitance	CJ	pF	Measured at 1.0MHz and applied reverse voltage of 4.0 volts.		400										

#### Notes:


Thermal resistance from junction to ambient and from junction to lead mounted on P.C.B. with 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pad areas

# Typical Characteristics


**FIG.1: FORWARD CURRENT DERATING CURVE**




**FIG.2: MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT**




**FIG.3: TYPICAL FORWARD CHARACTERISTICS**



**FIG.4: TYPICAL REVERSE CHARACTERISTICS**




## SMCG Package Outline Dimensions



Dimensions in inches and (millimeters)

## SMCG Suggested Pad Layout




### Note:

1. Controlling dimension: in millimeters.
2. General tolerance:  $\pm 0.05$  mm.
3. The pad layout is for reference purposes only.

### NOTICE

JSCJ reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. JSCJ does not assume any liability arising out of the application or use of any product described herein.

# Reel Taping Specifications For Surface Mount Devices-SMCG



**FIG: CONFIGURATION OF SURFACE MOUNTED DEVICES TAPING**

ITEM	SYMBOL	SMCG mm(inch)
Carrier width	A	6.05±0.1(0.238±0.004)
Carrier length	B	8.31±0.1(0.327±0.004)
Carrier depth	C	2.70±0.1(0.106±0.004)
Sprocket hole	d	1.55±0.05(0.061±0.002)
Reel outside diameter	D	330±2.0(13±0.079)
Reel inner diameter	D1	75 ±1.0 ( 2.95 ±0.039)
Feed hole diameter	D2	13±0.5(0.512±0.020)
Sprocket hole position	E	1.75±0.1(0.069±0.004)
Punch hole position	F	7.65±0.05(0.301±0.002)
Punch hole pitch	P	8.0±0.1(0.315±0.004)
Sprocket hole pitch	P0	4.0±0.1(0.157±0.004)
Embossment center	P1	2.0±0.1(0.079±0.004)
Total tape thickness	T	0.3± 0.1 (0.012±0.004)
Tape width	W	16.0±0.2(0.630±0.008)
Reel width	W1	24.0±2.0(0.945±0.079)

NOTE: Devices are packed in accordance with EIA standard RS-481-A and specification given above.