


S-SM340AF

Schottky Barrier Rectifiers Reverse Voltage 40V Forward Current 3.0A

1. FEATURES

- We declare that the material of product compliance with RoHS requirements and Halogen Free.
- S- prefix for automotive and other applications requiring unique site and control change requirements; AEC-Q101 qualified and PPAP capable.
- Plastic package has Underwriters Laboratory Flammability Classification 94V-0.
- Low power loss, high efficiency
- For use in low voltage high frequency inverters, free wheeling, and polarity protection applications
- Guardring for over voltage protection
- High temperature soldering guaranteed: 260°C/10 seconds at terminals
- Moisture Sensitivity Level-----Level 1
- ESD(Spec) Air≥15KV





2. DEVICE MARKING AND ORDERING INFORMATION

	_	
Device	Marking	Shipping
S-SM340AF	S34	3000/Tape&Reel

3. MAXIMUM RATINGS(Ta = 25°C)

Parameter	Symbol	Limits	Unit	
Maximum repetitive peak reverse voltage	VRRM	40	V	
Maximum RMS voltage	VRMS	28	V	
Maximum DC blocking voltage	VDC	40	V	
Maximum average forward rectified current lead length (See fig. 1) at TC = 75°C	IF(AV)	3	Α	
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	IFSM	100	Α	
Typical thermal resistance (Note 1)	RθJA	150	°C/W	
Typical thermal resistance (Note 1)	RθJL	35	C/VV	
Operating junction and storage temperature range	TJ, TSTG	_40 ~ +150	°C	
Lead temperature range	TL	125	$^{\circ}$	


4. ELECTRICAL CHARACTERISTICS (Ta= 25°C)

Characteristic	Symbol	Min.	Тур.	Max.	Unit
Maximum instantaneous forward voltage at 3.0A	VF	•	•	0.55	V
Maximum DC reverse current TA = 25°C	IR	-	-	0.5	mA
at rated DC blocking voltage Tj = 100°C	IIX	-	-	30	ША
Typical junction capacitance at 4.0V, 1MHz	CJ	-	265	-	pF


^{1. 8.0}mm² (.013mm thick) land areas





5. ELECTRICAL CHARACTERISTICS CURVES




Typical Instantaneous Forward Fig 3. -Characteristics 100 Instantaneous Forward Current (A) TJ = 25°C Pulse width = 300μ 1% Duty Cycle 10 1.0 0.1 0.01 0.4 0.6 0.8 1.0 0.2 Instantaneous Forward Voltage (V)












6.OUTLINE AND DIMENSIONS




SMA-FL			
DIM	MIN	MAX	Тур.
Α	4.40	4.80	4.60
В	2.30	2.70	2.60
С	3.30	3.70	3.50
D	1	1	0.55
Е	0.90	1.20	1.05
F	0.11	0.21	0.17
G	1.30	1.50	1.40
I	-	-	0.90
K	-	-	0.80
L	-	-	0.20
All Dimensions in mm			

GENERAL NOTES

- 1.Top package surface finish Ra0.4±0.2um
- 2.Bottom package surface finish Ra0.7±0.2um

7.SOLDERING FOOTPRINT



SMA-FL		
DIM	(mm)	
Χ	1.60	
Υ	1.80	
В	3.70	



DISCLAIMER

- Curve guarantee in the specification. The curve of test items with electric parameter is used as quality guarantee. The curve of test items without electric parameter is used as reference only.
- Before you use our Products for new Project, you are requested to carefully read this document and fully understand its contents. LRC shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any LRC's Products against warning, caution or note contained in this document.
- All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using LRC's Products, please confirm the latest information with a LRC sales represe--ntative.