

4

3

2

1

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.



LOC DS DIST -

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED (ECR-09-018695)	25.SEP.'09	KT	HG
	A2	REVISED (ECR-10-023563)	21.JUN.'11	KT	HG



A-A



B-B



NOTE

1. GENERAL TOLERANCE: ± 0.3 , $\pm 3^\circ$
2. APPLICABLE WIRE RANGE;

Conductor		Insulation Diameter	
Nominal Size	Calculated Cross-Section Area (mm ²)	Minimum (mm)	Maximum (mm)
0.13	0.14	0.9	0.95
0.22	0.24	1.0	1.05

3. APPLICATOR FEED: 7.5mm

Ⓜ

SELECTIVE GOLD

COPPER ALLOY

2005098-2

PRE-TIN

COPPER ALLOY

2005098-1

FINISH


MATERIAL

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:



MATERIAL SEE TABLE

FINISH SEE TABLE

DWN KT JUNG
CHK KT LIM
APVD HG CHD
PRODUCT SPEC

APPLICATION SPEC 114-61031

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

025 TH TAB CONTACT (SS)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

2005098

-

SCALE 10/1

SHEET 1 OF 1

REV A2