



Specifications :

Voltage rating: 100V AC / DC
 Current rating: 2A AC / DC
 Withstanding voltage: 500V AC/minute
 Temperature range: -40°C~+85°C
 Insulation resistance: ≥500MΩ
 Contact resistance: ≤20mΩ
 After environmental testing : ≤40mΩ

X1515 W R S-XX-LP SW

- ① Series No.
- ② Category : W-WAFER
- ③ Welding Board Angle : R-Straight 90°
- ④ Welding Way:S-SMT
- ⑤ Row No.-Pin No.: XX-02P~15P
- ⑥ Material : LP-LCP 94V-0
- ⑦ Plating Category: SW-Matte Tin Plating

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	7.30	1.50	4.45	09	17.80	12.00	14.95
03	8.80	3.00	5.95	10	19.30	13.50	16.45
04	10.30	4.50	7.45	11	20.80	15.00	17.95
05	11.80	6.00	8.95	12	22.30	16.50	19.45
06	13.30	7.50	10.45	13	23.80	18.00	20.95
07	14.80	9.00	11.95	14	25.80	19.50	22.45
08	16.30	10.50	13.45	15	26.80	21.00	23.95

X1515WRS-XX-LPSW	LCP UL 94V-0	Phosphor Bronze	X1515H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connectors
DWN	VIEW:	PART NO.: X1515WRS-XX-LPSW
CHKD	UNIT: mm/in	DWG NO.:
APPD	SIZE: A4	X-X1515WRS-XX-LPSW

广东星坤科技股份有限公司
 PCB LAYOUT
 生效日期
 文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ANGLAR				±5°
L ≤ 4				±0.2
4 < L ≤ 16				±0.3
16 < L ≤ 63				±0.4
L > 63				±0.5



XKB INDUSTRIAL PRECISION CO., LIMITED