FREE





## N-Channel 60 V (D-S) MOSFET

PRODUCT SUMMARY				
V <sub>DS</sub> (V)	$R_{DS(on)}$ ( $\Omega$ )	I <sub>D</sub> (mA)		
60	3 at V <sub>GS</sub> = 10 V	240		

## FEATURES Halogen-free According to IEC 61249-2-21 Definition

Low On-Resistance: 3 Ω
Low Threshold: 2 V (typ.)
Low Input Capacitance: 25 pF

Fast Switching Speed: 7.5 nsLow Input and Output Leakage

• Compliant to RoHS Directive 2002/95/EC

#### **BENEFITS**

- Low Offset Voltage
- Low-Voltage Operation
- Easily Driven Without Buffer
- · High-Speed Circuits
- Low Error Voltage

#### **APPLICATIONS**

- Direct Logic-Level Interface: TTL/CMOS
- Drivers: Relays, Solenoids, Lamps, Hammers, Display, Memories, Transistors, etc.
- · Battery Operated Systems
- · Solid-State Relays

TO-236 (SOT-23)	
G 1 3 D	Marking Code: 7E
Top View	

Ordering Information: 2N7002E-T1-E3 (Lead (Pb)-free)

2N7002E-T1-GE3 (Lead (Pb)-free and Halogen-free)

ABSOLUTE MAXIMUM RATINGS (T <sub>A</sub> = 25 °C, unless otherwise noted)					
Parameter		Symbol	Limit	Unit	
Drain-Source Voltage		V <sub>DS</sub>	60		
Gate-Source Voltage		V <sub>GS</sub>	± 20	V	
Continuous Drain Current (T <sub>.I</sub> = 150 °C)	T <sub>A</sub> = 25 °C	I <sub>D</sub>	240	mA	
Continuous Diain Current (1) = 150 C)	T <sub>A</sub> = 70 °C	סי	190		
Pulsed Drain Current <sup>a</sup>		I <sub>DM</sub>	1300		
Power Dissipation	T <sub>A</sub> = 25 °C	P <sub>D</sub>	0.35	W	
Power Dissipation	T <sub>A</sub> = 70 °C	' D	0.22	VV	
Thermal Resistance, Junction-to-Ambient		R <sub>thJA</sub>	357	°C/W	
Operating Junction and Storage Temperature Range		T <sub>J,</sub> T <sub>stg</sub>	- 55 to 150	°C	

#### Notes

a. Pulse width limited by maximum junction temperature.

## Vishay Siliconix



			Limits				
Parameter	Symbol	Test Conditions	Min.	Typ. <sup>a</sup>	Max.	Unit	
Static							
Drain-Source Breakdown Voltage	V <sub>DS</sub>	$V_{GS} = 0 \text{ V, } I_{D} = 10  \mu\text{A}$	60	68		V	
Gate-Threshold Voltage	V <sub>GS(th)</sub>	$V_{DS} = V_{GS}, I_{D} = 250 \mu A$	1	2	2.5	V	
Gate-Body Leakage	I <sub>GSS</sub>	$V_{DS} = 0 \text{ V}, V_{GS} = \pm 15 \text{ V}$			± 10	nA	
		V <sub>DS</sub> = 60 V, V <sub>GS</sub> = 0 V	1		1		
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	$V_{DS}$ = 60 V, $V_{GS}$ = 0 V , $T_{J}$ = 125 °C			500	μA	
On-State Drain Current <sup>b</sup>		V <sub>GS</sub> = 10 V, V <sub>DS</sub> = 7.5 V	800	1300			
	I <sub>D(on)</sub>	V <sub>GS</sub> = 4.5 V, V <sub>DS</sub> = 10 V	500	700		mA	
Drain-Source On-Resistance <sup>b</sup>	В	V <sub>GS</sub> = 10 V, I <sub>D</sub> = 250 mA		1.2	3		
	R <sub>DS(on)</sub>	V <sub>GS</sub> = 4.5 V, I <sub>D</sub> = 200 mA		1.8	4	Ω	
Forward Transconductance <sup>b</sup>	9 <sub>fs</sub>	V <sub>DS</sub> = 15 V, I <sub>D</sub> = 200 mA		600		mS	
Diode Forward Voltage	V <sub>SD</sub>	I <sub>S</sub> = 200 mA, V <sub>GS</sub> = 0 V		0.85	1.2	V	
Dynamic <sup>a</sup>			•		•		
Total Gate Charge	Q <sub>g</sub>	V 40 V V 45 V		0.4	0.6	nC	
Gate-Source Charge	Q <sub>gs</sub>	$V_{DS} = 10 \text{ V}, V_{GS} = 4.5 \text{ V}$ $I_{D} \cong 250 \text{ mA}$		0.06			
Gate-Drain Charge	Q <sub>gd</sub>			0.06			
Input Capacitance	C <sub>iss</sub>			21		pF	
Output Capacitance	C <sub>oss</sub>	$V_{DS} = 5 \text{ V}, V_{GS} = 0 \text{ V}, f = 1 \text{ MHz}$		7			
Reverse Transfer Capacitance	C <sub>rss</sub>			2.5			
Switching <sup>a, c</sup>				•			
Turn-On Time	t <sub>d(on)</sub>	$V_{DD}$ = 10 V, $R_L$ = 40 $\Omega$		13	20	ns	
Turn-Off Time	t <sub>d(off)</sub>	$I_D \cong 250 \text{ mA}, V_{GEN} = 10 \text{ V}, R_g = 10 \Omega$		18	25		


#### Notes:

- a. For DESIGN AID ONLY, not subject to production testing.
- b. Pulse test: pulse width  $\leq$  300  $\mu$ s duty cycle  $\leq$  2 %.
- c. Switching time is essentially independent of operating temperature.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.




## TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)









On-Resistance vs. Gate-Source Voltage




On-Resistance vs. Junction Temperature



**Transfer Characteristics** 



On-Resistance vs. Drain Current





**Threshold Voltage Variance Over Temperature** 

## Vishay Siliconix


# VISHAY

## TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)









Source-Drain Diode Forward Voltage

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see <a href="https://www.vishay.com/ppg270860">www.vishay.com/ppg270860</a>.

Vishay Siliconix

## SOT-23 (TO-236): 3-LEAD







Dim	MILLIMETERS		INCHES		
	Min	Max	Min	Max	
Α	0.89	1.12	0.035	0.044	
A <sub>1</sub>	0.01	0.10	0.0004	0.004	
A <sub>2</sub>	0.88	1.02	0.0346	0.040	
b	0.35	0.50	0.014	0.020	
С	0.085	0.18	0.003	0.007	
D	2.80	3.04	0.110	0.120	
E	2.10	2.64	0.083	0.104	
E <sub>1</sub>	1.20	1.40	0.047	0.055	
е	0.95 BSC		0.0374 Ref		
e <sub>1</sub>	1.90 BSC		0.0748 Ref		
L	0.40	0.60	0.016	0.024	
L <sub>1</sub>	0.64 Ref		0.025 Ref		
S	0.50 Ref		0.020 Ref		
q	3°	8°	3°	8°	
FCN: S-03946-Rev K 09-	lul-01	•			

ECN: S-03946-Rev. K, 09-Jul-01

DWG: 5479

Document Number: 71196 www.vishay.com 09-Jul-01



### **RECOMMENDED MINIMUM PADS FOR SOT-23**



Recommended Minimum Pads Dimensions in Inches/(mm)

Return to Index

APPLICATION NOTE



## **Legal Disclaimer Notice**

Vishay

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.