



Surface Mount Schottky Barrier Rectifier

Reverse Voltage - 100V

Forward Current - 5.0A

FEATURES

- Metal silicon junction, majority carrier conduction
- For surface mounted applications
- Low power loss, high efficiency
- High forward surge current capability
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications

PINNING

| PIN | DESCRIPTION |
|-----|-------------|
| 1   | Cathode     |
| 2   | Anode       |



Top View  
Marking Code: SL510  
Simplified outline SMAF and symbol

MECHANICAL DATA

- Case: SMAF
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 27mg / 0.00095oz

Absolute Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz resistive or inductive load, for capacitive load, derate by 20 %

| Parameter  | Symbols         | SSL510F    | Units |
|--|-----------------|------------|-------|
| Maximum Repetitive Peak Reverse Voltage  | $V_{RRM}$       | 100        | V     |
| Maximum RMS voltage  | $V_{RMS}$       | 70         | V     |
| Maximum DC Blocking Voltage  | $V_{DC}$        | 100        | V     |
| Maximum Average Forward Rectified Current  | $I_{F(AV)}$     | 5.0        | A     |
| Peak Forward Surge Current, 8.3ms<br>Single Half Sine-wave Superimposed<br>on Rated Load (JEDEC method)      | $I_{FSM}$       | 150        | A     |
| Max Instantaneous Forward Voltage at 5 A   | $V_F$           | 0.6        | V     |
| Maximum DC Reverse Current $T_a = 25^\circ\text{C}$<br>at Rated DC Reverse Voltage $T_a = 100^\circ\text{C}$ | $I_R$           | 1.0<br>50  | mA    |
| Typical Junction Capacitance <sup>(1)</sup>  | $C_j$           | 400        | pF    |
| Typical Thermal Resistance <sup>(2)</sup>  | $R_{\theta JA}$ | 60         | °C/W  |
| Operating Junction Temperature Range   | $T_j$           | -55 ~ +150 | °C    |
| Storage Temperature Range  | $T_{stg}$       | -55 ~ +150 | °C    |

( 1 ) Measured at 1 MHz and applied reverse voltage of 4 V D.C

( 2 ) P.C.B. mounted with 2.0" X 2.0" (5 X 5 cm) copper pad areas.



Fig.1 Forward Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Forward Characteristic




Fig.4 Typical Junction Capacitance




Fig.5 Maximum Non-Repetitive Peak Forward Surge Current





Fig.6- Typical Transient Thermal Impedance







## PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SMAF



### The recommended mounting pad size



### Marking

| Type number | Marking code |
|-------------|--------------|
| SSL510F     | SL510        |