
	CHA 容器制造商		う科尼盛		
	S	规格承 Specification fo	-		
客户	名称:				
(Custome	er Name)				
产品	名称:	贴片铝电解电	容器		
(Product	t Name)	SMD Alumir	num Electrolytic	Capacitor	
客户料	4号 :				
(Customer p	art number)				
科尼盛	料号:	XT100UF5	50V90RV006	7	
(KNSCHA	number)				
	现格:	XT 100UF50	V 8*10.5mm		
(Specifie	cations)	XT 100UF50	V 8*10.5mm		
	制造			客户	
	(Manufacture))		(Customer)	
	Approval 审核		检验	Approval 审核	核准
(Fiction)	审 核 (Chief)	1≪ /⊭ (Approval)	ায় ভয় (Inspect)	审 核 (Chief)	₁∞ /⊭ (Approval)
	た。 秋花島电子方況で 「 本 本 本 本 本 本 本 本 本 本 本 本 本				
刘淑芬		徐贵南			
东莞市科尼	盛电子有限公	、司			
DONG GUAN	KNSCHA ELEC	TRONICS CO.,LT	ſD.		
No. The 8th Fl	oor, A3 Buildiı	ng, R&D Center	(Phase I),		
Songshan Lak	e Intelligent Va	alley, Liaobu To	wn, Dongguan C	lity.	
TEL:0769-8369			-83861559		
Email : sales@	knscha.com W	/ebsite: http://v	vww.knscha.com	1	


Product Dimensions




	Unit: mm
Φ	8
L	10.5±0.4
A	8.3
В	8.3
C	9.2
W	0.7~1.2
Р	3.1±0.2

Items					Performance				
Category Temperature Range			−55°C~10	5°C					
Rated Voltage V_{R}			50 V						
Capacitance C _B			100 µ	F				(12	20Hz,20℃)
Capacitance Tolerance			± 20	%				(12	20Hz,20℃)
Surge Voltage $V_{\rm S}$			63 VDC						
Leakage Current (20°C)			ILEAK ≤	< 63	βμΑ			After	2 minutes
Tan δ		≤ 0.14						(12	20Hz,20℃)
Impedance max.		\$\lambda\$ \lambda\$						(100)KHz,20℃)
Ripple Current (I _{AC. R} / rms)		160mA						(120)Hz,105℃)
Low Temperature		Impodar			Z(_{-25°C}) / Z(_{+20°C})	2			
Characteristics at 120 Hz		Impedal	ipedance ratio		Z(_{-55°C}) / Z(_{+20°C})		3		
Ripple Current (A) and	Frequency	y (Hz)	Hz) 50.60		120	1K	1K 1C		
Frequency Multipliers	Multipli		0.85		1.00	1.10		1.20	
	Items	Endu	rance			Shelf L	ife Tes	st	
Endurance and Shelf Life	Test Time	2,00	0 Hrs at 10	5℃;	V _R	1,000	Hrs at	105℃	
Test	Cap. Change	Withi	n ±25 % of	initi	al value	Within	±25 9	% of initial valu	le
Test	Tan δ	Less	than 300%	of s	pecified value	Less th	nan 30	00% of specifie	ed value
	Leakage Curren	t Withi	n specified v	alue)	Within specified value			
Standards			JIS C	510	01-1, -18, IEC 6	0384-4			
Remarks					mpliance, Halo				

Marking: Each capacitor shall be marked with the following information. Marking color: Black



Please refer to "Precautions and Guidelines for Aluminum Electrolytic Capacitors" section in catalog for further details.



l	Jnit:mm	


D ^{±0.5}	L	A ±0.2	B ^{±0.2}	C ±0.2	w	P ^{±0.2}	Fig.No.
4	5.4 ^{±0.4}	4.3	4.3	5.1	0.5to0.8	1.0	1
4	5.8 ^{±0.4}	4.3	4.3	5.1	0.5to0.8	1.0	1
4	7.0 ^{±0.4}	4.3	4.3	5.1	0.5to0.8	1.0	1
5	5.4 ^{±0.4}	5.3	5.3	6.1	0.5to0.8	1.3	1
5	5.8 ^{±0.4}	5.3	5.3	6.1	0.5to0.8	1.3	1
5	7.0 ^{±0.4}	5.3	5.3	6.1	0.5to0.8	1.3	1
6.3	5.4 ^{±0.4}	6.6	6.6	7.2	0.5to0.8	2.2	1
6.3	5.8 ^{±0.4}	6.6	6.6	7.2	0.5to0.8	2.2	1
6.3	7.7 ^{±0.4}	6.6	6.6	7.2	0.5to0.8	2.2	1
6.3	7.9 ^{±0.4}	6.6	6.6	7.2	0.5to0.8	2.2	1
8	6.5 ^{±0.5}	8.3	8.3	9.2	0.7to1.2	3.1	1
8	7.9 ^{±0.5}	8.3	8.3	9.2	0.7to1.2	3.1	1
8	10.5 ^{±0.5}	8.3	8.3	9.2	0.7to1.2	3.1	1
8	11.5 ^{±0.5}	8.3	8.3	9.2	0.7to1.2	3.1	1
8	$12.5^{\pm 0.5}$	8.3	8.3	9.2	0.7to1.2	3.1	1
8	$13.5^{\pm 0.5}$	8.3	8.3	9.2	0.7to1.2	3.1	1
10	7.7 ^{±0.5}	10.3	10.3	11.2	0.7to1.2	4.4	1
10	$10.5^{\pm 0.5}$	10.3	10.3	11.2	0.7to1.2	4.4	1
10	11.5 ^{±0.5}	10.3	10.3	11.2	0.7to1.2	4.4	1
10	$12.5^{\pm 0.5}$	10.3	10.3	11.2	0.7to1.2	4.4	1
10	$13.5^{\pm 0.5}$	10.3	10.3	11.2	0.7to1.2	4.4	1
12.5	$13.5^{\pm 0.5}$	13.0	13.0	14.0	1.0to1.4	4.4	2
12.5	16.0 ^{±0.5}	13.0	13.0	14.0	1.0to1.4	4.4	2
16	16.5 ^{±0.5}	17.0	17.0	18.0	1.0to1.4	6.4	2
16	21.5 ^{±0.5}	17.0	17.0	18.0	1.0to1.4	6.4	2
18	16.5 ^{±0.5}	19.0	19.0	20.0	1.0to1.4	6.4	2
18	21.5 ^{±0.5}	19.0	19.0	20.0	1.0to1.4	6.4	2


Product Code Guide - SMD Type

1. Carrier Tape

Fig. 1-1 Carrier tape *φ*D≤10








Unit:mm

Size(¢D×L)	$Y^{\pm 0.3}$	H ^{±0.2}	W ^{±0.2}	P ^{±0.1}	E ^{±0.1}	F ^{±0.1}	T ^{±0.2}	S ^{±0.1}	Fig.No.
ф4×5.4	12.0	5.0	5.0	8.0	1.75	5.5	6.0	_	1-1
ф4×5.8	12.0	5.0	5.0	8.0	1.75	5.5	6.5	_	1-1
φ4×7.0	12.0	5.0	5.0	8.0	1.75	5.5	7.5	-	1-1
φ5×5.4	12.0	6.0	6.0	12.0	1.75	5.5	6.0	_	1-1
φ5×5.8	12.0	6.0	6.0	12.0	1.75	5.5	6.5	—	1-1
φ5×7.0	12.0	6.0	6.0	12.0	1.75	5.5	7.5	—	1-1
ф6.3×5.4	16.0	8.7	8.7	12.0	1.75	7.5	6.0	—	1-1
ф6.3×5.8	16.0	8.7	8.7	12.0	1.75	7.5	6.5	—	1-1
ф6.3×7.7	16.0	8.7	8.7	12.0	1.75	7.5	8.2	—	1-1
ф6.3×7.9	16.0	8.7	8.7	12.0	1.75	7.5	8.5	—	1-1
ф8×6.5	16.0	8.7	8.7	12.0	1.75	7.5	7.2	—	1-1
ф8×10.5	24.0	8.7	8.7	16.0	1.75	11.5	11.5	—	1-1
ф8×11.5	24.0	8.7	8.7	16.0	1.75	11.5	12.0	_	1-1
ф8×12.5	24.0	8.7	8.7	16.0	1.75	11.5	13.5	_	1-1
ф8×13.5	24.0	8.7	8.7	16.0	1.75	11.5	14.5	—	1-1
φ10×7.7	24.0	10.7	10.7	16.0	1.75	11.5	8.5	_	1-1
φ10×10.5	24.0	10.7	10.7	16.0	1.75	11.5	11.5	_	1-1
φ10×11.5	24.0	10.7	10.7	16.0	1.75	11.5	12.5	-	1-1
φ10×12.5	24.0	10.7	10.7	16.0	1.75	11.5	13.5	-	1-1
φ10×13.5	24.0	10.7	10.7	16.0	1.75	11.5	14.5	-	1-1
φ12.5×13.5	32.0	13.9	13.9	24.0	1.75	14.2	14.5	28.5	1-2
φ12.5×16.0	32.0	13.9	13.9	24.0	1.75	14.2	16.5	28.5	1-2
ф16×16.5	44.0	17.5	17.5	28.0	1.75	20.2	17.5	40.5	1-2
φ16×21.5	44.0	17.5	17.5	28.0	1.75	20.2	22.5	40.5	1-2
φ18×16.5	44.0	19.5	19.5	32.0	1.75	20.2	17.5	40.5	1-2
φ18×21.5	44.0	19.5	19.5	32.0	1.75	20.2	22.5	40.5	1-2


2. Reel Package

Fig. 2-1










Case size	Φ4~5	Ф6.З	Ф8×6.5	Ф8	Φ1Ο	Ф12.5	Ф16~18
A	14	18	18	26	26	34	46
D	380	380	380	380	380	380	380
Т	3.0	3.0	3.0	3.0	3.0	3.0	3.0

3. Packing specification

Fig. 3-1 Carrier Tape




Case size	Q'ty / Reel	Reels/Box	Q'ty/Box
Ф4	2,000	12	24,000
Φ5	1,000	12	12,000
Ф6.З	1,000	10	10,000
Ф8×6.5	1,000	10	10,000
Ф8×10.5	500	10	5,000
Ф8×11.5~13.5	400	10	4,000
Φ10×7.7~10.5	500	10	5,000
Ф10×11.5~13.5	400	10	4,000
Ф12.5×13.5	250	6	1,500
Ф12.5×16	200	6	1,200
Ф16×16.5	125	5	625
Ф16×21.5	100	5	500
Ф18×16.5	125	5	625
Ф18×21.5	100	5	500

Case size	Φ4~5	Ф6.З	Ф8×6.5	Φ8	Φ10	Ф12.5	Ф16~18
Н	260	260	260	340	340	240	260
W	395	395	395	395	395	395	395
L	390	390	390	390	390	390	390

Unit:pcs


4. Sealing Tape Reel Strength

- 4.1 Peel angle: 165 to 180°Crefered to the surface on which the tape is glued.
- 4.2 Peel speed: 300mm per minutes
- 4.3 The peel strength must be 0.1 \sim 0.7N under these conditions.



5. Packing Method

- 5.1 The leader length of the tape shall not be less than 150 mm including 10 or more embossed sections inwhich no parts are contained.
- 5.2 the core has an empty section with a length less than 60mm, and the perforation carrier is only suitable for ϕ D \leq 5mm.



Endurance characteristic:

No.	Item	(Condit	ions						C	Specifi	cation			
		Capacitor is placed i follow specific regula						Сар	acitanc	e chang	e With	nin ± 1	0% of i	nitial value	
1	Rotational Temperature	regulation is " +25℃ +25℃ (3 min.) → +	105℃	(30 mir	n.) → +2	25℃ (3	•	Tan	δ		With	Within specified value			
	Test	min.)", and it is called cycles, and then the	capaci	itor shal	l be sub	jected t		Lea	kage Ci	urrent	With	nin spec	ified va	lue	
		standard atmospher which measurement				rs, arter		Phy	sical		No I	No broken and undamaged			
		1.Capacitors shall be	- nlace	d in over	n with ar	nlicatio	n	Сар	acitanc	e chang	e With	nin ±25	5% of in	itial value	
2	High Temperature	of rated voltage2,00 2.hen the capacitor)0 +72	/ -0 ho	urs at 1	05°C.		Tanδ			Les: valu		00% of	specified	
	Endurance Life Test	atmospheric condition			, after w	vhich		Lea	kage Cu	urrent	With	nin spec	cified va	lue	
	LIIE TEST	measurements shall	be ma	de.			Ī	Phy	sical		No I	oroken a	and und	amaged	
								Сар	acitanc	e chane	e With	nin ± 2	5% of i	nitial value	
3	High Temperature	After 1,000 +48 / -1 rated voltage. And th	nen the	capaci	tor shall			Tan δ				s than3 e	00% of	specified	
	Unload Life	-	subjected to standard atmospheric conditions fours, after which measurements shall be made								With	nin spec	cified va	lue	
	Test										No I	No broken and undamaged			
		Capacitors shall be	apacitors shall be exposed for 1,000 +48 / -0							e chane	e With	nin ± 1	0% of i	nitial value	
4	Humidity	hours in an atmosph 3℃.And then the ca	iere of S	90 ~ 95	5% R. H.	at 60 =	±	Tan	δ		Les: valu		150% o	f specified	
	Test	standard atmospher				rs,		Leakage Current			With	nin spec	cified va	lue	
		afterwhich measurer	ments s	snall be	made.			Physical			No I	No broken and undamaged			
		Capacitors are place	nd at -5	5 + 3°) for 96	з + л		Capacitance change							
_	Low	hours. And then the						Tanδ			With	Within specified value			
5	Temperature Test	standard atmospher				rs, after		Leakage Current			With	Within specified value			
	1651	which measurement	s shall	be mad	Э.			Phy	sical		No I	No broken and undamaged			
		1. Fix it at the point 4	1 mm or	less fro	m body.	. For one	s	Сар	acitanc	e chang	e With	nin ± 1	0% of i	nitial value	
		of 12.5 mm or more			25 mm	or more		Tanδ			With	Within specified value			
6	Vibration	length, use separate 2. Direction and duri	ng of vi	bration:				Lea	kage Cu	urrent	With	nin spec	cified va	lue	
	Test	directions mutually e hours). 3. Frequency: 10 to 5 4. Total amplitude :	55 Hz re	eciproca			э.	Phy	sical		Not	No broken and undamaged			
		he capacitor shall be	e subie	cted to	1.000 c	vcles at	t	Сар	acitanc	e chang	e With	nin ± 2	:0% of i	nitial value	
		$15 \sim 35^{\circ}$ C. Protective each consisting of a	/e serie	s resist	or a 1K	Ω	-	Tan			Les	s than 2		f specified	
			conds, followed by discharge period of					Leakage Current				value Within specified value			
	Surge	approximately 5.5 m	pproximately 5.5 minutes.		t		sical			No broken and undamaged					
7	Voltage	Applying voltage:		1	I										
	Test	Rated Voltage(V)	4	6.3	10	16	2	25	35	50	63	80	100		
		Surge Voltage(V)	4.6	7.3	11.5	18.4	28	8.8	40.3	57.5	72.5	92	115		
		Rated Voltage(V)	160	200	250	315	3	50	400	420	450	500	525		
		Surge Voltage(V)	176	220	275	347	З	85	440	462	495	550	578		

No.	Item		Conditions			S	pecificat	tion			
			e fully immersed in the so t a temperature of 245 :		Capacitar	nce chang	Within ±	: 10% of	initial value		
8	Solderability		older coating must be mor		Tan δ		Within specified value				
	Test	95% Disping apoed 0			Leakage	Current	Within specified value				
		Dipping speed: 2 Dipping time: 3±			Physical			No broken and undamaged			
	Solder	1. IR Reflow			Physical		INU DI UKE		luaillageu		
	Heat-Resistance	↓ T4	t3		Capacitar	nce chang	Within ±	: 10% of	initial value		
		тз	$ \longrightarrow $				Within sp	pecified v	value		
		11 Temperature (°C)	t1 t2	Leakage	Current	Within sp	pecified v	value			
			Time(sec) —		Physical		No broke	en and un	damaged		
		Detect allow		1	4 5 0	00			100		
		Rated voltage			4-50	63 up 4-6.3	4-1		160 up		
		Case size (ϕ)) Temp.(T1~T2,℃)		1-6.3		8-	18	8-18		
		Preheat	Time (t1)(Max,secs)		150-180						
9			Temp.(T3,℃)	217	230	217	217	230	217		
		Duration	Time (t2)(Max,secs)	90	40	60	60	40	40		
			Temp.(T4,°C)	-	260	250	25	_	245		
		Peak	Time (t3,secs)						<u>I</u>		
		Reflow cycles	5			2 0	r less				
		 2.Solder iron method: Bit temperature: 350 ± 5°C Application time of soldering Iron: 3 +1/-0 sec **Please contact our representative if your condition is higher. **Please ensure that the capacitor became cold enough tothe room temperature (5°C ~ 35°C) before the second reflow. **Consult with us when performing reflow profile in IPC /JEDEC (J-STD-020) 									
10	Venting Test	 2. Test condition AC test: The ofrated volta DC test: Age Where case Note: When the proficapacitor elem 	the capacitor shall be connut tage or 250Vrms AC which oplying inverse DC rated w e diameter: $\phi D \leq 12.5$ m $\phi D > 12.5$ m essure relief vent operations ent (terminal and metal for essure relief device does	nected a chever is voltage v mm: 2 A I mm: 10 A ed, the pil etc.) o	cross an a the lower. with curren DC max. DC max. capacitor or cover.	pplying 50 t to the ca shall avoid	pacitor. I any dang	ger of fir	e or explosion		

No.	Item	Conditions						
11	Land Pattern	Recommended pad pattern and size	Case size Φ4 Φ5 Φ6.3 Φ8 Φ10 Φ12.5 Φ16 Φ18	G 1.0 1.4 1.9 3.0 4.0 4.0 6.0 6.0	U Land size 2.6 3.0 3.5 4.0 4.0 5.8 6.8 8.0	Init:mm X 1.8 1.8 2.5 2.5 3.0 3.5 3.5 3.5		
12	Standards	Satisfies Characteristic JIS C 5101-1, -18						

Conforming to RoHS and European REACH Regulation

The capacitors do not intentionally contain the banned substances (Cd, Pb, Hg, Cr(VI), PBB, PBDE, DEHP, BBP, DBP, DIBP) listed in "RoHS directrive : (EU) 2015/863" and its concentration is less than the threshold values.

Our products are "articles without any intended releas" besed published on 26 May2008. They are not applicable for "Registration" for European REACH Regulation Article 7 (1).

Precautions and Guidelines for Aluminum Electrolytic Capacitors

1.Guidelines for Circuit Design (General / Application guidelines for using electrolytic capacitors) Selecting of a right capacitor is a key to a good circuit design.

(1)Polarity

Most of the aluminum electrolytic capacitors are polarized. Therefore, they must be installed with the correct polarity. Usage in the reverse polarity results into a short-circuit condition that may damage or even explode the capacitor. In addition, it may influence circuit functionality. A bi-polar electrolytic capacitor should be installed when polarity across a capacitor is unstable / reversible. It should be, however, noted that usage of both polar and bi-polar capacitors are limited to DC applications. They must NOT be used for AC application.

(2)Operating Voltage

Applied DC voltage must not exceed rated voltage of the capacitor. Applying higher voltage than its rated voltage across a capacitor terminals cause overheating due to higher leakage currents and capacitor dielectric/insulation deterioration that will ultimately affect a capacitor's performance. The device, however, is capable of working under short-time transient voltages such as DC transients and peak AC ripples. Reverse voltages higher than 1 Volt with a specified temperature limit or AC voltages are not permissible. Overall, using capacitors at recommended operating voltages can prolong its lifespan. Note that the result of DC voltage overlapped with peak ripple voltage should not exceed rated voltage.

(3)Ripple Current

One of the key functions of any capacitor is removal of the ripple current i.e. the RMS value of AC flowing through a capacitor. But, a ripple current higher than rated ripple current will drop resultant capacitance, cause undue internal heating and thus reduces life span of the capacitor. In extreme cases, internal high temperature will cause the pressure relief vent to operate while destroying the device. Overall, it is important to note that an electrolytic capacitor must be used within a permissible range of ripple current. Indicators like temperature coefficient of allowable ripple current are generally sued to determine life expectancy of the capacitor, but to avoid related complex calculations and for the sake of simplicity, we haven't provided temperature coefficient in the catalogue. But it offers key indicators like maximum operating temperature for calculation of life expectancy at a given temperature.

(4)Operating Temperature

Capacitors should be used within a permissible range of operating temperatures. Using capacitor at a higher temperature than maximum rated temperature will considerably shorten its life. In the worst-case scenario, high temperature can cause pressure relief vent to operate and the device will get destroyed. Using capacitors at an ambient room temperature assure their longer life.

(5)Leakage Current

Leakage current flows through a capacitor when DC voltage is applied across it. Leakage current varies with changes in ambient temperature and applied DC voltage level and its time of application. Overvoltage situation, presence of moisture, and thermal stresses, especially occurring during the soldering process can enhance leakage current. Initial leakage current is usually higher and does not decrease until voltage is applied for a certain period of time. It is recommended to keep initial leakage current within specified levels.

(6)Charge and Discharge

Regular electrolytic capacitors are not suitable for rapid charging/discharging circuits. Such usage may either cause reduction in overall capacitance or damage due to overheating. provides special assistance for selecting appropriate capacitors for rapid charging/discharging circuits.

(7)Surge Voltage

The Surge voltage rating is referred as the maximum DC overvoltage that may be applied to an electrolytic capacitor for a short time interval of 30 seconds at infrequent at infrequent time intervals not exceeding 5.5minutes with a limiting resistance of 1k Ω . Unless otherwise described on the catalogue or product specifications, please do not apply a voltage exceeding the capacitor's voltage rating. The rated surge voltages corresponding to rated voltages of electrolytic capacitors are presented as follows:

Rated Voltage(V)	4	6.3	10	16	25	35	50	63	80	100
Surge Voltage(V)	4.6	7.3	11.5	18.4	28.8	40.3	57.5	72.5	92	115
Rated Voltage(V)	160	200	250	315	350	400	420	450	500	525
Surge Voltage(V)	176	220	275	347	385	440	462	495	550	578

(8)Surge Voltage

The capacitor shall NOT be exposed to:

(a)Fluids including water, saltwater spray, oil, fumes, highly humid or condensed climates, etc.

(b)Ambient conditions containing hazardous gases/fumes like hydrogen sulfide, sulfurous acid, nitrous acid, chlorine or bromine gas, ammonia, tec.

(c)Exposed to ozone, ultraviolet rays and radiation.

(d)Severe vibrations or physical shocks that exceeds the specifications mentioned in this catalogue.

(9)Circuit Design Consideration

(a)Please ensure whether application, operating and mounting conditions satisfy the conditions specified in the catalog before installation of a capacitor. Please consult KNSCHA, if any of the conditions are beyond the conditions specified in the catalog

(bave at the improvement of the provided the

(c)Electrical characteristics and performance of aluminum electrolytic capacitors are affected by variation of applied voltage, ripple current, ripple frequency and operating temperature. Therefore, these parameters shall not exceed specified values in the catalog.

(d)Aluminum capacitors may be connected in the parallel fashion for increasing total capacitance and/or for achieving higher ripple current capability. But, such design may cause unequal current flow through each of the capacitors due to differences in their impedances.

(e)When two or more capacitors are connected in series, voltage across each capacitor may differ and fall below the applied voltage. A resistor should be placed across each capacitor so as to match applied voltage with voltage across a capacitor.

(f)Please consult KNSCHA while selecting a capacitor for high- frequency switching circuit or a circuit that undergoes rapid charging/ discharging.

(g)Standard outer sleeve of the capacitor is not a perfect electrical insulator therefore is unsuitable for the applications that requires perfect electrical insulation. Please consult KNSCHA, if your application requires perfect electrical insulation.

(h)Tilting or twisting capacitor body is not recommended once it is soldered to the PCB.

2.Caution for Assembling Capacitors

(1)Mounting

(a)Aluminum electrolytic capacitors are not recommended to reuse in other circuits once they are mounted and powered in a circuit.

(b)Aluminum electrolytic capacitors may hold static charge between its anode and cathode, which is recommended to be discharged through a $1k\Omega$ resistor before re-use.

(c)A long storage of capacitors may result into its insulation deterioration. This can lead to a high leakage current when voltage is applied that may damage the capacitor. Capacitors following a long storage period must undergo voltage treatment/re-forming.

Capacitors are charged by applying rated DC voltage through a resistor of $1k\Omega$ in series at least for an hour. It is recommended to increase applied voltage gradually using a voltage regulator unit once capacitors are assembled on the board. The charging should be followed by discharging through a $1K\Omega$ resistor.

(d)Please check capacitor rated voltage before mounting.

(e)Please check capacitor polarity before mounting.

(f)Please don't drop capacitor on the floor / hard object.

(g)Please don't deform the capacitor during installation.

(h)Please confirm whether the lead spacing of the capacitors match with its pad spacing / footprint on PCB prior to installation.

(i)Please avoid excessive mechanical shocks to capacitor during the auto-insertion process, inspection or centering operations.

Please don't place any wiring or circuit over the capacitor's pressure relief vent. The pressure relief vent may fail to open if adequate clearance space is not provided. Following table shows minimum clearance space required for different case diameters.

Case Diameter	φ6.3~φ16	φ18~ φ35	ϕ 40 or above
Clearance(mm)	2 mm	3 mm	5 mm

(2)Soldering

(a)Please confirm that soldering conditions, especially temperature and contact time are within our specifications. Dip or flow soldering temperature should be limited at 260 ± 5 °C for 10 ± 1 sec while manual soldering using soldering iron should be limited at 350 ± 5 °C for 3 + 1/-0 seconds. Please do not dip capacitor body into molten solder. A capacitor's life will be negatively affected if these conditions are violated.

(b)Storage of capacitors in high humidity conditions is likely to affect the solder-ability of lead wires and terminals.

(c)Reflow soldering should NOLY be used for SMD type capacitors. The temperature and duration shall not exceed the specified temperature and duration in the specification. If the temperature or duration is higher than the value specified, please consult KNSCHAbefore usage.

(d)Standard aluminum electrolytic capacitors are not designed to withstand multiple reflow processes. Please consult KNSCHA if repeated reflowing is unavoidable.

(e)Incorrect mounting on PCB with improper external strength applied on its lead wires or capacitor body after soldering may damage a capacitor's internal structure, cause short circuit, or lead to high leakage current issues. Do not bend or twist the capacitor body after soldering. Referring to the drawings below only case (i) is recommended.

(i)Correct soldering

(ii)Hole-to-hole spacing on PCB differs from the lead space of lead wires.

(iii)Lead wires are bent after soldering.

(iv)Capacitor body doesn't stand vertical on PCB after soldering.


(3) Cleaning Circuit Boards after Soldering

(a)Following chemicals are not recommended for cleaning: Solvent containing halogen ions, Alkaline solvent, Xylene, Acetone, Terpene, petro-based solvent.

(b)Recommended cleaning conditions:

Fatty-alcohol - Pine Alpha ST-100S, Clean Through-750H and IPA (isopropyl alcohol) are examples of the most acceptable cleaning agents. Temperature of the cleaning agent must not exceed 60°C. Flux content in the cleaning agents should be limited to 2 Wt. %. Overall length of cleaning process (e.g., immersion, ultrasonic or other) shall be within 5 minutes (5 \sim 7mm height within 3 minutes). CFC substitute cleaning agents such as AK225AES can also be used for cleaning. In this case, its temperature shall not exceed 40 C and cleaning process (e.g., immersion, ultrasonic or other) shall be completed within 2 \sim 3 minutes. After cleaning capacitors should be dried with hot air for at least 10 minutes along with the PCB. Temperature of hot air shall not exceed maximum category temperature of

the capacitor. Insufficient drying may cause appearance defects, sleeve shrinkage, and bottom-plate bulging. However, usage of this CFC substitute must completely regulated for protection of environment.



3. Maintenance Inspection

Periodical inspection of aluminum capacitors is absolutely necessary especially when they are used with industrial equipment. The following items should be checked:

(1)Appearance: Bloated, vent operated, leaked, etc.

(2)Electrical characteristic: Capacitance, Tan δ , leakage current, and other specified items listed in specification.

KNSCHArecommend replacing the capacitors if any of the abovementioned items fail to meet specifications.

4.Storage

(1)The most suitable conditions for aluminum capacitor storage are 5 $^{\circ}$ C ~ 35 $^{\circ}$ C and indoor relative humidity less than 75%. High temperature and/or humidity storage is detrimental to the capacitors.

(2)Capacitors shall not be stored in wet or damp atmospheres containing water, brine, fumes or oil.

(3)Capacitors storage area shall neither be exposed to hazardous gases such as hydrogen sulfide, sulfurous acid, nitrous acid, chlorine, ammonium, etc. nor to acidic or alkaline solutions.

(4)Capacitors shall not be exposed to ozone, ultraviolet rays or radiation.

5.Estimation of life time

$$Lr = L_0 \times 2 \qquad 10$$

Lr: Estimated lifetime (hours)

Lo: Base lifetime specified at maximum operating temperature with applied the DC voltage and the ripple current (hours)

To max: The core temperature that rated ripple current applied at maximum operating temperature.

Tr max: The core temperature that applied actual ripple current at ambient temperature.

6.Maintenance Inspection

Please consult with a local industrial waste disposal specialist when disposing of aluminum electrolytic capacitors.

7.Environmental Consideration

KNSCHAalready have received ISO 14000 certificate. Cadmium (Cd), Lead (Pb), Mercury (Hg), Hexavalent Chromium (Cr+6), PBB,PBDE, DEHP, BBP, DBP and DIBP have never been using in capacitor. If you need "Halogen-free" products, please consult with us.

For further details, please refer to the following industrial standards:

IEC 60384-4- Fixed capacitors for use in electronic equipment – Part 4: Sectional specification – Aluminum electrolytic capacitors with solid (MnO2) and non-solid electrolyte (Established in January 1995, Revised in March 2007)

EIAJ RCR-2367B- Guideline of notabilia for fixed aluminum electrolytic capacitors for use in electronic equipment [Technical Standardization Committee on Passive Components (Established in March 1995, Revised in March 2002)].