

Not recommended items.

RV3

VERTICAL CHIP TYPE ALUMINUM ELECTROLYTIC CAPACITORS

ELNA®

Chip Type 85°C Capacitors (height:5.5mm,8.0mm)

GREEN CAP SMD Anti-cleaning solvent

- Compatible with surface mounting for 5.5mm, 8.0mm high capacitors.
- Supplied with carrier taping.
- Guarantees 2000 hours at 85°C.

High CV




Marking color : Black print

Specifications

Item	Performance												
Category temperature range (°C)	−40 to +85												
Tolerance at rated capacitance (%)	±20												
Leakage current (μA)	Less than 0.01CV or 3 whichever is larger (after 2 minutes) C : Rated capacitance (μF) ; V : Rated voltage (V)												
Tangent of loss angle (tanδ)	Rated voltage (V)	6.3	10	16	25	35	50						
	tanδ (max.)	0.42	0.32	0.26	0.18	0.14	0.12						
	(20°C,120Hz)												
Characteristics at high and low temperature	Rated voltage (V)	6.3	10	16	25	35	50						
	Impedance ratio (max.)	Z−25°C/Z+20°C	4	3	2	2	2						
		Z−40°C/Z+20°C	8	8	5	5	4						
	(20°C,120Hz)												
Endurance (85°C) (Applied ripple current)	Test time	2000 hours											
	Leakage current	The initial specified value or less											
	Percentage of capacitance change	Within ±30% of initial value											
	Tangent of the loss angle	300% or less of the initial specified value											
Shelf life (85°C)	Test time : 1000 hours ; other items are the same as those for the endurance. Voltage application treatment : According to JIS C5101-1												
Applicable standards	JIS C5101-1, -18 (IEC 60384-1, -18)												

Outline Drawing



Coefficient of Frequency for Rated Ripple Current

Frequency (Hz)	50	120	1k	10k·100k
6.3 to 16	0.80	1	1.15	1.25
25 to 35	0.80	1	1.25	1.40
50	0.70	1	1.35	1.50

Part numbering system (example : 16V220μF)

RV3	—	16	V	221	M	F80	U	—
Series code	Rated voltage symbol	Rated capacitance symbol	Capacitance tolerance symbol	Casing symbol			Taping symbol	

- Soldering conditions are described on page 13.
- Land pattern size are described on page 11.
- The taping specifications are described on page 14.

Standard Ratings

Item	6.3			10			16			25			35			50		
	Case φD (mm)	ESR (Ω)	Rated ripple current (mArms)	Case φD (mm)	ESR (Ω)	Rated ripple current (mArms)	Case φD (mm)	ESR (Ω)	Rated ripple current (mArms)	Case φD (mm)	ESR (Ω)	Rated ripple current (mArms)	Case φD (mm)	ESR (Ω)	Rated ripple current (mArms)	Case φD (mm)	ESR (Ω)	Rated ripple current (mArms)
4.7	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	4×5.3	42	20
10	—	—	—	—	—	—	—	—	—	4×5.3	30	23	4×5.3	23	27	5×5.3	20	34
22	—	—	—	4×5.3	24	26	4×5.3	20	30	5×5.3	14	43	5×5.3	11	47	6.3×5.3	9.0	59
33	4×5.3	21	28	4×5.3	16	33	5×5.3	13	44	5×5.3	9.0	54	6.3×5.3	7.0	67	6.3×7.7	6.0	82
47	4×5.3	15	34	5×5.3	11	45	5×5.3	9.2	50	6.3×5.3	6.4	75	6.3×7.7	4.9	90	6.3×7.7	4.2	98
68	5×5.3	10	47	5×5.3	7.8	54	6.3×5.3	6.3	74	6.3×5.3	4.4	90	6.3×7.7	3.4	109	—	—	—
100	5×5.3	7.0	58	—	—	—	6.3×5.3	4.3	103	6.3×7.7	3.0	124	—	—	—	—	—	—
150	6.3×5.3	4.6	83	6.3×7.7	3.5	98	6.3×7.7	2.9	109	—	—	—	—	—	—	—	—	—
220	6.3×7.7	3.2	113	6.3×7.7	2.4	130	6.3×7.7	2.0	144	—	—	—	—	—	—	—	—	—
330	6.3×7.7	2.1	139	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—

(Note) Rated ripple current : 85°C, 120Hz ; ESR : 20°C, 120Hz

NOTE

Design, Specifications are subject to change without notice.
Ask factory for technical specifications before purchase and/or use.