COMPLIANT

HALOGEN FREE



www.vishay.com

Vishay General Semiconductor

High-Voltage Surface-Mount Schottky Rectifier

High Barrier Technology for Improved High Temperature Performance



SMA (DO-214AC)



LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS				
I _{F(AV)}	1.0 A			
V _{RRM} 90 V, 100 V				
I _{FSM}	50 A			
V _F	0.62 V			
I _R	1.0 μA			
T _J max.	175 °C			
Package	SMA (DO-214AC)			
Circuit configuration	Single			

FEATURES

- · Low profile package
- · Ideal for automated placement
- Guardring for overvoltage protection
- · Low power losses, high efficiency
- · Low forward voltage drop
- · Low leakage current
- · High surge capability
- I light surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified available
 - Automotive ordering code: base P/NHE3 or P/NHM3
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

TYPICAL APPLICATIONS

For use in low voltage high frequency inverters, freewheeling, DC/DC converters, and polarity protection applications.

MECHANICAL DATA

Case: SMA (DO-214AC)

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade

Base P/N-M3 - halogen-free, RoHS-compliant, commercial

grade

Base P/NHE3_X - RoHS-compliant and AEC-Q101 qualified Base P/NHM3_X - halogen-free, RoHS-compliant, and AEC-Q101 qualified

("_X" denotes revision code e.g. A, B, ...)

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3, M3, HE3, and HM3 suffix meets JESD 201 class 2 whisker test

Polarity: color band denotes the cathode end

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	SS1H9	SS1H10	UNIT	
Device marking code		S9 S10			
Maximum repetitive peak reverse voltage	V _{RRM}	90 100		V	
Working peak reverse voltage	V_{RWM}	90 100		V	
Maximum DC blocking voltage	V _{DC}	90 100		V	
Maximum average forward rectified current (fig. 1)	I _{F(AV)}	1.0		Α	
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	50		А	
Peak repetitive reverse surge current at t _p = 2.0 μs, 1 kHz	I _{RRM}	1.0		Α	
Storage temperature range	T _{STG}	-65 to +175		°C	
Maximum operating temperature	T _J	175		°C	



Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)						
PARAMETER	TEST CONDITIONS		SYMBOL	SS1H9	SS1H10	UNIT
Maximum instantaneous forward voltage (1)	I _F = 1.0 A	T _J = 25 °C		0.77		V
		T _J = 125 °C	V _F	0.62		
	I _F = 2.0 A	T _J = 25 °C		0.86		
		T _J = 125 °C		0.	0.70	
Maximum reverse current at rated V _R ⁽²⁾		T _J = 25 °C	I _R	1.	.0	μΑ
		T _J = 125 °C		0.	.5	mA

Notes

 $^{(1)}\,$ Pulse test: 300 μs pulse width, 1 % duty cycle

(2) Pulse test: pulse width \leq 40 ms

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	SS1H9	SS1H10	UNIT	
Maximum thermal resistance (1)	$R_{\theta JA}$	88		°C/W	
Maximum thermal resistance (**)	$R_{ heta JL}$	30			

Note

 $^{(1)}\,$ PCB mounted with 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pad areas

ORDERING INFORMATION (Example)						
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE		
SS1H10-E3/61T	0.064	61T	1800	7" diameter plastic tape and reel		
SS1H10-E3/5AT	0.064	5AT	7500	13" diameter plastic tape and reel		
SS1H10HE3_B/H (1)	0.064	Н	1800	7" diameter plastic tape and reel		
SS1H10HE3_B/I (1)	0.064	I	7500	13" diameter plastic tape and reel		
SS1H10-M3/61T	0.064	61T	1800	7" diameter plastic tape and reel		
SS1H10-M3/5AT	0.064	5AT	7500	13" diameter plastic tape and reel		
SS1H10HM3_B/H (1)	0.064	Н	1800	7" diameter plastic tape and reel		
SS1H10HM3_B/I (1)	0.064	I	7500	13" diameter plastic tape and reel		

Note

(1) AEC-Q101 qualified

Vishay General Semiconductor

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)




Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 4 - Typical Reverse Characteristics




Fig. 5 - Typical Junction Capacitance





Fig. 6 - Typical Transient Thermal Impedance



Vishay General Semiconductor

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

SMA (DO-214AC)





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.