

## 30V N-Channel Enhancement Mode MOSFET

### GENERAL DESCRIPTION

The ME75N03 is the N-Channel logic enhancement mode power field effect transistors are produced using high cell density, DMOS trench technology. This high density process is especially tailored to minimize on-state resistance. These devices are particularly suited for low voltage application such as cellular phone and notebook computer power management and other battery powered circuits where high-side switching, and low in-line power loss are needed in a very small outline surface mount package.

### FEATURES

- $R_{DS(ON)} \leq 5.2\text{m}\Omega @ VGS=10\text{V}$
- $R_{DS(ON)} \leq 8\text{m}\Omega @ VGS=4.5\text{V}$
- Super high density cell design for extremely low  $R_{DS(ON)}$
- Exceptional on-resistance and maximum DC current capability



### APPLICATIONS

- Power Management in Note book
- DC/DC Converter
- Load Switch
- LCD Display inverter

### PIN CONFIGURATION

(TO-252-3L)

Top View



Ordering Information: ME75N03(Pb-free)

ME75N03-G (Green product-Halogen free)

### Absolute Maximum Ratings ( $T_c=25^\circ\text{C}$ Unless Otherwise Noted)

Parameter	Symbol	Maximum Ratings	Unit
Drain-Source Voltage	$V_{DS}$	30	V
Gate-Source Voltage	$V_{GS}$	$\pm 20$	V
Continuous Drain Current  $T_c=25^\circ\text{C}$	$I_D$	71	A
$T_c=70^\circ\text{C}$		57	
Pulsed Drain Current	$I_{DM}$	284	A
Maximum Power Dissipation  $T_c=25^\circ\text{C}$	$P_D$	42	W
$T_c=70^\circ\text{C}$		27	
Operating Junction Temperature	$T_J$	-55 to 150	°C
Thermal Resistance-Junction to Case *	$R_{\theta JC}$	3	°C/W

\* The device mounted on 1in<sup>2</sup> FR4 board with 2 oz copper



**30V N-Channel Enhancement Mode MOSFET**
**Electrical Characteristics (T<sub>C</sub> = 25°C Unless Otherwise Specified)**

Symbol	Parameter	Limit	Min	Typ	Max	Unit
<b>STATIC</b>						
BV <sub>DSS</sub>	Drain-Source Breakdown Voltage	V <sub>GS</sub> =0V, I <sub>D</sub> =250 μA	30			V
V <sub>GS(th)</sub>	Gate Threshold Voltage	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250 μA	1		3	V
I <sub>GSS</sub>	Gate-Body Leakage	V <sub>GS</sub> =±20V			±100	nA
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	V <sub>DS</sub> =30V, V <sub>GS</sub> =0V			1	μA
R <sub>DSON</sub>	Drain-Source On-Resistance*	V <sub>GS</sub> =10V, I <sub>D</sub> =20A		4.3	5.2	mΩ
		V <sub>GS</sub> =4.5V, I <sub>D</sub> =20A		6	8	
V <sub>SD</sub>	Diode Forward Voltage *	I <sub>SD</sub> =25A, V <sub>GS</sub> =0V		0.8	1.2	V
<b>DYNAMIC</b>						
Q <sub>g</sub>	Total Gate Charge	V <sub>DD</sub> =15V, V <sub>GS</sub> =10V, I <sub>D</sub> =20A		56		nC
Q <sub>g</sub>	Total Gate Charge			28		
Q <sub>gs</sub>	Gate-Source Charge	V <sub>DD</sub> =15V, V <sub>GS</sub> =4.5V, I <sub>D</sub> =20A		9		
Q <sub>gd</sub>	Gate-Drain Charge			13		
R <sub>g</sub>	Gate Resistance	V <sub>DS</sub> =0V, V <sub>GS</sub> =0V, f=1MHz		1.7		Ω
C <sub>iss</sub>	Input Capacitance	V <sub>DS</sub> =15V, V <sub>GS</sub> =0V, f=1MHz		2580		pF
C <sub>oss</sub>	Output Capacitance			393		
C <sub>rss</sub>	Reverse Transfer Capacitance			128		
t <sub>d(on)</sub>	Turn-On Delay Time	V <sub>DD</sub> =15V, R <sub>L</sub> =15Ω I <sub>D</sub> =1A, V <sub>GEN</sub> =10V R <sub>G</sub> =3Ω		23		ns
t <sub>r</sub>	Turn-On Rise Time			17		
t <sub>d(off)</sub>	Turn-Off Delay Time			76		
t <sub>f</sub>	Turn-Off Fall Time			12		







Notes: a. pulse test: pulse width ≤ 300us, duty cycle ≤ 2%, Guaranteed by design, not subject to production testing.

b. Matsuki Electric/ Force mos reserves the right to improve product design, functions and reliability without notice.








**30V N-Channel Enhancement Mode MOSFET**

**Typical Characteristics (T<sub>J</sub> = 25°C Noted)**




**30V N-Channel Enhancement Mode MOSFET**

**Typical Characteristics (T<sub>J</sub> = 25°C Noted)**



### TO-252-3L Package Outline



SYMBOL	MIN	MAX
A	2.10	2.50
B	0.40	0.90
C	0.40	0.90
D	5.30	6.30
D1	2.20	2.90
E	6.30	6.75
E1	4.80	5.50
L1	0.90	1.80
L2	0.50	1.10
L3	0.00	0.20
H	8.90	10.40
P	2.30 BSC	

