





SIGN	DATE	DESCRIPTION	APPROVER
△			
△			
△			



P. C. BOARD LAYOUT

78P	52.86	61.10	67.10	2.41	11.11	15.30
62P	55.42	63.50	69.32	2.41	8.36	12.50
44P	38.96	47.04	53.04	2.29	8.36	12.50
26P	25.25	33.32	39.14	2.29	8.36	12.50
15P	16.92	24.99	30.81	2.29	8.36	12.50
POS. NO.	A	B	C	D	E	F

DIMENSION

### SPECIFICATIONS:

Current rating:3.0A AC/DC

Voltage rating:250V AC/DC

Contact resistance:30m ohm MAX

Insulation resistance:5000M ohm MIN

Withstanding voltage:1000V AC for one minute

Operating temperature range:-40°C~+85°C

### MATERIAL AND FINISH

Insulator:PBT+30%G.F(UL94V-0)


Contact:Copper Alloy Nickel Undercoated

Selective Gold Plated


Finish:Metal Iron With Tin Plated

## Ordering Information

Number of contacts		Housing Type		Mounting Options		Contacts Material		Contact Plated		Insulator material		Insulator color		Mark	
Code	Definition	Code	Definition	Code	Definition	Code	Definition	Code	Contact Area	Code	Definition	Code	Definition	Code	Definition
B	15 PIN	M	Male	1	RIVETED W/ SHIELD ONLY	2	Brass	1	Full Gold 1u"	0	PBT	0	Black	0	NONE
D	26 PIN	F	Female	2	RIVETED W/ FRONT RIVET		Phosphor bronze	2	Gold 3u"			6	Blue	2	Nexttron
F	44 PIN			3	RIVETED W/ REAR RIVET			3	Gold 5u"			9	White		
G	62 PIN			4	RIVETED W/ NUT RIVET			4	Gold 10u"						
H	78 PIN			5	RIVETED W/ HEX SCREW+HEX NUT			5	Gold 15u"						
								6	Gold 30u"						



Mounting Options



正凌精密工业股份有限公司  
NEXTRONICS ENGINEERING CORP

PART. NAME: D型XX芯高密直插式PCB焊接插座(针)				TITLE:			
PART. NO.: SUB-HPBF-5171-092				DWG NAME:			
APPROVED BY	CHECKED BY	DESIGNED BY	DRAWN BY	CUSTOM NO.:		Tolerance	
Jonnson	Jeff	allan	Jacky			x. ±0.50	
						x.x ±0.30	
						x.xx ±0.10	
						xx° ±1°	