


Low Current LED in Ø 3 mm Tinted Diffused Package



19220

PRODUCT GROUP AND PACKAGE DATA

- Product group: LED
- Package: 3 mm
- Product series: low current
- Angle of half intensity: $\pm 25^\circ$

FEATURES

- Low power consumption
- High brightness
- CMOS / MOS compatible
- Specified at $I_F = 2$ mA
- Luminous intensity categorized
- Yellow and green color categorized
- Material categorization:
for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

APPLICATIONS

- Low power DC circuits

| PARTS TABLE | | | | | | | | | | | | | | |
|------------------------------|--------|--------------------------|------|------|---------------|-----------------|------|------|---------------|---------------------|------|------|---------------|--------------|
| PART | COLOR | LUMINOUS INTENSITY (mcd) | | | at I_F (mA) | WAVELENGTH (nm) | | | at I_F (mA) | FORWARD VOLTAGE (V) | | | at I_F (mA) | TECHNOLOGY |
| | | MIN. | TYP. | MAX. | | MIN. | TYP. | MAX. | | MIN. | TYP. | MAX. | | |
| TLLR4400 | Red | 0.63 | 1.2 | - | 2 | 612 | - | 625 | 2 | - | 1.9 | 2.4 | 2 | GaAsP on GaP |
| TLLR4400-AS12Z | Red | 0.63 | 1.2 | - | 2 | 612 | - | 625 | 2 | - | 1.9 | 2.4 | 2 | GaAsP on GaP |
| TLLR4401 | Red | 1 | 2 | - | 2 | 612 | - | 625 | 2 | - | 1.9 | 2.4 | 2 | GaAsP on GaP |
| TLLR4401-AS12 | Red | 1 | 2 | - | 2 | 612 | - | 625 | 2 | - | 1.9 | 2.4 | 2 | GaAsP on GaP |
| TLLR4401-AS12Z | Red | 1 | 2 | - | 2 | 612 | - | 625 | 2 | - | 1.9 | 2.4 | 2 | GaAsP on GaP |
| TLLY4400 | Yellow | 0.63 | 1.2 | - | 2 | 581 | - | 594 | 2 | - | 2.4 | 2.9 | 2 | GaAsP on GaP |
| TLLY4400-MS12 ⁽¹⁾ | Yellow | 0.63 | 1.2 | - | 2 | 581 | - | 594 | 2 | - | 2.4 | 2.9 | 2 | GaAsP on GaP |
| TLLY4401 | Yellow | 1 | 2 | - | 2 | 581 | - | 594 | 2 | - | 2.4 | 2.9 | 2 | GaAsP on GaP |
| TLLY4401-AS12 ⁽¹⁾ | Yellow | 1 | 2 | - | 2 | 581 | - | 594 | 2 | - | 2.4 | 2.9 | 2 | GaAsP on GaP |
| TLLY4401-AS12Z | Yellow | 1 | 2 | - | 2 | 581 | - | 594 | 2 | - | 2.4 | 2.9 | 2 | GaAsP on GaP |
| TLLY4401-MS12 ⁽¹⁾ | Yellow | 1 | 2 | - | 2 | 581 | - | 594 | 2 | - | 2.4 | 2.9 | 2 | GaAsP on GaP |
| TLLG4400 | Green | 0.63 | 1.2 | - | 2 | 562 | - | 575 | 2 | - | 1.9 | 2.4 | 2 | GaP on GaP |
| TLLG4400-AS12 | Green | 0.63 | 1.2 | - | 2 | 562 | - | 575 | 2 | - | 1.9 | 2.4 | 2 | GaP on GaP |
| TLLG4401 | Green | 1 | 2 | - | 2 | 562 | - | 575 | 2 | - | 1.9 | 2.4 | 2 | GaP on GaP |
| TLLG4401-AS12 | Green | 1 | 2 | - | 2 | 562 | - | 575 | 2 | - | 1.9 | 2.4 | 2 | GaP on GaP |
| TLLG4401-MS12 | Green | 1 | 2 | - | 2 | 562 | - | 575 | 2 | - | 1.9 | 2.4 | 2 | GaP on GaP |
| TLLG4401-MS21 | Green | 1 | 2 | - | 2 | 562 | - | 575 | 2 | - | 1.9 | 2.4 | 2 | GaP on GaP |

Note

- ⁽¹⁾ Not for new designs

**ABSOLUTE MAXIMUM RATINGS** ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)
TLLG440., TLLR440., TLLY440.

| PARAMETER | TEST CONDITION | SYMBOL | VALUE | UNIT |
|--|---|------------|-------------|--------------------|
| Reverse voltage | | V_R | 6 | V |
| DC forward current | | I_F | 7 | mA |
| Surge forward current | $t_p \leq 10\text{ }\mu\text{s}$ | I_{FSM} | 0.15 | A |
| Power dissipation | $T_{amb} \leq 84\text{ }^{\circ}\text{C}$ | P_V | 20 | mW |
| Junction temperature | | T_j | 100 | $^{\circ}\text{C}$ |
| Operating temperature range | | T_{amb} | -40 to +100 | $^{\circ}\text{C}$ |
| Storage temperature range | | T_{stg} | -55 to +100 | $^{\circ}\text{C}$ |
| Soldering temperature | $t \leq 5\text{ s}$, 2 mm from body | T_{sd} | 260 | $^{\circ}\text{C}$ |
| Thermal resistance junction to ambient | | R_{thJA} | 800 | K/W |

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)
TLLR440., RED

| PARAMETER | TEST CONDITION | PART | SYMBOL | MIN. | TYP. | MAX. | UNIT |
|-----------------------------------|---|----------|-------------|------|----------|------|------------|
| Luminous intensity ⁽¹⁾ | $I_F = 2\text{ mA}$ | TLLR4400 | I_V | 0.63 | 1.2 | - | mcd |
| | | TLLR4401 | I_V | 1 | 2 | - | mcd |
| Dominant wavelength | $I_F = 2\text{ mA}$ | | λ_d | 612 | - | 625 | nm |
| Peak wavelength | $I_F = 2\text{ mA}$ | | λ_p | - | 635 | - | nm |
| Angle of half intensity | $I_F = 2\text{ mA}$ | | ϕ | - | ± 25 | - | $^{\circ}$ |
| Forward voltage | $I_F = 2\text{ mA}$ | | V_F | - | 1.9 | 2.4 | V |
| Reverse voltage | $I_R = 10\text{ }\mu\text{A}$ | | V_R | 6 | 20 | - | V |
| Junction capacitance | $V_R = 0\text{ V}$, $f = 1\text{ MHz}$ | | C_j | - | 50 | - | pF |

Note⁽¹⁾ In one packing unit $I_{Vmin.}/I_{Vmax.} \leq 0.5$ **OPTICAL AND ELECTRICAL CHARACTERISTICS** ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)
TLLY440., YELLOW

| PARAMETER | TEST CONDITION | PART | SYMBOL | MIN. | TYP. | MAX. | UNIT |
|-----------------------------------|---|----------|-------------|------|----------|------|------------|
| Luminous intensity ⁽¹⁾ | $I_F = 2\text{ mA}$ | TLLY4400 | I_V | 0.63 | 1.2 | - | mcd |
| | | TLLY4401 | I_V | 1 | 2 | - | mcd |
| Dominant wavelength | $I_F = 2\text{ mA}$ | | λ_d | 581 | - | 594 | nm |
| Peak wavelength | $I_F = 2\text{ mA}$ | | λ_p | - | 585 | - | nm |
| Angle of half intensity | $I_F = 2\text{ mA}$ | | ϕ | - | ± 25 | - | $^{\circ}$ |
| Forward voltage | $I_F = 2\text{ mA}$ | | V_F | - | 2.4 | 2.9 | V |
| Reverse voltage | $I_R = 10\text{ }\mu\text{A}$ | | V_R | 6 | 20 | - | V |
| Junction capacitance | $V_R = 0\text{ V}$, $f = 1\text{ MHz}$ | | C_j | - | 50 | - | pF |

Note⁽¹⁾ In one packing unit $I_{Vmin.}/I_{Vmax.} \leq 0.5$



| OPTICAL AND ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified) | | | | | | | |
|---|---------------------------------|----------|----------------|------|------|------|------|
| TLLG440., GREEN | | | | | | | |
| PARAMETER | TEST CONDITION | PART | SYMBOL | MIN. | TYP. | MAX. | UNIT |
| Luminous intensity ⁽¹⁾ | I _F = 2 mA | TLLG4400 | I _V | 0.63 | 1.2 | - | mcd |
| | | TLLG4401 | I _V | 1 | 2 | - | mcd |
| Dominant wavelength | I _F = 2 mA | | λ _d | 562 | - | 575 | nm |
| Peak wavelength | I _F = 2 mA | | λ _p | - | 565 | - | nm |
| Angle of half intensity | I _F = 2 mA | | φ | - | ± 25 | - | ° |
| Forward voltage | I _F = 2 mA | | V _F | - | 1.9 | 2.4 | V |
| Reverse voltage | I _R = 10 μA | | V _R | 6 | 20 | - | V |
| Junction capacitance | V _R = 0 V, f = 1 MHz | | C _j | - | 50 | - | pF |

Note

(1) In one packing unit I_{Vmin}/I_{Vmax} ≤ 0.5

| LUMINOUS INTENSITY CLASSIFICATION | | |
|-----------------------------------|-----------------------|------|
| GROUP | LIGHT INTENSITY (mcd) | |
| STANDARD | MIN. | MAX. |
| K | 0.63 | 1.25 |
| L | 1 | 2 |
| M | 1.6 | 3.2 |
| N | 2.5 | 5 |
| P | 4 | 8 |
| Q | 6.3 | 12.5 |
| R | 10 | 20 |
| S | 16 | 32 |
| T | 25 | 50 |
| U | 40 | 80 |

Note

- Luminous intensity is tested at a current pulse duration of 25 ms. The above type numbers represent the order groups which include only a few brightness groups. Only one group will be shipped on each bag (there will be no mixing of two groups on each bag).
In order to ensure availability, single brightness groups will not be orderable.
In a similar manner for colors where wavelength groups are measured and binned, single wavelength groups will be shipped on any one bag.
In order to ensure availability, single wavelength groups will not be orderable

| COLOR CLASSIFICATION | | | | |
|----------------------|----------------------|------|-------|------|
| GROUP | DOM. WAVELENGTH (nm) | | | |
| | YELLOW | | GREEN | |
| | MIN. | MAX. | MIN. | MAX. |
| 0 | - | - | - | - |
| 1 | 581 | 584 | - | - |
| 2 | 583 | 586 | - | - |
| 3 | 585 | 588 | 562 | 565 |
| 4 | 587 | 590 | 564 | 567 |
| 5 | 589 | 592 | 566 | 569 |
| 6 | 591 | 594 | 568 | 571 |
| 7 | - | - | 570 | 573 |
| 8 | - | - | 572 | 575 |

Note

- Wavelengths are tested at a current pulse duration of 25 ms

TYPICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)




Fig. 1 - Forward Current vs. Ambient Temperature




Fig. 4 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 2 - Relative Luminous Intensity vs. Angular Displacement




Fig. 5 - Relative Luminous Intensity vs. Forward Current/Duty Cycle




Fig. 3 - Forward Current vs. Forward Voltage




Fig. 6 - Relative Luminous Intensity vs. Forward Current




Fig. 7 - Relative Intensity vs. Wavelength




Fig. 10 - Relative Luminous Intensity vs. Forward Current/Duty Cycle




Fig. 8 - Forward Current vs. Forward Voltage




Fig. 11 - Relative Luminous Intensity vs. Forward Current




Fig. 9 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 12 - Relative Intensity vs. Wavelength




Fig. 13 - Forward Current vs. Forward Voltage




Fig. 16 - Relative Luminous Intensity vs. Forward Current




Fig. 14 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 17 - Relative Intensity vs. Wavelength





Fig. 15 - Relative Luminous Intensity vs. Forward Current/Duty Cycle



PACKAGE DIMENSIONS in millimeters



Drawing-No.: 6.544-5255.01-4
Issue: 9; 28.07.14

REEL DIMENSIONS in millimeters




Fig. 18 - Reel

AS12 = cathode leaves tape first
AS21 = anode leaves tape first

TAPE




Fig. 19 - LED in Tape

AMMOPACK





Fig. 20 - Tape Direction

Note

- The new nomenclature for ammpack is e.g. ASZ only, without suffix for the LED orientation. The carton box has to be turned to the desired position: "+" for anode first, or "-" for cathode first. AS12Z and AS21Z are still valid for already existing types, BUT NOT FOR NEW DESIGN

TAPE DIMENSIONS in millimeters



| | |
|---------------|-------------------------|
| Quantity per: | Reel (Mat.-no. 1764) |
| | 2000 |

21885

| OPTION | DIMENSION "H" ± 0.5 mm |
|--------|------------------------|
| AS | 17.3 |
| MS | 25.5 |



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.