

# **KBJ6005 THRU KBJ610**


## **BRIDGE RECTIFIER**

### **FEATURES**

- · Glass passivated chip junction
- · Reliable low cost construction utilizing molded plastic technique
- · Ideal for printed circuit board
- · Low forward voltage drop
- · Low reverse leakage current
- · High surge current capability

#### MECHANICAL DATA

Case: Molded plastic, KBJ Epoxy: UL 94V-O rate flame retardant Terminals: Leads solderable per MIL-STD-202, method 208 guaranteed Mounting position: Any Weight: 0.16ounce, 4.6gram



Dimensions in inches and (millimeters)

()<sup>®</sup>

 $\mathbf{\Theta}$ 

广东钜兴电子科技有限公司

### Maximum Ratings and Electrical Characteristics

Ratings at 25 ambient temperature unless otherwise specified. Single phase, half wave, 60H<sub>Z</sub>, resistive or inductive load. For capacitive load, derate current by 20%.

	Symbols	KBJ6005	KBJ601	KBJ602	KBJ604	KBJ606	KBJ608	KBJ610	Units
Maximum Recurrent Peak Reverse Voltage	V <sub>RRM</sub>	50	100	200	400	600	800	1000	Volts
Maximum RMS Voltage	V <sub>RMS</sub>	35	70	140	280	420	560	700	Volts
Maximum DC Blocking Voltage	V <sub>DC</sub>	50	100	200	400	600	800	1000	Volts
Maximum Average Forward	Т	L <sub>(AV)</sub> 6.0							A.m.n
Rectified Current at T <sub>C</sub> =110	I <sub>(AV)</sub>	0.0							Атр
Peak Forward Surge Current,									
8.3ms single half-sine-wave	I <sub>FSM</sub>	I <sub>FSM</sub> 120							Amp
superimposed on rated load (JEDEC method)									
Maximum Forward Voltage	V <sub>F</sub>	1.0							Volts
at 3.0A DC and 25	۴F								
Maximum Reverse Current at T <sub>A</sub> =25	Т	5.0							uAmp
at Rated DC Blocking Voltage T <sub>A</sub> =125	IR	I <sub>R</sub> 500							
Typical Junction Capacitance (Note 1)	CJ	80							pF
Typical Thermal Resistance (Note 2)	$R_{\theta JC}$	1.5							/W
Operating and Storage Temperature Range	T <sub>J</sub> , Tstg	-55 to +150							

#### NOTES:

version: 02

1- Measured at 1 MHz and applied reverse voltage of 4.0 VDC.


2- Thermal Resistance from Junction to Case with Device Mounted on 75mm x 75mm x 1.6mmCu Plate Heatsink.




# KBJ6005 THRU KBJ610

## BRIDGE RECTIFIER

#### Characteristic Curves (T<sub>A</sub>=25 °C unless otherwise noted)











FIG.4- TYPICAL REVERSE CHARACTERISTICS PER BRIDGE ELEMENT



广东钜兴电子科技有限公司

version: 02