

-30V P-Channel Enhancement Mode MOSFET

Description

The AP150P03NF uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge and operation with gate voltages as low as 4.5V. This device is suitable for use as a Battery protection or in other Switching application.

General Features

$V_{DS} = -30V$ $I_D = -150A$






$R_{DS(ON)} < 3.2m\Omega$ @ $V_{GS} = -10V$ (Type: 2.5m Ω)

Application

Lithium battery protection

Wireless impact

Mobile phone fast charging



Package Marking and Ordering Information

Product ID	Pack	Marking	Qty(PCS)
AP150P03NF	PDFN5*6-8L	AP150P03NF XXX YYYYY	5000

Absolute Maximum Ratings (TC=25°C unless otherwise noted)

Symbol	Parameter	Rating	Units
V _{DS}	Drain-Source Voltage	-30	V
V _{GS}	Gate-Source Voltage	±20	V
I _D @TC=25°C	Continuous Drain Current, V _{GS} @ -10V ₁	-150	A
I _D @TC=100°C	Continuous Drain Current, V _{GS} @ -10V ₁	-75	A
I _{DM}	Pulsed Drain Current ₂	-450	A
E _{AS}	Single Pulse Avalanche Energy ₃	576	mJ
I _{AS}	Avalanche Current	-70	A
P _D @TC=25°C	Total Power Dissipation ₄	150	W
T _{STG}	Storage Temperature Range	-55 to 150	°C
T _J	Operating Junction Temperature Range	-55 to 150	°C
R _{θJA}	Thermal Resistance Junction-Ambient 1	25	°C/W
R _{θJC}	Thermal Resistance Junction-Case1	1.06	°C/W

-30V P-Channel Enhancement Mode MOSFET

Electrical Characteristics (T_J=25 °C, unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
BVDSS	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =-250μA	-30	-35		V
IDSS	Zero Gate Voltage Drain Current	V _{DS} =-30V, V _{GS} =0V			-1	μA
IGSS	Gate-Body Leakage Current	V _{GS} =±20V, V _{DS} =0V			±100	nA
VGS(th)	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =-250μA	-1	-1.7	-2.5	V
RDS(ON)	Drain-Source On-State Resistance	V _{GS} =-10V, I _D =-20A		2.5	3.2	mΩ
		V _{GS} =-4.5V, I _D =-20A		4.0	5.2	mΩ
gFS	Forward Transconductance	V _{DS} =-5V, I _D =-20A		65		S
Ciss	Input Capacitance	V _{DS} =-15V, V _{GS} =0V, f=1.0MHz		7000		pF
Coss	Output Capacitance			820		pF
Crss	Reverse Transfer Capacitance			540		pF
Rg	Gate resistance	V _{GS} =0V, V _{DS} =0V, f=1.0MHz		2.2		Ω
td(on)	Turn-on Delay Time	V _{GS} =-10V, V _{DS} =-15V, R _L =0.75Ω, R _{GEN} =3Ω		14		nS
t _r	Turn-on Rise Time			13		nS
td(off)	Turn-Off Delay Time			65		nS
t _f	Turn-Off Fall Time			37		nS
Q _g	Total Gate Charge	V _{GS} =-10V, V _{DS} =-15V, I _D =-20A		130		nC
Q _{gs}	Gate-Source Charge			12		nC
Q _{gd}	Gate-Drain Charge			31		nC
ISD	Source-Drain Current (Body Diode)				-150	A
VSD	Forward on Voltage ^(Note 3)	V _{GS} =0V, I _S =-20A			-1.3	V
trr	Reverse Recovery Time	I _F =-20A, di/dt=100A/μs		30		ns
Q _{rr}	Reverse Recovery Charge	I _F =-20A, di/dt=100A/μs		40		nC

Note :

- 1、 The data tested by surface mounted on a 1 inch 2 FR-4 board with 2OZ copper.
- 2、 The data tested by pulsed , pulse width ≤ 300us , duty cycle ≤ 2%
- 3、 The EAS data shows Max. rating . The test condition is T_J =25°C, V_{DD}=-15V, V_G=-10V, R_G=25Ω, L=0.5mH, I_{AS}=-30A
- 4、 The power dissipation is limited by 150°C junction temperature
- 5、 The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.

-30V P-Channel Enhancement Mode MOSFET

Typical Characteristics




Figure 1. Output Characteristics




Figure 2. Transfer Characteristics




Figure 3. Power Dissipation




Figure 4. Drain Current




Figure 5. BV_{DSS} vs Junction Temperature




Figure 6. $R_{DS(ON)}$ vs Junction Temperature



-30V P-Channel Enhancement Mode MOSFET




Figure 7. Gate Charge Waveforms




Figure 8. Capacitance




Figure 9. Body-Diode Characteristics




Figure 10. Maximum Safe Operating Area




Figure.11 Switching Time Waveform





Figure.12 Unclamped Inductive Switching Waveform

Package Mechanical Data-DFN5*6-8L-JQ Single



Symbol	Common			
	mm		Inch	
	Min	Max	Min	Max
A	1.03	1.17	0.0406	0.0461
b	0.34	0.48	0.0134	0.0189
c	0.824	0.0970	0.0324	0.082
D	4.80	5.40	0.1890	0.2126
D1	4.11	4.31	0.1618	0.1697
D2	4.80	5.00	0.1890	0.1969
E	5.95	6.15	0.2343	0.2421
E1	5.65	5.85	0.2224	0.2303
E2	1.60	/	0.0630	/
e	1.27 BSC		0.05 BSC	
L	0.05	0.25	0.0020	0.0098
L1	0.38	0.50	0.0150	0.0197
L2	0.38	0.50	0.0150	0.0197
H	3.30	3.50	0.1299	0.1378
I	/	0.18	/	0.0070

-30V P-Channel Enhancement Mode MOSFET**Attention**

1, Any and all APM Microelectronics products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your APM Microelectronics representative nearest you before using any APM Microelectronics products described or contained herein in such applications.

2, APM Microelectronics assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all APM Microelectronics products described or contained herein.

3, Specifications of any and all APM Microelectronics products described or contained here instipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

4, APM Microelectronics Semiconductor CO., LTD. strives to supply high quality high reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

5, In the event that any or all APM Microelectronics products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

6, No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of APM Microelectronics Semiconductor CO., LTD.

7, Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. APM Microelectronics believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

8, Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the APM Microelectronics product that you intend to use.

-30V P-Channel Enhancement Mode MOSFET

Edition	Date	Change
Rve1.0	2021/3/10	Initial release

Copyright Attribution“APM-Microelectronice”