



Recommended P. C. B  
Layout( $\pm 0.05$ )

Technical Date

Pin(outer sleeve):Brass,machined CuZn38pb2  
 Clip (Contact 4 Finger):Beryllium copper,heat treated  
 Insulator:PBT UL94V-0 colour:black  
 Gold Plated:2um"/80u"Ni,GF  
 Current rating:3Amps  
 Mechanical Life:min 500 cycles  
 Contact resistance: 10mΩ max  
 Dielectric strength:1000V  
 Operating temperature:-40 °C to +105°C  
 Soldering temperature:+255°C

X5621 F V -2xXX- C762 D1150 -1150  
 ① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:F-Female
- 3.Welding Board Angle:V-Straight 180°
- 4.Row No-Pin No:2xXX-2x01Pin-2xXXPin
- 5.line spacing:C=7.62mm
- 6.Pin Length:D=11.50mm
- 7.1150:Type1150

X5621FV-2xXX-C762D1150-1150	PBT	Brass	X5621W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

广东星坤科技股份有限公司

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGULAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
ΔX					16 < L ≤ 63 ±0.4
MARK					L > 63 ±0.5



DSND	SCALE: N/A
DWN	VIEW: ④
CHKD	UNIT: mm/in
APPD	SIZE: A4

MODEL TYPE:	2.54mm BTB Style Connector
PART NO.:	X5621FV-2xXX-C762D1150-1150
DWG NO.:	X-X5621FV-2xXX-C762D1150-1150
WEIGHT	SHEET
	REVISION
1/1	A0

文件工程章