

PRODUCT-DETAILS

CR-M230AC4L

CR-M230AC4L Pluggable interface relay 4c/o, A1-A2=230VAC, 250V/6A, LED



General Information

| Extended Product Type | CR-M230AC4L |
|-----------------------|--|
| Product ID | 1SVR405613R3100 |
| EAN | 4013614497766 |
| Catalog Description | CR-M230AC4L Pluggable interface relay 4c/o, A1-A2=230VAC, 250V/6A, LED |
| Long Description | The CR-M230AC4L pluggable interface relay is a miniature relay, which is to be plugged into a suitable ABB CR-M socket. Plugged into a socket, the combination of relay and socket may be seemlessly snap-on mounted onto a DIN Rail. This relay operates with a 230 V AC rated control supply voltage and has a 4 c/o (SPDT) output with contacts rated at 250 V / 6A, enabling the possibility of switching multiple circuits with a single input signal. The relay has an integrated test button which is used for the manual actuation of the relay by locking it's output contacts. The test button facilitates easy testing and commissioning. The relay also has an integrated LED, which provides the visual indication of the energization of the relay coil. Standard sockets, logic sockets, pluggable function modules, holders and markers are available as accessories. |

| Ordering | |
|------------------------|----------|
| Minimum Order Quantity | 10 piece |
| Customs Tariff Number | 85364900 |
| | |

Popular Downloads

Data Sheet, Technical Information 2CDC110004C0210_05

| Instructions and | 1SVC405600M9000 |
|------------------|-----------------|
| Manuals | |

| Dimensions | |
|-------------------------------|----------|
| Product Net Width | 21.2 mm |
| Product Net Height | 35.6 mm |
| Product Net Depth / Length | 27.5 mm |
| Product Net Weight | 0.033 kg |

| Technical | |
|---|--|
| Function | Pluggable miniature interface relay CR-M |
| Sub-Function | Relay with built in LED |
| Output | 4 c/o (SPDT) contacts |
| Output Signal | 250 V / 6 A |
| Rated Control Supply Voltage (U _s) | 230 V AC |
| Terminal Type | Flat-Pin Connections |

| Environmental | |
|----------------------|-----------------------------------|
| Ambient Air | Operation -40 +55 °C |
| Temperature | Storage -40 +85 °C |
| Maximum Operating | Without Derating 2000 m |
| Altitude Permissible | |
| RoHS Status | Following EU Directive 2011/65/EU |

| Technical UL/CSA | |
|-------------------------------------|----------|
| Maximum Operating Voltage UL/CSA | 300 V AC |
| Ampere Rating UL/CSA | 2.5 A |
| Contact Rating UL/CSA | B300 |
| Pilot Duty UL/CSA | B300 |

| Certificates and Declarations (Document Number) | |
|---|-----------------------------|
| CCC Certificate | CCC_2014010303720193 |
| CQC Certificate | CQC2014010303720193 |
| CSA Certificate | CSA_2735700 |
| cUR Certificate | cUR_E244330 |
| Declaration of Conformity - CCC | 2020980303000200 |
| Declaration of Conformity - CE | 1SVD982021-0003 |
| Declaration of Conformity - UKCA | 1SVD982021-1000 |
| EAC Certificate | EAC_RU_C-DE.ME77.B.00446-19 |
| Environmental Information | 1SAA981009-2401 |
| Instructions and Manuals | 1SVC405600M9000 |
| LR Certificate | LR_05_20002_E5 |
| RMRS Certificate | RMRS_1740019250 |
| RoHS Information | 1SVD982021-0003 |

| UR Certificate | UR_E244330 |
|-----------------|--------------|
| VDE Certificate | VDE_40040327 |

| Container Information | |
|-----------------------------------|---------------|
| Package Level 1 Units | box 10 piece |
| Package Level 1 Width | 114 mm |
| Package Level 1 Height | 61 mm |
| Package Level 1 Depth / Length | 50 mm |
| Package Level 1 Gross Weight | 0.35 kg |
| Package Level 1 EAN | 4013614373657 |

| Classifications | |
|-------------------------------|----------------------------|
| Object Classification Code | К |
| ETIM 4 | EC001437 - Switching relay |
| ETIM 5 | EC001437 - Switching relay |
| ETIM 6 | EC001437 - Switching relay |
| ETIM 7 | EC001437 - Switching relay |
| ETIM 8 | EC001437 - Switching relay |
| eClass | V11.0 : 27371601 |
| UNSPSC | 39122331 |
| E-Number (Finland) | 2712710 |
| E-Number (Sweden) | 4005356 |

Categories

 ${\sf Low \ Voltage \ Products \ and \ Systems \ \rightarrow \ Control \ Products \ \rightarrow \ Electronic \ Relays \ and \ Controls \ \rightarrow \ Interface \ Relays \ and \ Optocouplers \ And \$

