

General Description

The B50T040F N-Channel MOSFET uses advanced technology and allows a minimum $R_{DS(ON)}$ and superior switching performance. It also can withstand high energy pulse in the avalanche and commutation mode.

Application

- High frequency switching mode power supply
- Electronic ballast
- Motor Driver

Features

- Low Gate Charge
- Low C_{rss} (typical 2.1pF)
- Fast switching
- Improved dv/dt capability
- 100% Avalanche Tested
- Fast Reverse Recovery

Typical Application

V_{DS}	500	V
$R_{DS(ON)MAX}$	3.6	Ω
I_D	4	A





Figure 1. Schematic Diagram

Ordering Information

Part Number	Package	Operating Temperature	Packing Type	Marking
B50T040F	TO-252	-40 °C to 105 °C	Tape & Reel 2,500pcs/Reel	B50T040 XXXXXXKP XXXXWWF

Pin Configuration and Marking Information



B50T040
XXXXXXKP
XXXXWWF

XXXXXXK: Lot Code
WW: Week

Figure 2. Pin Configuration and Marking Information

Pin Definition

Pin No.	Name	Description
1	G	Gate
2	D	Drain
3	S	Source

Absolute Maximum Rating (note 1) (Unless otherwise specified, $T_A=25^{\circ}\text{C}$)

Symbol	Parameters	Range	Unit
V_{DS}	Drain-Source Voltage ($V_{GS}=0V$)	500	V
V_{GS}	Gate-Source Voltage ($V_{DS}=0V$)	± 30	V
$I_{D(DC)}$	Continuous Drain Current at $T_c=25^{\circ}\text{C}$ (note 2)	4.0	A
T_J, T_{STG}	Operating Junction and Storage Temperature Range	-55 to 150	$^{\circ}\text{C}$
R_{thJC}	Thermal Resistance, Junction-to-Case	2.2	$^{\circ}\text{C}/\text{W}$
R_{thJA}	Thermal Resistance, Junction-to-Ambient	62.5	$^{\circ}\text{C}/\text{W}$

Note 1: Stress beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. Under "recommended operating conditions" the device operation is assured, but some particular parameter may not be achieved. The electrical characteristics table defines the operation range of the device, the electrical characteristics is assured on DC and AC voltage by the test program. For the parameters without minimum and maximum value in the EC table, the typical value defines the operation range, the accuracy is not guaranteed by spec.

Note 2: Limited by maximum junction temperature.

Disclaimer

The information provided in this datasheet is believed to be accurate and reliable. However, Bright Power Semiconductor (BPS) reserves the right to make changes at any time without prior notice.

No license, to any intellectual property right owned by BPS or any other third party, is granted under this document. BPS provides information in this datasheet "AS IS" and with all faults, and makes no warranty, express or implied, including but not limited to, the accuracy of the information provided in this datasheet, merchantability, fitness of a specific purpose, or non-infringement of intellectual property rights of BPS or any other third party. BPS disclaims any and all liabilities arising out of this datasheet or use of this datasheet, including without limitation consequential or incidental damages.