



SSL54F THRU SSL56F

Surface Mount Low VF Schottky Rectifiers

Reverse Voltage - 20 to 60V

Forward Current - 5.0A

FEATURES

- Metal silicon junction, majority carrier conduction
- For surface mounted applications
- Low power loss, high efficiency
- High forward surge current capability
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications

MECHANICAL DATA

- Case: SMAF
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 27mg 0.00086oz

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Simplified outline SMAF and symbol

Absolute Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz resistive or inductive load, for capacitive load, derate by 20 %

Parameter	Symbols	SSL54F	SSL56F	Units	
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	40	60	V	
Maximum RMS voltage	V_{RMS}	28	42	V	
Maximum DC Blocking Voltage	V_{DC}	40	60	V	
Maximum Average Forward Rectified Current	$I_{F(AV)}$	5.0			A
Peak Forward Surge Current, 8.3ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I_{FSM}	150			A
Max Instantaneous Forward Voltage at 5 A	V_F	0.45	0.55	V	
Maximum DC Reverse Current $T_a = 25^\circ\text{C}$ at Rated DC Reverse Voltage $T_a = 100^\circ\text{C}$	I_R	1.0 50		mA	
Typical Junction Capacitance ¹⁾	C_j	800	500	pF	
Typical Thermal Resistance ²⁾	$R_{\theta JA}$	55			°C/W
Operating Junction Temperature Range	T_j	-55 ~ +125			°C
Storage Temperature Range	T_{stg}	-55 ~ +150			°C

1) Measured at 1MHz and applied reverse voltage of 4 V D.C.

2) P.C.B. mounted with 0.2 X 0.2" (5 X 5 mm) copper pad areas.



广东钜兴电子科技有限公司
GUANGDONG JUXING ELECTRONIC TECHNOLOGY., LTD



SSL54F THRU SSL56F

Surface Mount Low VF Schottky Rectifiers

Characteristic Curves ($T_A=25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Forward Characteristic




Fig.4 Typical Junction Capacitance




Fig.5 Maximum Non-Repetitive Peak Forward Surge Current





Fig.6- Typical Transient Thermal Impedance






SSL54F THRU SSL56F

Surface Mount Low VF Schottky Rectifiers

PACKAGE OUTLINE


Plastic surface mounted package; 2 leads

SMAF



UNIT		A	C	D	E	e	g	H _E	<
mm	max	1.2	0.23	3.7	2.7	1.6	1.3	4.9	7°
	min	0.9	0.18	3.3	2.4	1.3	1.0	4.4	
mil	max	47	9.1	146	106	63	51	193	7°
	min	35.4	7.1	130	94	51	39	173	

The recommended mounting pad size



Marking

Type number	Marking code
SSL54F	SSL54
SSL56F	SSL56