

Description

- Fast Acting, high breaking capacity under 500V
- 6x32mm physical size
- Special Engineering Material tube, Silver plated copper cap construction
- Designed to UL 248-1
- Lead Free material

Applications

- DC common bus
- DC drives
- Power converters/rectifiers
- Reduced voltage starters
- Electric vehicle charging column

Electrical Characteristics

Current Rating	% of Ampere Rating	Opening Time
10A-30A	200%	30 min Max.
	300%	10 sec Max.

Specifications



Part Number	Voltage Rating	Current Rating	Interrupting Rating ¹ (A)	Typical Cold Resistance ² (mOhms)	Typical Pre-Arcing I ² t (A ² Sec)
6CT6-10A <u>xxx</u> ³	500VAC	10A	30KA@500VAC	17.1	98
6CT6-20A <u>xxx</u>	500V AC/DC	20A	30KA@500VAC 20KA@500VDC	5.5	141
6CT6-25A <u>xxx</u>		25A		4.6	211
6CT6-30A <u>xxx</u>		30A		3.7	282


¹ DC Cold Resistance are measured at <10% of rated current in ambient temperature of 25°C

² Typical Pre-arcing I²t (Measured at 10In-rated current, not to exceed IR, time constant of calibrated circuit less than 50 microseconds)


³ xxx = Axial lead length

Dimension(Unit/mm)

Cylindrical



Axial leaded



The length of the lead

38.00 ± 1.0 Ordering P/N: 6CT6-xxx E

52.00 ± 2.0 Ordering P/N: 6CT6-xxx ME


Packaging

Cylindrical fuses: 250pcs per box

38 mm Axial Lead Fuses: 75pcs per box

52mm Axial Lead Fuses: 200pcs per bag

Temperature Derating Curve



Wave Soldering Parameters

Reservoir Temperature: 260°C ± 3°C
 Soldering Time: 10 seconds max.

Recommended Hand Solder Parameters

Soldering Iron Tip Temperature: 350°C ± 5°C
 Heating Time: 5 seconds max.

Operating Temperature Range

- 55°C to + 125°C

Time-Current Curves

