






**N- channel 650V, 12A Power MOSFET**

<p><b>Description</b> The Power MOSFET is fabricated using the advanced planer VDMOS technology. The resulting device has low conduction resistance, superior switching performance and high avalanche energy.</p> <p><b>Features</b></p> <ul style="list-style-type: none"> <li>◆ Low <math>R_{DS(on)}</math></li> <li>◆ Low gate charge (typ. <math>Q_g = 41.9</math> nC)</li> <li>◆ 100% UIS tested</li> <li>◆ RoHS compliant</li> </ul> <p><b>Applications</b></p> <ul style="list-style-type: none"> <li>◆ Power factor correction.</li> <li>◆ Switched mode power supplies.</li> <li>◆ LED driver.</li> </ul>	<p><b>Product Summary</b></p> <table border="0"> <tr> <td><math>V_{DSS}</math></td> <td>650V</td> </tr> <tr> <td><math>I_D</math></td> <td>12A</td> </tr> <tr> <td><math>R_{DS(on),max}</math></td> <td>0.8<math>\Omega</math></td> </tr> <tr> <td><math>Q_{g,typ}</math></td> <td>41.9 nC</td> </tr> </table> <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  <p><b>TO-252</b></p> </div> <div style="text-align: center;">  <p><b>TO-220F</b></p> </div> </div> <div style="text-align: center; margin-top: 20px;">  <p><b>N-Channel MOSFET</b></p> </div>	$V_{DSS}$	650V	$I_D$	12A	$R_{DS(on),max}$	0.8 $\Omega$	$Q_{g,typ}$	41.9 nC
$V_{DSS}$	650V								
$I_D$	12A								
$R_{DS(on),max}$	0.8 $\Omega$								
$Q_{g,typ}$	41.9 nC								

**Absolute Maximum Ratings**

Parameter	Symbol	Value	Unit
Drain-Source Voltage	$V_{DSS}$	650	V
Continuous drain current ( $T_c=25^\circ\text{C}$ ) ( $T_c = 100^\circ\text{C}$ )	$I_D$	12 7.5	A A
Pulsed drain current <sup>1)</sup>	$I_{DM}$	48	A
Gate-Source voltage	$V_{GSS}$	$\pm 30$	V
Avalanche energy, single pulse <sup>2)</sup>	$E_{AS}$	500	mJ
Peak diode recovery $dv/dt$ <sup>3)</sup>	$dv/dt$	5	V/ns
Power Dissipation TO-220F/TO-220F Narrow Pin ( $T_c=25^\circ\text{C}$ ) Derate above $25^\circ\text{C}$	$P_D$	42 0.34	W W/ $^\circ\text{C}$
Power Dissipation TO-252 ( $T_c = 25^\circ\text{C}$ ) Derate above $25^\circ\text{C}$		150 1.2	W W/ $^\circ\text{C}$
Operating junction and storage temperature range	$T_J, T_{STG}$	-55 to +150	$^\circ\text{C}$
Continuous diode forward current	$I_S$	12	A
Diode pulse current	$I_{S,pulse}$	48	A

**Thermal Characteristics**

Parameter	Symbol	Value		Unit
		TO-220F\TO-220F Narrow Pin	TO-252	
Thermal resistance, Junction-to-case	$R_{\theta JC}$	2.98	0.83	$^\circ\text{C/W}$



Thermal resistance, Junction-to-ambient	R <sub>θJA</sub>	110	62.5	°C/W
---	------------------	-----	------	------

## Package Marking and Ordering Information

Device	Device Package	Marking	Units/Tube	Units/Real
BCT12N65	TO-220F	BCT12N65	50	
BCD12N65	TO-252	BCD12N65		2500

## Electrical Characteristics

T<sub>c</sub> = 25°C unless otherwise noted

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
<b>Static characteristics</b>						
Drain-source breakdown voltage	BV <sub>DSS</sub>	V <sub>GS</sub> =0 V, I <sub>D</sub> =0.25 mA	650	-	-	V
Gate threshold voltage	V <sub>GS(th)</sub>	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =0.25 mA	2	-	4	V
Drain cut-off current	I <sub>DSS</sub>	V <sub>DS</sub> =650 V, V <sub>GS</sub> =0 V, T <sub>J</sub> = 25°C T <sub>J</sub> = 125°C	-	-	1 100	μA
Gate leakage current, Forward	I <sub>GSSF</sub>	V <sub>GS</sub> =30 V, V <sub>DS</sub> =0 V	-	-	100	nA
Gate leakage current, Reverse	I <sub>GSSR</sub>	V <sub>GS</sub> =-30 V, V <sub>DS</sub> =0 V	-	-	-100	nA
Drain-source on-state resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> =10 V, I <sub>D</sub> =6A	-	0.64	0.8	Ω
<b>Dynamic characteristics</b>						
Input capacitance	C <sub>iss</sub>	V <sub>DS</sub> =25V, V <sub>GS</sub> =0V,	-	2000	-	pF
Output capacitance	C <sub>OSS</sub>	f = 1 MHz	-	164	-	
Reverse transfer capacitance	C <sub>rss</sub>		-	7.4	-	
Turn-on delay time	t <sub>d(on)</sub>	V <sub>DD</sub> =325V, I <sub>D</sub> =12A	-	14.6	-	ns
Rise time	t <sub>r</sub>	R <sub>G</sub> = 10 Ω, V <sub>GS</sub> =15 V	-	37.8	-	
Turn-off delay time	t <sub>d(off)</sub>		-	69.3	-	
Fall time	t <sub>f</sub>		-	15.8	-	
<b>Gate charge characteristics</b>						
Gate to source charge	Q <sub>GS</sub>	V <sub>DD</sub> =520 V, I <sub>D</sub> =12 A,	-	10.8	-	nC
Gate to drain charge	Q <sub>GD</sub>	V <sub>GS</sub> =0 to 10 V	-	15	-	
Gate charge total	Q <sub>G</sub>		-	41.9	-	
Gate plateau voltage	V <sub>plateau</sub>		-	5	-	V
<b>Reverse diode characteristics</b>						
Diode forward voltage	V <sub>SD</sub>	V <sub>GS</sub> =0 V, I <sub>F</sub> =12 A	-	-	1.5	V
Reverse recovery time	t <sub>rr</sub>	V <sub>R</sub> =325 V, I <sub>F</sub> =12 A,	-	450.4	-	ns
Reverse recovery charge	Q <sub>rr</sub>	dI <sub>F</sub> /dt=100 A/μs	-	4.75	-	μC
Peak reverse recovery current	I <sub>rrm</sub>		-	21.1	-	A

### Notes:

1. Pulse width limited by maximum junction temperature.
2. L=10mH, I<sub>AS</sub> = 10A, Starting T<sub>J</sub>= 25°C.
3. I<sub>SD</sub> = 12A, di/dt ≤ 100A/μs, V<sub>DD</sub> ≤ BV<sub>DSS</sub>, Starting T<sub>J</sub>= 25°C.



### Electrical Characteristics Diagrams

Figure 1. Typical Output Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance Variation vs. Drain Current




Figure 4. Threshold Voltage vs. Temperature




Figure 5. Breakdown Voltage vs. Temperature




Figure 6. On-Resistance vs. Temperature






Figure 7. Capacitance Characteristics




Figure 8. Gate Charge Characteristics




Figure 9. Maximum Safe Operating Area TO-220F/TO-220F Narrow Pin




Figure 10. Maximum Safe Operating Area TO-252




Figure 11. Power Dissipation vs. Temperature TO-220F/TO-220F Narrow Pin




Figure 12. Power Dissipation vs. Temperature TO-252






Figure 13. Continuous Drain Current vs. Temperature




Figure 14. Body Diode Transfer Characteristics




Figure 15 Transient Thermal Impedance, Junction to Case, TO-220F/TO-220F Narrow Pin







Figure 16. Transient Thermal Impedance, Junction to Case, TO-252









Gate Charge Test Circuit & Waveform



Switching Test Circuit & Waveforms




Unclamped Inductive Switching Test Circuit & Waveforms






**Mechanical Dimensions for TO-220F**

UNIT: mm




SYMBOL	MIN	NOM	MAX
A	4.5		4.9
A1	2.3		2.9
b	0.65		0.9
b1	1.1		1.7
b2	1.2		1.4
c	0.35		0.65
D	14.5		16.5
D1	6.1		6.9
E	9.6		10.3
E1	6.5	7	7.5
e	2.44	2.54	2.64
L	12.5		14.3
L1	9.45		10.05
L2	15		16
L3	3.2		4.4
φP	3		3.3
Q	2.5		2.9

**TO-220F Part Marking Information**






**Mechanical Dimensions for TO-252**



UNIT: mm

SYMBOL	MIN	NOM	MAX
A	2.10		2.50
B	0.80		1.25
b	0.50		0.85
b1	0.50		0.90
b2	0.45		0.60
C	0.45		0.60
D	6.35		6.75
D1	5.10		5.50
E	5.80		6.30
e1	2.25	2.30	2.35
e2	4.45		4.75
L1	9.50		10.20
L2	0.90		1.45
L3	0.60		1.10
K	-0.1		0.10


**TO-252 Part Marking Information**







**Mechanical Dimensions for TO-220F Narrow Pin**



(UNITS:mm)

SYMBOL	MIN	NOM	MAX
A	4.50	4.70	4.83
A1	2.34	2.54	2.74
A2	0.70 REF		
A3	2.56	2.76	2.93
b	0.60	—	0.80
b1	0.90	—	1.10
c	0.45	0.50	0.60
D	15.67	15.87	16.07
D1	12.87	13.07	13.27
D2	12.28	12.48	12.68
E	9.96	10.16	10.36
e	2.54BSC		
H1	6.48	6.68	6.88
L	12.68	12.98	13.28
L1	—	—	0.85
L2	6.50REF		
$\phi P$	3.08	3.18	3.28
Q	3.20	—	3.40
$\theta 1$	1°	3°	5°

**TO-220F Narrow Pin Part Marking Information**

