

# DATA SHEET

## AUTOMOTIVE GRADE HIGH VOLTAGE CHIP RESISTORS

RV series  
0.5%, 1%, 5%  
sizes 0603/0805/1206/2010/2512

RoHS compliant

IEC 62368-1 Safety Certificate issued by UL Demko:  
sizes 0603/0805/1206



SCOPE

This specification describes RV0603/0805/1206/2010/2512 high voltage chip resistors with lead-free terminations made by thick film process.

APPLICATIONS

- Converter
- Printer equipment
- Battery charger
- Computer
- Power supply
- Car electronics

FEATURES

- AEC-Q200 qualified
  - RoHS compliant
  - Reducing environmentally hazardous wastes
  - High component and equipment reliability
  - Non-forbidden materials used in products/production
  - Halogen Free Epoxy
  - Moisture sensitivity level: MSL 1
  - IEC 62368-1:2018 safety certificate issued by UL Demko for the following sizes and resistance ranges:
    - 0603: 100KΩ to 12MΩ
    - 0805: 100KΩ to 24MΩ
    - 1206: 100KΩ to 27MΩ
- \*Please refer to UL certification

ORDERING INFORMATION - GLOBAL PART NUMBER & I2NC

Both part numbers are identified by the series, size, tolerance, packing type, temperature coefficient, taping reel and resistance value.

**YAGEO BRAND ordering code**

**GLOBAL PART NUMBER (PREFERRED)**

**RV XXXX X X X XX XXXX L**  
 (1) (2) (3) (4) (5) (6) (7)

**(1) SIZE**

0603/0805/1206/2010/2512

**(2) TOLERANCE**

D = ±0.5%  
 F = ±1%  
 J = ±5%

**(3) PACKAGING TYPE**

R = Paper/PE taping reel  
 K = Embossed taping reel

**(4) TEMPERATURE COEFFICIENT OF RESISTANCE**

– = Base on spec

**(5) TAPING REEL**

07= 7 inch dia. Reel

**(6) RESISTANCE VALUE**

There are 2~4 digits indicated the resistor value. Letter R/K/M is decimal point, no need to mention the last zero after R/K/M, e.g.1K2, not 1K20.

Detailed resistance rules show in table of "Resistance rule of global part number".

**(7) DEFAULT CODE**

Letter L is system default code for ordering only <sup>(Note)</sup>

| Resistance rule of global part number |  |
|---------------------------------------|--|
| Resistance code rule                  | Example                                  |
| XXXX<br>(10 to 97.6 KΩ)               | 10K = 10,000 Ω<br>97K6 = 97,600 Ω        |
| XXXX<br>(100 to 976 KΩ)               | 100K = 100,000Ω<br>976K = 976,000Ω       |
| XMXX<br>(1 to 9.76 MΩ)                | 1M = 1,000,000 Ω<br>9M76 = 9,760,000 Ω   |
| XXMX<br>(10 to 16 MΩ)                 | 10M = 10,000,000 Ω<br>27M = 27,000,000 Ω |

**ORDERING EXAMPLE**

The ordering code of a RV1206 chip resistor, value 1 MΩ with ±5% tolerance, supplied in 7-inch tape reel is: RV1206JR-071ML.

**NOTE**

1. All our R-Chip products meet RoHS compliant. "LFP" of the internal 2D reel label mentions "Lead Free Process"
2. On customized label, "LFP" or specific symbol printed and the optional "L" at the end of GLOBAL PART NUMBER / I2NC can be added (both are on customer request)

**PHYCOMP BRAND ordering codes**

Both GLOBAL PART NUMBER (preferred) and I2NC (traditional) codes are acceptable to order Phycomp brand products.

**GLOBAL PART NUMBER (PREFERRED)**

For detailed information of GLOBAL PART NUMBER and ordering example, please refer to page 2.

**I2NC CODE**

| SIZE | TYPE    | 2322 XXX XXXXX L |     |             |           | EMBOSSED (2)<br>TAPE ON REEL<br>4,000 | PAPER/PE (2)<br>TAPE ON REEL (units)<br>5,000 | Last digit of I2NC<br>Resistance decade (3) | Last digit |
|------|---------|------------------|-----|-------------|-----------|---------------------------------------|---|---|------------|
|      |         | (1)              | (2) | (3)         | (4)       |                                       |   |   |            |
| 0805 | VRC11   | 2322             | ±5% | 47 to 10M Ω | -         | 792 61xxx                             | 0.01 to 0.0976 Ω                              | 0   |            |
|      | VRC12   | 2322             | ±1% | 47 to 10M Ω | -         | 793 6xxxx                             | 0.1 to 0.976 Ω                                | 7   |            |
| 1206 | VRC01   | 2322             | ±5% | 47 to 27M Ω | -         | 790 61xxx                             | 1 to 9.76 Ω                                   | 8   |            |
|      | VRC02   | 2322             | ±1% | 47 to 10M Ω | -         | 791 6xxxx                             | 10 to 97.6 Ω                                  | 9   |            |
| 2512 | VPRC221 | 2322             | ±5% | 47 to 16M Ω | 762 98xxx | -                                     | 100 to 976 Ω                                  | 1   |            |
|      |         |                  |     |             |           |                                       | 1 to 9.76 KΩ                                  | 2   |            |
|      |         |                  |     |             |           |                                       | 10 to 97.6 KΩ                                 | 3   |            |
|      |         |                  |     |             |           |                                       | 100 to 976 KΩ                                 | 4   |            |
|      |         |                  |     |             |           |                                       | 1 to 9.76 MΩ                                  | 5   |            |
|      |         |                  |     |             |           |                                       | 10 to 97.6 MΩ                                 | 6   |            |

- (1) The resistors have a 12-digit ordering code starting with 2322.
- (2) The subsequent 4 or 5 digits indicate the resistor tolerance and packaging.
- (3) The remaining 4 or 3 digits represent the resistance value with the last digit indicating the multiplier as shown in the table of "Last digit of I2NC".
- (4) "L" is optional symbol (Note).

**ORDERING EXAMPLE**

The ordering code of a VRC01 resistor, value 1 MΩ with ±5% tolerance, supplied in tape of 5,000 units per reel is: 232279061105L or RVI206JR-071ML.

Example:


|        |   |             |
|--------|---|-------------|
| 0.02 Ω | = | 0200 or 200 |
| 0.3 Ω  | = | 3007 or 307 |
| 1 Ω    | = | 1008 or 108 |
| 33 KΩ  | = | 3303 or 333 |
| 10 MΩ  | = | 1006 or 106 |

**NOTE**

- 1. All our R-Chip products are RoHS compliant. "LFP" of the internal 2D reel label mentions "Lead Free Process"
- 2. On customized label, "LFP" or specific symbol printed and the optional "L" at the end of GLOBAL PART NUMBER / I2NC can be added (both are on customer request)


**MARKING**

**RV0603/0805/1206/2010/2512**



E-24 series: 3 digits, ±5%  
First two digits for significant figure and 3rd digit for number of zeros

**RV0603**




E-24 series: 3 digits, ±0.5% & ±1%  
Exception values 10/11/13/15/20/75 of E24 series  
One short bar under marking letter



E-96 series: 3 digits, ±0.5% & ±1%  
Including values 10/11/13/15/20/75 of E24 series  
First two digits for E-96 marking rule and 3rd letter for number of zeros

**RV0805/1206/2010/2512**



Both E-24 and E-96 series: 4 digits, ±0.5% & ±1%  
First three digits for significant figure and 4th digit for number of zeros

For further marking information, please refer to data sheet “Chip resistors marking”.

**CONSTRUCTION**

The resistor is constructed on top of a high-grade ceramic body. Internal metal electrodes are added on each end to make the contacts to the thick film resistive element. The composition of the resistive element is a noble metal imbedded into a glass and covered by a second glass to prevent environment influences. The resistor is laser trimmed to the rated resistance value. The resistor is covered with a protective epoxy coat, finally the two external terminations (matte tin on Ni-barrier) are added. See fig.5

**DIMENSIONS**

Table I For outlines see fig. 5

| TYPE   | L (mm)     | W (mm)     | H (mm)     | l <sub>1</sub> (mm) | l <sub>2</sub> (mm) |
|--------|------------|------------|------------|---------------------|---------------------|
| RV0603 | 1.60 ±0.10 | 0.80 ±0.10 | 0.45 ±0.10 | 0.25 ±0.15          | 0.25 ±0.15          |
| RV0805 | 2.00 ±0.10 | 1.25 ±0.10 | 0.50 ±0.10 | 0.35 ±0.20          | 0.35 ±0.20          |
| RV1206 | 3.10 ±0.10 | 1.60 ±0.10 | 0.55 ±0.10 | 0.45 ±0.20          | 0.40 ±0.20          |
| RV2010 | 5.00 ±0.10 | 2.50 ±0.15 | 0.55 ±0.10 | 0.55 ±0.15          | 0.50 ±0.20          |
| RV2512 | 6.35 ±0.10 | 3.10 ±0.15 | 0.55 ±0.10 | 0.60 ±0.20          | 0.50 ±0.20          |

**OUTLINES**




Fig. 5 Chip resistor outlines

**ELECTRICAL CHARACTERISTICS**

Table 2

| TYPE   | RESISTANCE RANGE             | CHARACTERISTICS |                             |                      |                       |                                 |                                       |
|--------|------------------------------|-----------------|-----------------------------|----------------------|-----------------------|---------------------------------|---------------------------------------|
|        |                              | Rated Power     | Operating Temperature Range | Max. Working Voltage | Max. Overload Voltage | Dielectric Withstanding Voltage | Temperature Coefficient of Resistance |
| RV0603 | 5% (E-24) 47Ω to 10MΩ        | 1/10W           |                             | 350V                 | 500V                  | 500V                            |                                       |
|        | 1% (E-24/E-96) 47Ω to 10MΩ   |                 |                             |                      |                       |                                 |                                       |
|        | 0.5% (E-24/E-96) 47Ω to 10MΩ |                 |                             |                      |                       |                                 |                                       |
| RV0805 | 5% (E-24) 47Ω to 22MΩ        | 1/8 W           |                             | 400 V                | 800 V                 | 800 V                           |                                       |
|        | 1% (E-24/E-96) 47Ω to 22MΩ   |                 |                             |                      |                       |                                 |                                       |
|        | 0.5% (E-24/E-96) 47Ω to 10MΩ |                 |                             |                      |                       |                                 |                                       |
| RV1206 | 5% (E-24) 47Ω to 27MΩ        | 1/4 W           | -55 °C to +155 °C           | 500 V                | 1,000 V               | 1,000 V                         | ±200 ppm/°C                           |
|        | 1% (E-24/E-96) 47Ω to 27MΩ   |                 |                             |                      |                       |                                 |                                       |
|        | 0.5% (E-24/E-96) 47Ω to 15MΩ |                 |                             |                      |                       |                                 |                                       |
| RV2010 | 5% (E-24) 47Ω to 22MΩ        | 3/4W            |                             | 500 V                | 1,000 V               | 1,000 V                         |                                       |
|        | 1% (E-24/E-96) 47Ω to 22MΩ   |                 |                             |                      |                       |                                 |                                       |
|        | 0.5% (E-24/E-96) 47Ω to 10MΩ |                 |                             |                      |                       |                                 |                                       |
| RV2512 | 5% (E-24) 47Ω to 16MΩ        | 1 W             |                             | 500 V                | 1,000 V               | 1,000 V                         |                                       |
|        | 1% (E-24/E-96) 47Ω to 16MΩ   |                 |                             |                      |                       |                                 |                                       |
|        | 0.5% (E-24/E-96) 47Ω to 10MΩ |                 |                             |                      |                       |                                 |                                       |

**FOOTPRINT AND SOLDERING PROFILES**

For recommended footprint and soldering profiles, please refer to data sheet “Chip resistors mounting”.

**PACKING STYLE AND PACKAGING QUANTITY**

Table 3 Packing style and packaging quantity

| PACKING STYLE            | REEL DIMENSION | RV0603 | RV0805 | RV1206 | RV2010 | RV2512 |
|--------------------------|----------------|--------|--------|--------|--------|--------|
| Paper/PE taping reel (R) | 7" (178 mm)    | 5,000  | 5,000  | 5,000  | ---    | ---    |
| Embossed taping reel (K) | 7" (178 mm)    | ---    | ---    | ---    | 4,000  | 4,000  |

**NOTE**

I. For Paper/PE/Embossed tape and reel specification/dimensions, please refer to data sheet “Chip resistors packing”.

**FUNCTIONAL DESCRIPTION****OPERATING TEMPERATURE RANGE**

Range: -55 °C to +155 °C

**POWER RATING**

Each type rated power at 70 °C:

RV0603=1/10W; RV0805=1/8W; RV1206=1/4W;

RV2010=3/4W; RV2512=1W

**RATED VOLTAGE**

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V = \sqrt{(P \times R)}$$

or max. working voltage whichever is less


Where

V = Continuous rated DC or AC (rms) working voltage (V)

P = Rated power (W)

R = Resistance value ( $\Omega$ )

Maximum working voltage can be applicable to resistors only if the resistance value is equal to or higher than the critical resistance value.



**TESTS AND REQUIREMENTS**

**Table 4** Test condition, procedure and requirements

| TEST                         | TEST METHOD                                | PROCEDURE  | REQUIREMENTS                       |
|------------------------------|--|--|------------------------------------|
| High Temperature Exposure    | AEC-Q200 Test 3<br>MIL-STD-202 Method 108  | 1,000 hours at T <sub>A</sub> = 155 °C, unpowered  | ±(1.0%+0.05Ω)                      |
| Moisture Resistance          | AEC-Q200 Test 6<br>MIL-STD-202 Method 106  | Each temperature / humidity cycle is defined at 8 hours (method 106F), 3 cycles / 24 hours for 10d. with 25 °C / 65 °C 95% R.H, without steps 7a & 7b, unpowered   | ±(2.0%+0.05Ω)                      |
| Biased Humidity              | AEC-Q200 Test 7<br>MIL-STD-202 Method 103  | 1,000 hours; 85 °C / 85% RH<br>10% of operating power<br>Measurement at 24±4 hours after test conclusion.  | ±(5.0%+0.05Ω)                      |
| Operational Life             | AEC-Q200 Test 8<br>MIL-STD-202 Method 108  | 1,000 hours at 125 °C, derated voltage applied for 1.5 hours on, 0.5 hour off, still-air required  | ±(3.0%+0.05Ω)                      |
| Resistance to Soldering Heat | AEC-Q200 Test 15<br>MIL-STD-202 Method 210 | Condition B, no pre-heat of samples<br>Lead-free solder, 260±5 °C, 10±1 seconds immersion time<br>Procedure 2 for SMD: devices fluxed and cleaned with isopropanol | ±(1.0%+0.05Ω)<br>No visible damage |
| Thermal Shock                | AEC-Q200 Test 16<br>MIL-STD-202 Method 107 | -55/+125 °C<br>Number of cycles is 300. Devices mounted<br>Maximum transfer time is 20 seconds.<br>Dwell time is 15 minutes. Air – Air                             | ±(1.0%+0.05Ω)                      |
| ESD                          | AEC-Q200 Test 17<br>AEC-Q200-002           | Human Body Model,<br>I <sub>pos.</sub> + I <sub>neg.</sub> discharges<br>0201: 500V<br>0402/0603: 1KV<br>0805 and above: 2KV                                       | ±(4.0%+0.05Ω)                      |

| TEST   | TEST METHOD                      | PROCEDURE   | REQUIREMENTS                                    |
|--|----------------------------------|---|---|
| Solderability<br>- Wetting                     | AEC-Q200 Test I8<br>J-STD-002    | Electrical Test not required Magnification 50X<br>SMD conditions:<br>(a) Method B, aging 4 hours at 155 °C dry heat, dipping at 235±3 °C for 5±0.5 seconds.<br>(b) Method B, steam aging 8 hours, dipping at 215±3 °C for 5±0.5 seconds.<br>(c) Method D, steam aging 8 hours, dipping at 260±3 °C for 30±0.5 seconds.  | Well tinned (≥95% covered)<br>No visible damage |
| Board Flex                                     | AEC-Q200 Test 21<br>AEC-Q200-005 | Chips mounted on a 90mm glass epoxy resin PCB (FR4)<br>Bending for 0201/0402: 5 mm<br>0603/0805: 3 mm<br>1206 and above: 2 mm<br>Holding time: minimum 60 seconds   | ±(1.0%+0.05Ω)                                   |
| Temperature Coefficient of Resistance (T.C.R.) | MIL-STD-202 Method 304           | At +25/-55 °C and +25/+125 °C<br><br><b>Formula:</b><br>$T.C.R = \frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6 \text{ (ppm/°C)}$<br>Where<br>t <sub>1</sub> =+25 °C or specified room temperature<br>t <sub>2</sub> =-55 °C or +125 °C test temperature<br>R <sub>1</sub> =resistance at reference temperature in ohms<br>R <sub>2</sub> =resistance at test temperature in ohms | Refer to table 2                                |
| Short Time Overload                            | IEC60115-1 4.13                  | 2.5 times of rated voltage or maximum overload voltage whichever is less for 5 sec at room temperature  | ±(2.0%+0.05Ω)                                   |



REVISION HISTORY

| REVISION   | DATE          | CHANGE NOTIFICATION | DESCRIPTION   |
|------------|---------------|---------------------|---|
| Version 10 | Aug. 13, 2021 | -                   | - Upgrade to Automotive Grade   |
| Version 9  | Feb. 01, 2021 | -                   | - Update IEC62368-1 safety certificate declaration for sizes 0603/0805/1206   |
| Version 8  | Nov. 09, 2018 | -                   | - Add AEC-Q200 for 47ohm ≤ R < 5Mohm  |
| Version 7  | Jul. 06, 2017 | -                   | - Add IEC62368-1 safety certificate declaration for sizes 0603/0805/1206  |
| Version 6  | Dec. 01, 2016 | -                   | - Extend resistor value of RV1206 0.5%  |
| Version 5  | Aug. 27, 2015 | -                   | - Extend resistor range and add 0.5%  |
| Version 4  | Jan. 27, 2014 | -                   | - RV0603 resistance range extend to 10MΩ<br>- Add RV2010  |
| Version 3  | Aug. 26, 2013 | -                   | - Add RV0603  |
| Version 2  | Sep 29, 2011  | -                   | - Type error correction   |
| Version 1  | Nov 19, 2008  | -                   | - Change to dual brand datasheet that describes RV0805/1206/2512 with RoHS compliant<br>- Description of "Halogen Free Epoxy" added<br>- Define global part number  |
| Version 0  | Feb 14, 2006  | -                   | - New datasheet for high voltage chip resistors sizes of 0805/1206/2512, 5%, 1% tolerance with lead-free terminations<br>- Replace the 0805/1206/2512 parts of pdf files: VRC01_02_11_12_51_3.pdf, VPRC221_5_3.pdf, and combine into a document.<br>- Test method and procedure updated<br>- PE tape added (paper tape will be replaced by PE tape) |

“ Yageo reserves all the rights for revising the content of this datasheet without further notification, as long as the products itself are unchanged. Any product change will be announced by PCN.”