



3A SURFACE MOUNT SCHOTTKY BRIDGE

FEATURES:


- Reverse Voltage - 40 to 200 V
- Forward Current - 3 A
- High Surge Current Capability
- Designed for Surface Mount Application

PINNING

PIN	DESCRIPTION
1	Input Pin (~)
2	Input Pin (~)
3	Output Anode (+)
4	Output Cathode (-)

MECHANICAL DATA

- Case: MBF
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 75mg 0.0026oz



Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified.

Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derate by 20 %.

Parameter	Symbols	MB34F	MB36F	MB38F	MB310F	MB320F	Units					
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	40	60	80	100	200	V					
Maximum RMS voltage	V_{RMS}	28	42	56	70	140	V					
Maximum DC Blocking Voltage	V_{DC}	40	60	80	100	200	V					
Maximum Average Forward Rectified Current at $T_c = 100^\circ C$	$I_{F(AV)}$	3.0					A					
Peak Forward Surge Current, 8.3ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I_{FSM}	80		70			A					
Max Instantaneous Forward Voltage at 3 A	V_F	0.55	0.70	0.85		0.95	V					
Maximum DC Reverse Current $T_a = 25^\circ C$ at Rated DC Reverse Voltage $T_a = 100^\circ C$	I_R	0.5 10	0.3 5			mA						
Typical Junction Capacitance ¹⁾	C_j	220	160			100	pF					
Typical Thermal Resistance ²⁾	$R_{\theta JA}$	65					°C/W					
Operating Junction Temperature Range	T_j	-55 ~ +150					°C					
Storage Temperature Range	T_{stg}	-55 ~ +150					°C					

Note: 1. Measured at 1MHz and applied reverse voltage of 4 V D.C.

2. Mounted on glass epoxy PC board with 4×1.5"×1.5" (3.81×3.81 cm) copper pad.



Fig.1 Forward Current Derating Curve




Fig.3 Typical Forward Characteristic




Fig.5 Maximum Non-Repetitive Peak Forward Surge Current




Fig.2 Typical Reverse Characteristics




Fig.4 Typical Junction Capacitance





Fig.6-Typical Transient Thermal Impedance







PACKAGE OUTLINE

Plastic surface mounted package; 4 leads

MBF



The recommended mounting pad size



Marking

Type number	Marking code
MB34F	MB34F
MB36F	MB36F
MB38F	MB38F
MB310F	MB310F
MB320F	MB320F