iW1709



Off-Line Digital Green-Mode Quasi-Resonant PWM Controller

1 Description

The iW1709 is a high performance AC/DC power supply controller that uses digital control technology to build peak current mode PWM flyback power supplies. The device directly drives a power BJT and operates in quasi-resonant mode to provide high efficiency and key built-in protection features, while minimizing the external component count, simplifying EMI design, and lowering the total bill of material cost. The iW1709 features a distinctive soft-start scheme, which allows for fast and yet smooth start-up with both small and large capacitive loads. The iW1709 removes the need for a secondary feedback circuit while achieving excellent line and load regulation. It also eliminates the need for loop compensation components while maintaining stability over all operating conditions. The pulse-by-pulse waveform analysis allows for fast dynamic load response. The built-in power limit function enables optimized transformer design for a wide input voltage range.

Dialog's innovative proprietary technology ensures that power supplies built with the iW1709 can achieve both the highest average efficiency and less than 50mW no-load power consumption; they also have fast yet smooth start-up with a wide range of capacitive loads with output voltage of 12V and above, and are ideal for network, set-top box, and home appliance power supply applications.

2 Features

- Optimized for 12V/1A AC/DC adapters with <50mW no-load power consumption at 230V_{AC} and fast dynamic response
- Direct drive of low-cost BJT power switch
- Adaptively controlled soft start enables fast and smooth start-up for a wide range of capacitive loads (from 330µF to 6,000µF) with output voltage of 12V and above
- Very tight constant voltage and constant current regulation over entire operating range
- **PrimAccurate**[™] primary-side feedback eliminates opto-isolator and simplifies design
- EZ-EMI® design enhances manufacturability
- Intrinsically low common mode noise

- Optimized 72kHz maximum PWM switching frequency achieves best size and efficiency
- Adaptive multi-mode PWM/PFM control improves efficiency
- Quasi-resonant operation for highest overall efficiency
- Dynamic base current control
- No external loop compensation components required
- Complies with EPA 2.0/CoC Ver5/DoE energy-efficiency specifications with ample margin
- Built-in protections for output short-circuit, output low impedance, and output overvoltage
- Built-in over-temperature protection (OTP)
- No audible noise over entire operating range

3 Applications

- Network power adapters for ADSL, wireless access points and routers
- AC/DC adapter for set-top box
- AC/DC power supplies for home appliances

Product Summary	





Figure 3.1 : iW1709 Typical Application Circuit (Achieving < 50mW No-load Power Consumption in 12V/1A Adapter Designs. Using Depletion Mode NFET as Active Start-up Device.)



Figure 3.2 : iW1709 Typical Application Circuit (Achieving < 100mW No-load Power Consumption in 12V/1A Adapter Designs. Alternative Circuit without Using Active Start-up Device.)

Product Summary	Rev. 1.1	24-Jan-2022

iW1709



Off-Line Digital Green-Mode Quasi-Resonant PWM Controller

4 Pinout Description



Figure 4.1 : 8-Lead SOIC-8 Package

Pin Number	Pin Name	Туре	Pin Description
1	GND	Ground	Ground.
2	GND	Ground	Ground.
3	GND	Ground	Ground.
4	OUTPUT	Output	Base drive for BJT.
5	I _{SENSE}	Analog Input	Primary current sense. It is used for cycle-by-cycle peak current control and limit.
6	V _{SENSE}	Analog Input	Auxiliary voltage sense. It is used for primary regulation.
7	ASU	Output	Control signal for active start-up device (BJT or Depletion NFET).
8	V _{cc}	Power Input	IC power supply.

5 Absolute Maximum Ratings

Absolute maximum ratings are the parameter values or ranges which can cause permanent damage if exceeded. For maximum safe operating conditions, refer to Electrical Characteristics in Section 6.

Parameter	Symbol	Value	Units
DC supply voltage range (pin 8, I _{CC} = 20mA max)	V _{cc}	-0.3 to 25.0	V
Continuous DC supply current at V_{CC} pin (V_{CC} = 15V)	I _{cc}	25	mA
ASU output (pin 7)		-0.3 to 19.0	V
Output (pin 4)		-0.3 to 4.0	V
V _{SENSE} input (pin 6, I _{VSENSE} ≤ 10mA)		-0.7 to 4.0	V
I _{SENSE} input (pin 5)		-0.3 to 4.0	V
Maximum junction temperature	T _{JMAX}	150	°C
Operating junction temperature	T _{JOPT}	-40 to 150	°C
Storage temperature	T _{STG}	-65 to 150	°C
Thermal resistance junction-to-ambient	θ _{JA}	155	°C/W
ESD rating per JEDEC JESD22-A114		±2,000	V
Latch-up test per JESD78D		±100	mA



6 Physical Dimensions

8-Lead Small Outline (SOIC) Package



nbol	Inches		Millim	eters
Syr	MIN	MAX	MIN	MAX
А	0.053	0.069	1.35	1.75
A1	0.0040	0.010	0.10	0.25
A2	0.049	0.059	1.25	1.50
В	0.014	0.019	0.35	0.49
С	0.007	0.010	0.19	0.25
D	0.189	0.197	4.80	5.00
Е	0.150	0.157	3.80	4.00
е	0.050 BSC		1.27	BSC
Н	0.228	0.244	5.80	6.20
h	0.10	0.020	0.25	0.50
L	0.016	0.049	0.4	1.25
α	0°	8°		

Compliant to JEDEC Standard MS12F

Controlling dimensions are in inches; millimeter dimensions are for reference only

This product is RoHS compliant and Halide free.

Soldering Temperature Resistance:

[a] Package is IPC/JEDEC Std 020D moisture sensitivity level 1

[b] Package exceeds JEDEC Std No. 22-A111 for solder immersion resistance; package can withstand 10 s immersion < 260°C

Dimension D does not include mold flash, protrusions or gate burrs. Mold flash, protrusions or gate burrs shall not exceed 0.15 mm per end. Dimension E1 does not include interlead flash or protrusion. Interlead flash or protrusion shall not exceed 0.25 mm per side.

The package top may be smaller than the package bottom. Dimensions D and E1 are determined at the outermost extremes of the plastic body exclusive of mold flash, tie bar burrs, gate burrs and interlead flash, but including any mismatch between the top and bottom of the plastic body.

7 Ordering Information

Part Number	Options	Package	Description
iW1709-00	Cable Comp = 0mV, OTP recovery threshold = 100°C	SOIC-8	Tape & Reel ¹
iW1709-01	Cable Comp = 150mV, OTP recovery threshold = 100°C	SOIC-8	Tape & Reel ¹
iW1709-11	Cable Comp = 150mV, OTP recovery threshold = 120°C	SOIC-8	Tape & Reel ¹

Note 1: Tape & Reel packing quantity is 2,500/reel. Minimum ordering quantity is 2,500.

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers skilled in the art designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only for development of an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising out of your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

© 2022 Renesas Electronics Corporation. All rights reserved.

RoHS Compliance

Dialog Semiconductor's suppliers certify that its products are in compliance with the requirements of Directive 2011/65/EU of the European Parliament on the restriction of the use of certain hazardous substances in electrical and electronic equipment. RoHS certificates from our suppliers are available on request.

(Rev.1.0 Mar 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu Koto-ku, Tokyo 135-0061, Japan www.renesas.com

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit: www.renesas.com/contact/

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Product	Summary
---------	---------

24-Jan-2022