

PRODUCT-DETAILS

GS201 AC-C20/0.03

GS201 AC-C20/0.03 Residual Current Circuit Breaker with Overcurrent Protection



General Information

Extended Product Type	GS201 AC-C20/0.03
Product ID	2TAZ210111R2204
EAN	6940342287100
Catalog Description	GS201 AC-C20/0.03 Residual Current Circuit Breaker with Overcurrent Protection
Long Description	Residual Current Circuit Breaker with Overcurrent Protection GS201 AC-C20/0.03

Technical	
Standards	IEC 61009 GB 16917
Tripping Characteristic	C
Type of Residual Current	AC type
Rated Operational Voltage	230 V AC
Rated Current (In)	20 A
Rated Residual Current	30 mA
Rated Short-Circuit Capacity (I _{cn})	6 kA
Maximum Breaking Capacity	6 kA
Number of Poles	1+N
Number of Protected Poles	1
Number of Earth Leakage Circuit Breakers	1

Operating Characteristic	Instantaneous
Position of Neutral Terminals	Right
Release Type	C
Accessories Available	Yes

Technical UL/CSA

Short-Circuit Current	
Rating (SCCR)	

Dimensions	
Product Net Width	69 mm
Product Net Height	0.085 m
Product Net Depth / Length	70 mm
Product Net Weight	0.203 kg

Container Information

Ordering	
Minimum Order Quantity	1 piece
Customs Tariff Number	85363010
Country of Origin	China (CN)

Certificates and Declarations (Document N	
Declaration of	No declaration needed
Conformity - CE	
Instructions and	No document needed
Manuals	

Popular Downloads	
Data Sheet, Technical Information	1SXF400005C2013
Instructions and Manuals	No document needed

Classifications	
ETIM 7	EC002281 - Distributor assembly with combination RCCB/MCB
ETIM 8	EC002281 - Distributor assembly with combination RCCB/MCB
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer
CN8	85363010

30 mA

6940342287100

Categories

Low Voltage Products and Systems \rightarrow Modular DIN Rail Products \rightarrow Residual Current Devices RCDs \rightarrow Residual Current Circuit Breakers with Overcurrent Protection RCBO

