





Outline Drawing(mm)



Electrical structure



Recommended layout(mm)



Pin Connections


Input	3
Output 1	4
Output 2	6
ground	1,2,5

Features

- Operating temperature range: -40 °C to +85 °C
- Storage temperature range: -55 °C to +100 °C





Applications

- For catv
- For broadband and wireless communications




Electrical Specifications: TA=25 °C, 0dBm, Z0=75Ω

Parameter	Test Conditions	Units	Min	Typ	Max
Main line Loss (Pin3-4)	5-200MHz	dB	—	0.4	1.5
Main line Loss (Pin3-6)	5-200MHz	dB	—	0.5	1.8
Amplitude Balance	5-200MHz	dB	0.0	0.1	1.0
Phase Balance	5-200MHz	°	0.0	3.0	8.0
Input Return Loss(Pin3)	5-200MHz	dB	20.0	25.0	—
CMRR	5-200MHz	dB	20.0	30.0	—



Carrier Tape Orientation



Tape & Reel Information

Parameter	Units	Value
Qty per reel	PCS	2000
Reel Size	mm	330
Tape Width	mm	12.00
Pitch	mm	8.00
Ao	mm	4.50
Bo	mm	5.30
Ko	mm	3.60