

# N-Channel 60V(D-S) MOSFET

## RC2308A

### GENERAL DESCRIPTION

The SS2308 is the N-Channel logic enhancement mode power field effect transistors are produced using high cell density, DMOS trench technology. This high density process is especially tailored to minimize on-state resistance. These devices are particularly suited for low voltage application such as cellular phone and notebook computer power management and other battery powered circuits where high-side switching and low in-line power loss are needed in a very small outline surface mount package.

### FEATURES

- $R_{DS(ON)} \leq 100m\Omega @ V_{GS} = 10V$
- $R_{DS(ON)} \leq 130m\Omega @ V_{GS} = 4.5V$
- Super high density cell design for extremely low  $R_{DS(ON)}$
- Exceptional on-resistance and maximum DC current capability
- Capable doing Cu wire bonding

### APPLICATIONS

- Power Management in Note book
- Portable Equipment
- Battery Powered System
- Load Switch
- DSC


### Feature

60V/2.6A,     $R_{DS(ON)} = 80m\Omega(\text{MAX}) @ V_{GS} = 4.5V$ .  
 $R_{DS(ON)} = 140m\Omega(\text{MAX}) @ V_{GS} = 2.5V$ .

Super High dense cell design for extremely low  $R_{DS(ON)}$ .

Reliable and Rugged.

SOT-23 for Surface Mount Package.



SOT-23

N-Channel MOSFET

# N-Channel 60V(D-S) MOSFET

## RC2308A

**Absolute Maximum Ratings (T<sub>A</sub>=25°C Unless Otherwise Noted)**

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V <sub>DSS</sub>	60	V
Gate-Source Voltage	V <sub>GSS</sub>	±20	V







**Electrical Characteristics (T<sub>j</sub>=25°C Unless Otherwise Specified)**

Symbol	Parameter	Limit	Min	Typ	Max	Unit
<b>STATIC</b>						
BV <sub>DSS</sub>	Drain-Source Breakdown Voltage	V <sub>GS</sub> =0, I <sub>D</sub> =250 μA	60			V
V <sub>G(th)</sub>	Gate Threshold Voltage	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250 μA	1		3	V
I <sub>GSS</sub>	Gate Body Leakage	V <sub>DS</sub> =0V, V <sub>GS</sub> =±20V			±100	nA
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	V <sub>DS</sub> =60V, V <sub>GS</sub> =0V			1	μA
'R <sub>D(on)</sub>	Drain-Source On-Resistance	V <sub>GS</sub> =10V, I <sub>D</sub> = 2.6A		82	100	mΩ
		V <sub>GS</sub> =4.5V, I <sub>D</sub> = 2.1A		96	130	
		V <sub>GS</sub> =3.3V, I <sub>D</sub> = 1.8A		139	200	
V <sub>SD</sub>	Diode Forward Voltage	I <sub>S</sub> =1.0A, V <sub>GS</sub> =0V		0.8	1.2	V
<b>DYNAMIC</b>						
Q <sub>g</sub>	Total Gate Charge	V <sub>DS</sub> =30V, V <sub>GS</sub> =10V, I <sub>D</sub> =2.6A		12		nC
Q <sub>g</sub>	Total Gate Charge	V <sub>DS</sub> =30V, V <sub>GS</sub> =4.5V, I <sub>D</sub> =2.6A		6.5		
Q <sub>gs</sub>	Gate-Source Charge			2.2		
Q <sub>gd</sub>	Gate-Drain Charge			2.7		
C <sub>iss</sub>	Input capacitance	V <sub>DS</sub> =30V, V <sub>GS</sub> =0V, f=1MHz		350		pF
C <sub>oss</sub>	Output Capacitance			40		
C <sub>rss</sub>	Reverse Transfer Capacitance			12		
R <sub>g</sub>	Gate Resistance	V <sub>DS</sub> =0V, V <sub>GS</sub> =0V, f=1MHz		0.7		Ω
t <sub>d(on)</sub>	Turn-On Delay Time	V <sub>DD</sub> =20V, R <sub>L</sub> =20 Ω I <sub>D</sub> =1A, V <sub>GEN</sub> =10V R <sub>G</sub> =1Ω		10		ns
t <sub>r</sub>	Turn-On Rise Time			11		
t <sub>d(off)</sub>	Turn-Off Delay Time			29		
t <sub>f</sub>	Turn-Off Fall Time			3		

# N-Channel 60V(D-S) MOSFET

## RC2308A

### Typical Characteristics ( $T_J = 25^\circ\text{C}$ Noted)



# N-Channel 60V(D-S) MOSFET

## RC2308A

### Typical Characteristics ( $T_J = 25^\circ\text{C}$ Noted)

