

PRODUCT-DETAILS

GDA204 AC-25/0.03

GDA204 AC-25/0.03 Residual Current Device Block



General Information

Extended Product Type	GDA204 AC-25/0.03
Product ID	2TAZ812401R2250
EAN	6957625383725
Catalog Description	GDA204 AC-25/0.03 Residual Current Device Block
Long Description	Residual Current Device Block GDA204 AC-25/0.03

Technical

Standards	IEC 61009 GB 16917
Type of Residual Current	AC type
Rated Voltage (U_r)	230...400 V
Rated Operational Voltage	230 / 400 V AC
Rated Insulation Voltage (U_i)	500 V
Rated Impulse Withstand Voltage (U_{imp})	4 kV
Rated Current (I_n)	25 A
Rated Residual Current	30 mA
Maximum Surge Current	0.25 kA

Leakage Current Type	AC
Rated Frequency (f)	50/60 Hz
Number of Poles	4
Operating Characteristic	Instantaneous
Connecting Capacity	Rigid 16 ... 16 mm ² Flexible 16 ... 16 mm ²

Environmental

Ambient Temperature	-25...55 °C
Ambient Air Temperature	Operation -25...55 °C
Degree of Protection	IP2X
Pollution Degree	2

Technical UL/CSA

Short-Circuit Current Rating (SCCR)	0.03 ... 0.03 A
-------------------------------------	-----------------

Dimensions

Product Net Width	0.105 m
Product Net Height	0.093 m
Product Net Depth / Length	0.069 m
Product Net Weight	0.164 kg

Container Information

Package Level 1 EAN	6957625383725
---------------------	---------------

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030
Country of Origin	China (CN)

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	No declaration needed
Instructions and Manuals	No document needed

Popular Downloads

Data Sheet, Technical Information	1SXF400005C2013
Instructions and Manuals	No document needed

Classifications

ETIM 7	EC002297 - Residual current circuit breaker (RCCB) module
ETIM 8	EC002297 - Residual current circuit breaker (RCCB) module
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer
CN8	85363030

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Circuit Breakers with Overcurrent Protection RCBO

